

# Slip Fix Couplings

## Product Features

- For cold water use only
- Can be used in repairing broken lines or when adding additional lines or fittings
- Pipe ends must be restrained
- Working pressure rating: 150 psi
- Available in 1/2" - 2" Sizes
- PVC SCH.40 Type 1 Grade 1
- IPS Spigot/IPS Socket
- Internal self-lubricating EPDM O-ring for long life and smooth movement
- Complies with ASTM and ANSI standards



PF40SFC


## Installation Instructions

- Cut out section of broken pipe slightly longer than compressed slip fix coupling
- Apply glue to expand Quick-Fix to fill the gap

## Model Numbers

MODEL NO.	Size	D	D1	I	L	L1	L2	d1	d2								
		in	mm	in	mm	in	mm	in	mm								
PF40SFCD	1/2"	1.8	46.1	0.8	21.3	0.8	20.5	6.7	171.0	8.6	219.5	0.8	20.5	0.8	21.5	0.8	21.2
PF40SFCF	3/4"	2.0	51.5	1.0	26.7	1.1	27.4	7.6	192.0	9.8	249.5	1.0	26.0	1.1	26.9	1.0	26.6
PF40SFCG	1"	2.5	63.3	1.3	33.4	1.2	31.0	8.8	223.0	11.3	287.5	1.1	28.6	1.3	33.7	1.3	33.3
PF40SFCH	1-1/4"	2.9	73.7	1.7	42.2	1.3	34.0	9.8	248.5	12.5	317.0	1.3	31.8	1.7	42.4	1.7	42.0
PF40SFCJ	1-1/2"	3.2	80.5	1.7	42.3	1.4	35.5	9.8	249.0	12.7	323.5	1.3	33.4	1.9	48.1	1.9	48.1
PF40SFCK	2"	3.6	92.6	2.4	60.3	1.5	37.0	11.3	286.5	14.3	364.3	1.4	34.5	2.4	60.6	2.4	60.2

NO.	PART	MATERIAL
1	BODY	PVC
2	SLIDER	PVC
3	UNION NUT	PVC
4	O' RING	EPDM
5	O' RING	EPDM



## Warranty and Codes

This PROFLO product carries a 1 Year Limited Warranty. Complies with ASTM and ANSI standards.