



This Part requires two clamps, part number 212-300.  
See additional drawing for information on these clamps.

**NOTES:**  
-SOME HIDDEN LINES NOT SHOWN  
-BREAK ALL SHARP CORNERS  
-REPORT ALL CHANGES TO ENGINEERING

**PROPRIETARY AND CONFIDENTIAL**  
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF FERNCO, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF FERNCO, INC. IS PROHIBITED.

Part Weight	6.46 lbs.
Min/Max Temp.	-30/140 Degrees F
Pressure Tested	4.3 PSI
Material	Flexible PVC
Installation Torque	60" Lbs.
Conforms to ASTM	D5926, C1173
Box Quantity	5
Clamps used	300 Series

**TOLERANCES:**  
.X= Fractional ±  
.XX= ±.02  
.XXX= ±.030  
ANG.= ±0.5°  
UNLESS OTHERWISE SPECIFIED

DESCRIPTION:  
**Coupling 12" Plastic x 12" Plastic**

**1056-1212**

UNITS: <b>INCHES</b>	SIZE <b>A</b>	DESIGNER: <b>D. Brady</b>	SCALE not to scale
3RD ANGLE PROJECTION DO NOT SCALE DRAWING		CHECKER:	DATE: <b>1/31/2007</b>
			SHEET 1 OF 1