


# FERNCO FLEXIBLE COUPLINGS

connect pipe sizes 1-1/4" to 27"

\*Supplied with reducer.

For sizes over 27", see Large Diameter Couplings, Page 12.



## Asbestos Cement Fibre or Ductile Iron to Cast Iron or Plastic

SERIES 1051 designed for asbestos cement fibre or ductile iron to cast iron or plastic.

Part No.	A		B		C	
	in.	mm	in.	mm	in.	mm
*1051-43	4.75	120	3.38	85	4.00	101
1051-44	4.87	120	4.50	111	4.00	101
1051-54	5.90	149	4.38	111	4.00	101
1051-55	5.90	149	5.38	136	5.00	127
1051-64	7.00	177	4.38	111	6.00	152
1051-65	7.00	177	5.38	136	6.00	152
1051-66	7.00	177	6.38	162	6.00	152
*1051-86	9.12	231	6.38	162	6.00	152
1051-88	9.12	231	8.50	215	6.00	152
*1051-10-8	11.12	282	8.50	215	6.00	152
1051-1010	11.12	282	10.60	269	6.00	152
*1051-1210	13.20	335	10.60	269	6.00	152
1051-1212	13.20	335	12.60	320	6.00	152
1051-1615	17.85	453	15.40	391	7.00	177
1051-1818	19.50	495	18.90	480	10.00	254

## Asbestos Cement Fibre or Ductile Iron to Asbestos Cement Fibre or Ductile Iron

SERIES 1055 designed for asbestos cement fibre or ductile iron to asbestos cement fibre or ductile iron.

Part No.	A		B		C	
	in.	mm	in.	mm	in.	mm
1055-44	4.75	120	4.75	120	4.00	101
*1055-54	5.90	149	4.75	120	5.00	127
1055-55	5.90	149	5.90	149	5.00	127
1055-64	7.00	177	4.75	120	6.00	152
1055-65	7.00	177	5.90	149	6.00	152
1055-66	7.10	180	7.10	180	6.00	152
*1055-86	9.12	231	7.00	177	6.00	152
1055-88	9.12	231	9.12	231	6.00	152
*1055-10-8	11.12	282	9.12	231	6.00	152
1055-1010	11.12	282	11.12	282	6.00	152
*1055-1210	13.20	335	11.12	282	6.00	152
1055-1212	13.20	335	13.20	335	6.00	152
*1055-1615	17.80	452	16.50	419	10.00	254
*1055-1818	19.50	495	19.50	495	10.00	254

## Cast Iron, Plastic, Copper, Steel or Lead to Cast Iron, Plastic, Copper, Steel or Lead

SERIES 1056 designed for cast iron or plastic to cast iron or plastic.

Part No.	A		B		C	
	in.	mm	in.	mm	in.	mm
1056-125	1.65	40	1.65	40	3.50	88
1056-150/125	1.90	48	1.65	40	3.50	88
1056-150	1.90	48	1.90	48	3.50	88
1056-215	2.40	60	1.90	48	3.50	88
1056-22	2.40	60	2.40	60	3.50	88
1056-315	3.38	85	1.90	48	4.00	101
1056-32	3.38	85	2.40	60	4.00	101
1056-33	3.38	85	3.38	85	4.00	101
1056-415	4.38	111	1.90	48	4.00	101
1056-42	4.38	111	2.40	60	4.00	101
1056-43	4.38	111	3.38	85	4.00	101
1056-44	4.42	112	4.42	112	4.00	101
*1056-53	5.62	142	3.38	85	4.00	101
1056-54	5.62	142	4.38	111	4.00	101
1056-55	5.62	142	5.62	142	4.00	101
*1056-63	6.38	162	3.38	85	6.00	152
1056-64	6.38	162	4.38	111	6.00	152
1056-65	6.50	165	5.50	140	6.00	152
1056-66	6.38	162	6.38	162	6.00	152
*1056-84	8.50	215	4.38	111	6.00	152
1056-86	8.50	215	6.38	162	6.00	152
1056-88	8.50	215	8.50	215	6.00	152
1056-10-8	10.60	269	8.50	215	6.00	152
1056-1010	10.60	269	10.60	269	6.00	152
1056-1210	12.60	320	10.60	269	6.00	152
1056-1212	12.83	326	12.83	326	6.00	152
1056-1512	16.00	391	12.60	320	6.00	152
1056-1515	15.40	391	15.40	391	10.00	254
*1056-1815	18.90	480	15.30	404	10.00	254
1056-1818	18.90	480	18.90	480	10.00	254
1056-2121	22.30	566	22.30	566	10.00	254
1056-2424	25.00	635	25.00	635	10.00	254
1056-2727	28.20	716	28.20	716	10.00	254

## SIZING CHART 1059 Socket to Pipe

Part No.	A		B		C	
	in.	mm	in.	mm	in.	mm
1059-150	2.25	57	1.93	49	4.00	101
1059-22	2.75	70	2.43	62	4.00	101
1059-33	3.95	100	3.51	89	4.00	101
1059-44	4.99	127	4.51	115	4.00	101

## SIZING CHART 1060 Socket to Socket

Part No.	A		B		C	
	in.	mm	in.	mm	in.	mm
1060-150	2.25	57	2.25	57	4.00	101
1060-22	2.75	70	2.75	70	4.00	101
1060-33	3.95	100	3.95	100	4.00	101
1060-44	4.99	127	4.99	127	4.00	101

