



aquatherm NPT TRANSITION PIECE (female)

With hex-shaped threaded transition.



Stainless steel part no. (ISO)	Lead-free (potable) brass part no. (NPT)	Dimension PP-R (ND — OD) x thread	d	R	l	z	D	L	SW	Weight
			[in]	[in]	[in]	[in]	[in]	[in]	[in]	[lb]
-	0621108	(½" — 20 mm) x ½" F	0.79	0.50	1.36	0.79	1.48	1.99	0.94	0.17
-	0621110	(½" — 20 mm) x ¾" F	0.79	0.75	1.14	0.57	1.71	1.97	1.22	0.25
-	0621111	(¾" — 25 mm) x ½" F	0.98	0.50	1.42	0.79	1.48	2.05	0.94	0.20
-	0621112	(¾" — 25 mm) x ¾" F	0.98	0.75	1.14	0.51	1.71	1.97	1.22	0.24
-	0621113	(1" — 32 mm) x ¾" F	1.26	0.75	1.26	0.55	1.71	2.09	1.22	0.25
(NPT)										
1121114	0621114	(1" — 32 mm) x 1" F	1.26	1.00	1.48	0.77	2.36	2.34	1.54	0.53
1121115	0621115	(1 ¼" — 40 mm) x 1" F	1.57	1.00	1.57	0.77	2.36	2.44	1.54	0.50
1121116	0621116	(1 ¼" — 40 mm) x 1 ¼" F	1.57	1.25	1.57	0.77	2.91	2.48	1.97	0.85
1121117	0621117	(1 ½" — 50 mm) x 1 ¼" F	1.97	1.25	1.69	0.77	2.91	2.60	1.97	0.89
1121118	0621118	(1 ½" — 50 mm) x 1 ½" F	1.97	1.50	1.77	0.85	3.37	2.64	2.17	0.92
1121119	0621119	(2" — 63 mm) x 1 ½" F	2.48	1.50	2.03	0.94	3.31	2.89	2.17	0.97
1121120	0621120	(2" — 63 mm) x 2" F	2.48	2.00	2.01	0.93	3.98	3.03	2.64	1.32
-	0621122	(2 ½" — 75 mm) x 2" F	2.95	2.00	2.01	0.83	3.94	3.03	2.64	1.34

aquatherm TRANSITION PIECE round (female)



Stainless steel part no. (ISO)	Lead-free (potable) brass part no. (NPT)	Dimension PP-R (ND — OD) x thread	d	R	l	z	D	L	Weight
			[in]	[in]	[in]	[in]	[in]	[in]	[lb]
0921008	0621008	(½" — 20 mm) x ½" F	0.79	0.50	1.08	0.51	1.48	1.59	0.14
0921010	0621010	(½" — 20 mm) x ¾" F	0.79	0.75	1.08	0.51	1.71	1.59	0.20
0921011	0621011	(¾" — 25 mm) x ½" F	0.98	0.50	1.59	0.51	1.48	1.65	0.14
0921012	0621012	(¾" — 25 mm) x ¾" F	0.98	0.75	1.08	0.45	1.71	1.59	0.19
0921013	0621013	(1" — 32 mm) x ¾" F	1.26	0.75	1.20	0.49	1.71	1.71	0.20



aquatherm

we've got a pipe for that