


aquatherm NPT FUSION OUTLET (female)

Includes hex-shaped female thread, weld-in surface and weld-in socket for fusion with the inner wall of the pipe. The necessary welding heads are listed on pages 57-58 (part no. 0050614 - 0050640).



Stainless steel part no. (ISO)	Lead-free (potable) brass part no. (NPT)	Dimension pipe x outlet (ND — OD) x thread	r	d	R	l	z	D	SW	Weight
			[in]	[in]	[in]	[in]	[in]	[in]	[in]	[lb]
0928214	0628214	1 ¼" x ½" — 40 x 25 mm x ½" F	0.79	0.98	0.50	1.54	1.69	1.52	0.94	0.19
0928216	0628216	1 ½" x ½" — 50 x 25 mm x ½" F	0.99	0.98	0.50	1.54	1.89	1.52	0.94	0.20
0928218	0628218	2" x ½" — 63 x 25 mm x ½" F	1.24	0.98	0.50	1.54	2.15	1.52	0.94	0.20
0928220	0628220	2 ½" x ½" — 75 x 25 mm x ½" F	1.48	0.98	0.50	1.54	2.11	1.52	0.94	0.18
0928222	0628222	3" x ½" — 90 x 25 mm x ½" F	1.77	0.98	0.50	1.54	2.17	1.52	0.94	0.20
0928224	0628224	3 ½" x ½" — 110 x 25 mm x ½" F	2.17	0.98	0.50	1.54	3.07	1.52	0.94	0.20
0928226	0628226	4" x ½" — 125 x 25 mm x ½" F	2.46	0.98	0.50	1.54	3.37	1.52	0.94	0.20
0928230	0628230	6" x ½" — 160 x 25 mm x ½" F	3.15	0.98	0.50	1.54	4.06	1.52	0.94	0.20
0928232	0628232	8 to 10" x ½" — 200 to 250 x 25 mm x ½" F	3.94	0.98	0.50	1.54	1.50	1.52	0.94	0.20
0928234	0628234	1 ¼" x ¾" — 40 x 25 mm x ¾" F	0.79	0.98	0.75	1.54	1.69	1.71	1.22	0.24
0928236	0628236	1 ½" x ¾" — 50 x 25 mm x ¾" F	0.99	0.98	0.75	1.54	1.95	1.71	1.22	0.24
0928238	0628238	2" x ¾" — 63 x 25 mm x ¾" F	1.24	0.98	0.75	1.54	2.19	1.71	1.22	0.24
0928240	0628240	2 ½" x ¾" — 75 x 25 mm x ¾" F	1.48	0.98	0.75	1.54	2.48	1.71	1.22	0.24
0928242	0628242	3" x ¾" — 90 x 25 mm x ¾" F	1.77	0.98	0.75	1.54	2.87	1.71	1.22	0.24
0928244	0628244	3 ½" x ¾" — 110 x 25 mm x ¾" F	2.17	0.98	0.75	1.54	3.17	1.71	1.22	0.24
0928246	0628246	4" x ¾" — 125 x 25 mm x ¾" F	2.46	0.98	0.75	1.54	3.78	1.71	1.22	0.25
0928250	0628250	6" x ¾" — 160 x 25 mm x ¾" F	3.15	0.98	0.75	1.54	2.30	1.71	1.22	0.25
0928254	0628254	8 to 10" x ¾" — 200 to 250 x 25 mm x ¾" F	3.94	0.98	0.75	1.54	2.60	1.71	1.22	0.25
(NPT)										
1128260	0628260	2 ½" x 1" — 75 x 32 mm x 1" F	1.48	1.26	1.00	1.69	2.99	2.36	1.54	0.49
1128262	0628262	3" x 1" — 90 x 32 mm x 1" F	1.77	1.26	1.00	1.69	3.29	2.36	1.54	0.49
1128264	0628264	3 ½" x 1" — 110 x 32 mm x 1" F	2.17	1.26	1.00	1.69	3.98	2.36	1.54	0.49
1128266	0628266	4" x 1" — 125 x 32 mm x 1" F	2.46	1.26	1.00	1.69	4.84	2.36	1.54	0.49
1128270	0628270	6" x 1" — 160 x 32 mm x 1" F	3.15	1.26	1.00	1.69	4.65	2.36	1.54	0.50
1128274	0628274	8 to 10" x 1" — 200 to 250 x 32 mm x 1" F	3.94	1.26	1.00	1.69	4.76	2.36	1.54	0.54



aquatherm

we've got a pipe for that