



aquatherm UNION WITH BRASS NUT



Part no.	Dimension (ND — OD)	d	l	z	D	SW1	SW2	Weight
		[in]	[in]	[in]	[in]	[in]	[in]	[lb]
0115812	1" — 32 mm	1.26	1.44	0.73	1.61	2.52	1.97	1.06
0115814	1 ¼" — 40 mm	1.57	1.50	0.69	1.97	3.15	2.36	1.85
0115816	1 ½" — 50 mm	1.97	1.61	0.69	2.40	3.39	2.76	1.81
0115818	2" — 63 mm	2.48	1.77	0.69	2.99	4.25	3.54	3.30
0115820	2 ½" — 75 mm	2.95	1.22	0.69	3.54	5.04	4.09	4.40

Replacement gaskets available upon request.

aquatherm UNION WITH PP-R NUT



Part no.	Dimension (ND — OD)	d	l	z	l1	z1	D	Weight
		[in]	[in]	[in]	[in]	[in]	[in]	[lb]
0115838	½" — 20 mm	0.79	1.02	0.47	0.79	0.22	1.81	0.08
0115840	¾" — 25 mm	0.98	1.10	0.47	0.83	0.20	2.20	0.13
0115842	1" — 32 mm	1.26	1.26	0.47	0.91	0.20	2.60	0.20
0115844	1 ¼" — 40 mm	1.57	1.50	0.55	1.00	0.20	3.11	0.30
0115846	1 ½" — 50 mm	1.97	1.77	0.63	1.12	0.20	3.43	0.37
0115848	2" — 63 mm	2.48	2.19	0.79	1.28	0.20	4.21	0.53
0115850	2 ½" — 75 mm	2.95	1.97	0.79	1.42	0.24	5.04	1.20

Replacement gaskets available upon request.