


aquatherm blue pipe® REDUCING TEE (REDUCER) (inlet, outlet, branch)



SDR	Part no.	Dimension (ND — OD)	d	d1	l	z	Weight
			[in]	[in]	[in]	[in, +0.25/-0.0]	[lb]
17.6	2513604 ^a	6" x 6" x 4" — 160 x 160 x 125 mm	6.30	4.92	9.06	9.06	6.39
	2513618	8" x 8" x 6" — 200 x 200 x 160 mm	7.87	6.30	11.8	12.0	12.2
	2513634	10" x 10" x 6" — 250 x 250 x 160 mm	9.84	6.30	14.8	14.8	22.7
	2513640	10" x 10" x 8" — 250 x 250 x 200 mm	9.84	7.87	14.8	14.8	22.3
	2513655	12" x 12" x 8" — 315 x 315 x 200 mm	12.4	7.87	18.1	18.1	48.0
	2513657	12" x 12" x 10" — 315 x 315 x 250 mm	12.4	9.84	18.1	18.1	44.5
	2513669	14" x 14" x 10" — 355 x 355 x 250 mm	14.0	9.84	18.9	18.9	54.6
	2513671	14" x 14" x 12" — 355 x 355 x 315 mm	14.0	12.4	18.9	18.9	58.6
	2513684	16" x 16" x 12" — 400 x 400 x 315 mm	15.8	12.4	19.7	19.7	69.3
	2513685	16" x 16" x 14" — 400 x 400 x 355 mm	15.8	14.0	19.7	19.7	68.6
	2513699	18" x 18" x 14" — 450 x 450 x 355 mm	17.7	14.0	20.7	20.7	94.6
	2513700	18" x 18" x 16" — 450 x 450 x 400 mm	17.7	15.8	20.7	20.7	93.8
	2513813	20" x 20" x 14" — 500 x 500 x 355 mm	19.7	14.0	23.6	23.6	137
	2513814	20" x 20" x 16" — 500 x 500 x 400 mm	19.7	15.8	23.6	23.6	137
	2513815	20" x 20" x 18" — 500 x 500 x 450 mm	19.7	17.7	23.6	23.6	135
	2513849	24" x 24" x 16" — 630 x 630 x 400 mm	24.8	15.8	26.2	26.2	246
	2513850	24" x 24" x 18" — 630 x 630 x 450 mm	24.8	17.7	26.2	26.2	247
	2513851	24" x 24" x 20" — 630 x 630 x 500 mm	24.8	19.7	26.2	26.2	242
11	2613605 ^a	6" x 6" x 4" — 160 x 160 x 125 mm	6.30	4.92	9.06	9.06	9.12
	2613619	8" x 8" x 6" — 200 x 200 x 160 mm	7.87	6.30	11.8	12.0	18.0
	2613635	10" x 10" x 6" — 250 x 250 x 160 mm	9.84	6.30	14.8	14.8	35.1
	2613641	10" x 10" x 8" — 250 x 250 x 200 mm	9.84	7.87	14.8	14.8	35.2
	2013655	12" x 12" x 8" — 315 x 315 x 200 mm	12.4	7.87	18.1	18.1	66.3
	2013657	12" x 12" x 10" — 315 x 315 x 250 mm	12.4	9.84	18.1	18.1	66.7
	2013669	14" x 14" x 10" — 355 x 355 x 250 mm	14.0	9.84	18.9	18.9	83.9
	2013671	14" x 14" x 12" — 355 x 355 x 315 mm	14.0	12.4	18.9	18.9	90.3
	2013684	16" x 16" x 12" — 400 x 400 x 315 mm	15.8	12.4	19.7	19.7	108
	2013685	16" x 16" x 14" — 400 x 400 x 355 mm	15.8	14.0	19.7	19.7	107
	2013699	18" x 18" x 14" — 450 x 450 x 355 mm	17.7	14.0	20.7	20.7	146
	2013700	18" x 18" x 16" — 450 x 450 x 400 mm	17.7	15.8	20.7	20.7	146
9	0813604 ^a	6" x 6" x 4" — 160 x 160 x 125 mm	6.30	4.92	9.06	9.06	12.6
	0813618	8" x 8" x 6" — 200 x 200 x 160 mm	7.87	6.30	11.8	11.8	24.7
	0813634	10" x 10" x 6" — 250 x 250 x 160 mm	9.84	6.30	14.8	14.8	47.6
	0813640	10" x 10" x 8" — 250 x 250 x 200 mm	9.84	7.87	14.8	14.8	48.3
	0813908	12" x 12" x 8" — 315 x 315 x 200 mm	12.4	7.87	18.1	18.1	93.1
	0813910	12" x 12" x 10" — 315 x 315 x 250 mm	12.4	9.84	18.1	18.1	94.6
	0813922	14" x 14" x 10" — 355 x 355 x 250 mm	14.0	9.84	18.9	18.9	122.8
	0813924	14" x 14" x 12" — 355 x 355 x 315 mm	14.0	12.4	18.9	18.9	122.2

^a4" branch is socket fusion. If needed, branch can come with a 1ft extension to be used for butt-fusion.



aquatherm

we've got a pipe for that