


aquatherm blue pipe® ELBOW 90° SD (STANDARD DIMENSION, SEGMENTED, BUTT-FUSION)



| SDR | Part no. | Dimension (ND — OD) | d | z | Weight |
|---------|--------------|------------------------|------|------------------|--------|
| | | | [in] | [in, +0.25/-0.0] | [lb] |
| 17.6 | 7412130 | 6" — 160 mm | 6.30 | 9.00 | 4.25 |
| | 7412134 | 8" — 200 mm | 7.87 | 12.0 | 8.25 |
| | 7412138 | 10" — 250 mm | 9.84 | 15.0 | 15.8 |
| | 7412142 | 12" — 315 mm | 12.4 | 18.0 | 30.0 |
| | 7412144 | 14" — 355 mm | 14.0 | 21.0 | 44.0 |
| | 7412146 | 16" — 400 mm | 15.8 | 24.0 | 63.0 |
| | 7412148 | 18" — 450 mm | 17.8 | 27.0 | 90.0 |
| | 7412150 | 20" — 500 mm | 19.7 | 30.0 | 123 |
| 7412154 | 24" — 630 mm | 24.8 | 36.0 | 233 | |
| 11 | 7512130 | 6" — 160 mm | 6.30 | 9.00 | 6.25 |
| | 7512134 | 8" — 200 mm | 7.87 | 12.0 | 12.5 |
| | 7512138 | 10" — 250 mm | 9.84 | 15.0 | 24.3 |
| | 7512142 | 12" — 315 mm | 12.4 | 18.0 | 46.0 |
| | 7512144 | 14" — 355 mm | 14.0 | 21.0 | 67.0 |
| | 7512146 | 16" — 400 mm | 15.8 | 24.0 | 97.0 |
| | 7512148 | 18" — 450 mm | 17.7 | 27.0 | 138 |
| 9 | 7212130 | 6" — 160 mm | 6.30 | 9.00 | 11.4 |
| | 7212134 | 8" — 200 mm | 7.87 | 12.0 | 19.2 |
| | 7212138 | 10" — 250 mm | 9.84 | 15.0 | 45.5 |
| | 7212142 | 12" — 315 mm | 12.4 | 18.0 | 54.3 |
| | 7212144 | 14" — 355 mm | 14.0 | 21.0 | 80.4 |

UV Coated fittings available upon request. Contact your Aquatherm Regional Sales Manager for pricing and availability.