



# Cast Iron Test Plug

## Product Features and Applications

- For testing leaks and for sealing off piping
- Includes hollow stems which can be fill or drain piping
- Low Pressure ONLY: Max. 10 PSI.
- Designed for use on water only
- Cast Iron: (Top, Body & Plug)
- Wing Nut: Ductile Iron
- Rubber Gasket: Neoprene
- Steel Tube




PF39006

## Model Numbers

PF39002	2"	CI	TEST PLUG W/ WINGNUT
PF39003	3"	CI	TEST PLUG W/ WINGNUT
PF39004	4"	CI	TEST PLUG W/ WINGNUT
PF39006	6"	CI	TEST PLUG W/ WINGNUT
PF39008	8"	CI	TEST PLUG W/ WINGNUT
PF39010	10"	CI	TEST PLUG W/ WINGNUT
PF39012	12"	CI	TEST PLUG W/ WINGNUT

## Specifications

Size	A (mm)	B inches (mm)	C – Nipple Dimensions
2"	1.8"(48)	9.7"(247)	3/8" with 3/8"-18 NPT
3"	2.7"(70)	12.9"(328)	1/2" with 1/2"-14 NPT
4"	3.5"(90)	13"(332)	1/2" with 1/2"-14 NPT
6"	5.5"(140)	13"(332)	1/2" with 1/2"-14 NPT
8"	7.4"(190)	17.8"(434)	1/2" with 1/2"-14 NPT
10"	9.5"(242)	17.3"(440)	1/2" with 1/2"-14 NPT
12"	11.3"(289)	20.5"(520)	1" with 1"-11.5 NPT



## Warranty and Codes

This PROFLO product carries a 1-year limited warranty.