

CAST IRON TWO-PIECE VALVE BOXES

for 4" through 12" valves, 5 1/4 shaft, slip type


Tyler Union Valve boxes are available either assembled or as individual tops and bottoms.

NOTE: Domestic valve boxes available in Heavy Duty only. Non-Domestic available in Standard or Heavy Duty

6855 ASSEMBLED BOXES (LESS LID)

Box (Components)	Extension Height	** (D-HD) UPC 670610	** (ND-HD) UPC 670610	Weight	** (ND-Std.) UPC 670610	Weight
461-A (10T + 15B)	19-22	145844	502234	55	112099	34
462-A (10T + 24B)	27-32	145831	—	65	112105	46
562-A (16T + 24B)	27-37	145868	502241	72	112112	55
563-A (16T + 30B)	33-43	145714	—	81	112129	67
564-A (16T + 36B)	39-50	145875	502258	83	112136	72
662-A (26T + 30B)	36-52	145721	—	97	112143	83
664-A (26T + 36B)	39-60	145882	502265	99	112150	88
666-A (26T+24B+60 Ext)	53-71	145899	—	124	112167	108
668-A (26T+36B+60 Ext)	64-82	145905	—	135	112181	125

** D = Domestic ND = Import HD = Heavy Duty Weight Std. = Standard Weight




6855 Assembly
(Less Lid)

6855 INDIVIDUAL TOPS (LESS LID)

Box	Top Length	** (D-HD) UPC 670610	Weight	** (ND-HD) UPC 670610	Weight	** (ND-Std.) UPC 670610	Weight
461-A	(10T)	144960	29	502272	29	112211	15
462-A	(10T)	144960	29	502272	29	112211	15
562-A	(16T)	144977	36	502289	36	112228	25
563-A	(16T)	144977	36	502289	36	112228	25
564-A	(16T)	144977	36	502289	36	112228	25
662-A	(26T)	144984	52	502296	52	112235	38
664-A	(26T)	144984	52	502296	52	112235	38
666-A	(26T)	144984	52	502296	52	112235	38
668-A	(26T)	144984	52	502296	52	112235	38

** D = Domestic ND = Import HD = Heavy Duty Weight Std. = Standard Weight




Top

6855 INDIVIDUAL BOTTOMS

Box	Bottom Length	** (D-HD) UPC 670610	Weight	** (ND-HD) UPC 670610	Weight	** (ND-Std.) UPC 670610	Weight
461-A	(15B)	145073	26	502302	26	112051	20
462-A	(24B)	145080	36	502319	36	112068	30
562-A	(24B)	145080	36	502319	36	112068	30
563-A	(30B)	145127	45	502333	45	112075	39
564-A	(36B)	145097	47	502340	47	112082	43
662-A	(30B)	145127	45	502333	45	112075	39
664-A	(36B)	145097	47	502340	47	112082	43
666-A	(24B)	*145080	36	*502319	36	*112068	30
668-A	(36B)	*145097	47	*502240	47	*112082	43
—	(60B)	—	—	—	—	458302	75

** D=Domestic ND=Import HD=Heavy Duty Weight Std.=Standard Weight

*Note: When installing with an extension a 6850 screw type bottom is required



Bottom

See page 50 for extensions.