

# Whole House Water Filtration Housings

Housings do not come with a water filter cartridge. Drop-in cartridges are sold separately. Flow rate and reduction claims vary with drop-in water filter cartridge used.

## AP100 Series

### Standard Diameter Sump Style Systems

- May use AP124, AP110, AP1001, AP117, APS117 or AP420 drop-in cartridges in the AP100 series
- AP102T recommended for homes with 3-4 bathrooms
- 1-High cartridge height is 9.75" and 2-High cartridge height is 19.5"

1 High		1 High	2 High
			
<b>AP111T</b>		<b>AP101T</b>	<b>AP102T</b>
Pressure relief valve 8 gpm*		Valve in Head 8 gpm*	Valve in Head 16 gpm*

## AP800 Series

### Large Diameter Sump Style Systems

- May use AP810, AP811 or AP817 drop-in cartridges in the AP800 series
- AP802 recommended for homes with 3-4 bathrooms
- 1-High cartridge height is 9.75" and 2-High cartridge height is 20"

1 High		2 High
		
<b>AP801</b>		<b>AP802</b>
20 gpm**		45 gpm**

\*AP110 used to model differences in flow rate. Actual flow rate is dependent on cartridge used.

\*\*AP810 used to model differences in flow rate. Actual flow rate is dependent on cartridge used.

# Whole House Large Diameter Blue Opaque Housings and Associated Drop-in Cartridges

White Head, Blue Opaque Sump



AP800 Series Housings (Filter Not Included) and Associated Replacement Cartridges - 2 High Cartridges Used with the AP802

Model Name	Part Number	3M ID / UPC Code	Used With	Includes	Reduction Claims	Micron Rating (um)	Life (Months)	Flow Rate (gpm/lpm)	Filter Capacity (gal/lit)	Max Temp (°F/°C)	Max Pressure (psi/kPa)	Size (approx.) (in/cm)	Case Lot	Case Weight (lbs/kg)	UOM
AP801	5585701	70020007822/ 00016145607165	AP811, AP810, AP817	Mounting Bracket, Screws, Wrench	Dependent on Drop-in Filter Cartridge Used in this Housing					100/ 37.8	90/ 621	7-1/4 x 13-5/16	2	11.7/ 5.3	ea
AP802	5585704	70020002492/ 00016145802102	AP810-2, AP817-2	Mounting Bracket, Screws, Wrench	Dependent on Drop-in Filter Cartridge Used in this Housing					100/ 37.8	100/ 689	7-1/4 x 23-7/16	2	15.9/ 7.2	ea
AP811	5618904	70020170547/ 00016145165108	AP801	N/A	Sediment*	25	6	20/75.7	N/A	100/ 37.8	N/A	4.5 x 9.75	4	4.4/2	ea
AP811-2	5618905	70020176742/ 00016145171277	AP802	N/A	Sediment*	25	6	45/170.3	N/A	100/ 37.8	N/A	4.5 x 20	4	5.5/ 2.5	ea
AP810	5618902	70020164177/ 00016145158766	AP801	N/A	Sediment*	5	6	20/ 75.7	N/A	100/ 37.8	N/A	4.5 x 9.75	4	4/1.8	ea
AP810-2	5618903	70020162437/ 00016145157028	AP802	N/A	Sediment*	5	6	45/170.3	N/A	100/ 37.8	N/A	4.5 x 20	4	7.8/ 3.5	ea
AP817	5602719	70020315159/ 00054007979715	AP801	N/A	Sediment*/ CTO*	25	6	10/37.9	N/A	100/ 37.8	N/A	4.5 x 9.75	4	11.2/ 5.1	ea
AP817-2	5602721	70020315167/ 00054007979722	AP802	N/A	Sediment*/ CTO*	25	6	20/75.7	N/A	100/ 37.8	N/A	4.5 X 20	4	20.8/ 9.4	ea

AP800 Series Accessories

Model Name	Part Number	3M ID/ UPC Code	Description	Case Lot	Case Weight (lbs/kg)	UOM
AP-MB801	6890131	70020021948/00016145009570	Mounting bracket kit for the AP800 series housings	1	1.9/0.9	ea
O-RING	6889832	70020021906/00016145009532	O-ring AP800 Series Housings	1	0/0	ea
WRENCH	6890033	70020021930/00016145009563	AP800 Series Wrench	1	0.216/0.1	ea

\*As tested and verified by manufacturer's laboratory.