


MONTE CARLO

FAN COLLECTIONS

3CLYR42OZD-V1: 42" Clarity II - Oil Rubbed Bronze

Specification Images:



Collection: Clarity II

Dimmable

UPC #: 014817583113

Finish: Oil Rubbed Bronze (OZ)

Blade Finish: Roman Bronze

Dimensions:

Diameter: 42"
Weight: 14.75 lbs.
Reverse Switch: Remote Controlled
Motor Size: 153.0 X 12.0
Diameter of Housing: 8.5
Capacitor Value: 85?, 4.5+5+6uF, 350V+250V+250V
Light Kit Included: Yes
Remote Included: Wall / Hand Remote
Location of Receiver: Switch Housing
Remote Group(s):

Bulbs:

1 - LED Integrated Array 17w 120v - included

Features:

- This fan comes with a light kit.
- This advanced LED technology is carefully designed and selected to consist of the highest quality LED chipsets for superior performance and reliability.
- Integrated LED fixtures that meet the high efficacy LED standards set forth in Title 24 and are listed in the California Energy Commission Appliance database.

Material List:

Safety Listing:

Safety Listed for Dry Locations

Instruction Sheets:

English (3CLYR52_42XXD-V1-CUL-ENG)
 French (3CLYR52_42XXD-V1-CUL-CF)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Frosted Acrylic	1									

Monte Carlo reserves the right to revise the design of components of any product due to parts availability or change in safety listing standards without assuming any obligation or liability to modify any products previously manufactured and without notice. This literature depicts a product design that is the sole and exclusive property of Monte Carlo. In compliance with U.S copyright and patent requirements, notification is hereby presented in this form that this literature, or the product it depicts, is not to be copied, altered or used in any manner without the express written consent of, or contrary to the best interests of Monte Carlo.

Blade Details:

Blade Group	Diameter	Included	RPM Hi	CFM Hi	Watts Hi	Amps Hi	RPM Med	CFM Med	Watts Med	Amps Med	RPM Low	CFM Low	Watts Low	Amps Low
VN - 42"	42	Yes		2405.34	38.73									

Mounting Options:

Mounting Type	Included	Item	Downrod Length	Downrod Diameter	Overall Height	Blade to Ceiling	Min. Ceiling Height	Canopy Style	Canopy Diameter
Flush (Included)	yes				9.2	6.7	7.56		

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Frts. Class	UPS Ship
Individual	3CLYR42OZD-V1	1	014817583113	26.2	12.5	10.5	1.99	17.25	110	Yes
NJ Pallet		36		48	40	73.5	81.667	619.2		No
NV Pallet		42		48	40	78	86.667	725		No