



Shown with a custom-fabricated liner purchased locally

ENERGY STAR® rated hood for ducted applications provides optimum energy savings.

Heat Sentry™ detects excessive heat and adjusts speed to high automatically.

Charcoal filter option available for recirculation applications (Please note: Recirculation installations will not meet ENERGY STAR® requirements).

Works with optional Universal Make-Up Air Dampers. (The P195ES does not require make-up air per IRC M1503.4 requirements.)

#### Model Numbers:

P195ES52SB

P195ES70SB



Two fluorescent lights provide bright cooktop lighting.



Variable 3-speed slider switch control enables the user to choose operating preference.



Protect cabinetry from steam and grease with stainless steel liners that provide a custom fit.



### Hood Sizes

<b>Widths</b>	<b>20-1/2", 27-1/2"</b>
<b>Depth</b>	<b>11-1/4"</b>

### Finish

Stocked	Brushed Stainless Steel
Special Order	Not Available

### Features

Lighting Type	Fluorescent Bulbs 13 W, G24Q-1
Number of Lamps	2
Lighting Levels	1
Lighting Lamps Included	Yes
Control Type	3-speed Slider Switch
Control Features	Heat Sentry™
Remote Control	Not Available
Filter Type	Mesh Grease Filter
Non-ducted Capability	Yes

### Hood Blower Included (P195ES ENERGY STAR® Rated)



Internal Vertical	
ENERGY STAR® rated internal Blower CFM	
P195ES52SB Low/High CFM	120/290
P195ES70SB Low/High CFM	120/370
Sones Low/High	
P195ES52SB Low/High CFM	0.5/5.0
P195ES70SB Low/High CFM	0.3/5.0

### Accessories

Recirculation Filter	FILTEREB40 (for P195ES52SB) ROUNDFILTER (for P195ES70SB)
Liners: Optional	L5230 (for P195ES52SB) L7030 / L7036 / L7048 (for P195ES70SB)
Light Panel for Liners: Optional	ALP30, 36, 48
Universal Make-up Air Damper: Optional	MD6TU for 6" duct (for P195ES70SB) MD8TU for 8" duct (for P195ES70SB)

### Installation Requirements

Amps @ 120V	2.8
Electrical	Cord Connected
Duct Size: Internal Blower	6" (P195ES52) 8" (P195ES70)
Duct Size: External Blower	Not Available
Duct Direction	Vertical
Backdraft Damper	Included



Installation height above the cooking surface: 24"-30"

For more details see the product specifications sheet found at [www.BESTRangeHoods.com](http://www.BESTRangeHoods.com)