



EXTREME® STANDARD REPLACEMENT TIPS

A full series of manual lighting tips can be used with any Air Acetylene torch handle (PLF-A5 or G-4). Add range to your torch kit with economical tips that also feature a removable orifice screw.



A-2

Replacement Tip
Part No. 0386-0100



A-3

Replacement Tip
Part No. 0386-0101



A-5

Replacement Tip
Part No. 0386-0102



A-8

Replacement Tip
Part No. 0386-0103



A-11

Replacement Tip
Part No. 0386-0104



A-14

Replacement Tip
Part No. 0386-0105



A-32

Replacement Tip
Part No. 0386-0106



MSA-8

Replacement Tip
Part No. 0386-0365



Combo Accessory Pro Pack
Part No. 0386-0577

Includes:

- Air Acetylene Tips: A-8, A-5 and A-2 for use with Quick Disconnect Handles
- PL-812 Torch Shield 8" x 12" made with PyroSil™
- L-1 Flint Striker

AIR ACETYLENE

Replacement Tip No.	Tip Part No.	Tip Size	Soft Solders	Silver Brazes	Gas Flow		Replacement Orifice
					@14 PSI SCFH	(0.9 BAR) M3/HR	
A-2	0386-0100	1/8" (3.2 mm)	1/8" - 1/2" (3.2 - 13 mm)	1/8" - 1/4" (3.2 - 6.4 mm)	2.0	0.060	OR-A2
A-3	0386-0101	3/16" (4.8 mm)	1/4" - 1" (6.4 - 25 mm)	1/8" - 1/2" (3.2 - 13 mm)	3.6	0.108	OR-A3
A-5	0386-0102	1/4" (6.4 mm)	3/4" - 1 1/2" (19 - 38 mm)	1/4" - 3/4" (6.4 - 19 mm)	5.7	0.171	OR-A5
A-8	0386-0103	5/16" (7.9 mm)	1" - 2" (25 - 50 mm)	1/2" - 1" (25 - 50 mm)	8.3	0.249	OR-A8
A-11	0386-0104	7/16" (11 mm)	1 1/2" - 3" (38 - 76 mm)	7/8" - 1 5/8" (22 - 41 mm)	11.0	0.330	OR-A11
A-14	0386-0105	1/2" (13 mm)	2" - 3 1/2" (50 - 89 mm)	1" - 2" (25 - 50 mm)	14.5	0.435	OR-A14
A-32	0386-0106	3/4" (19 mm)	4" - 6" (102 - 152 mm)	1 1/2" - 4" (38 - 102 mm)	33.2	0.996	OR-A32
MSA-8	0386-0368	3/8" (9.5 mm)	3/4" - 3" (19 - 76 mm)	1/4" - 3/4" (6.4 - 19 mm)	5.8	0.174	OR-A5