



Size	VALVE									GEAR-OP				
	H1	H2		B	L	Ød	C	n	h	RATIO	H	G	D	ØF
		731	732											
2	2.77	5.06	4.94	1.93	1.693	2.05	4.75	4	5/8	24:1	8.74	2.83	6.85	5.79
2-1/2	2.96	5.36	5.2	2.52	1.811	2.64	5.5	4	5/8	24:1	8.74	2.83	6.85	5.79
3	3.67	5.64	6.07	3.03	1.811	3.15	6	4	5/8	24:1	8.74	2.83	6.85	5.79
4	4.18	6.41	6.54	3.82	2.047	3.94	7.5	8	5/8	24:1	8.74	2.83	6.85	5.79
5	4.69	7.34	7.13	4.8	2.205	4.92	8.5	8	3/4	24:1	8.74	2.83	6.85	5.79
6	5.48	7.98	7.84	5.83	2.205	5.93	9.5	8	3/4	24:1	8.74	2.83	6.85	5.79
8	6.51	9.34	9.26	7.62	2.362	7.74	11.75	8	3/4	30:1	10.51	3.31	11.50	11.81
10	7.86	11.13	10.5	9.65	2.677	9.72	14.25	12	7/8	30:1	10.51	3.31	11.50	11.81
12	9.47	12.27	12.15	11.54	3.071	11.63	17	12	7/8	50:1	10.51	3.31	11.50	11.81