

# Standard No-Hub Couplings



## Product Features

- PROFLO no-hub couplings are engineered to connect no-hub cast iron pipe and fittings. PROFLO no-hub products are designed to meet or exceed specifications for couplings used in all drain, waste, and vent (DWV) no-hub cast iron pipe systems.
- Temperature range: -30°F to 220°F
- Corrosion resistant

Optional accessories: RAPTOR® torque wrench RAP18552



PFNHC10

## Certifications

Coupling Meets ASTM C1277	IAPMO Listed File # 3198	NSF
Gasket Meets ASTM C564	Meets CSA B602	Buy America Act compliant

## Available Sizes

SIZE	SKU	NO. OF CLAMPS	COUPLING WIDTH	INSTALLATION TORQUE	SCREW HEX SIZE
1-1/2"	PFNHCH	2	2-1/8"	60 inch-pounds (all sizes)	5/16" (all sizes)
2"	PFNHCK				
3"	PFNHCM				
4"	PFNHCP				
5"	PFNHCS	4	3"		
6"	PFNHCU		4"		
8"	PFNHCHX				
10"	PFNHC10				
2" X 1-1/2"	PFNHRCKJ	2	2-1/8"		
3" x 2"	PFNHRCKK				
4" x 3"	PFNHRCKM				

MATERIALS	
Clamp:	All 300 Series AISI Stainless Steel (Band and Screw Housing)
Screw:	All 300 Series AISI Stainless Steel (5/16" Hex Head/Shoulder)
Shield:	All 300 Series AISI Stainless Steel
Rivets:	All 300 Series AISI Stainless Steel
Gasket:	Elastomeric Compound Primarily Consisting of Neoprene; Meets ALL Requirements of ASTM C564

## Warranty and Codes

This PROFLO product carries a 1-year limited warranty.

Distributed Exclusively by Ferguson and Wolseley Canada  
©2020 PROFLO

Made in the USA



1845615 0420