

LEAD-FREE* PERFORMANCE BRONZE® FITTINGS

APPLICATIONS

 Specifically designed for use in applications that deliver water for human consumption; this includes commercial as well as residential construction

MATERIALS & CONSTRUCTION

- NIBCO lead-free wrot copper fittings are made from commercially pure copper mill products per ASTM B 75 Alloy C12200
- NIBCO lead-free dezincification-resistant (DZR) fittings are made of high quality lead-free Performance Bronze[®] alloy per ASTM B 584 Alloy C87850 or C87600
- NIBCO lead-free forged fittings are made from C69300, an EcoBrass[®] alloy.

DESIGN CRITERIA

- Third party certified to Annex G of NSF/ANSI 61
- Manufactured in NIBCO ISO registered facilities
- * Weighted average lead content $\leq 0.25\%$







NIBCO[®] wrot copper solder fittings manufactured in Stuarts Draft, Virginia, are generally 3rd party certified to Annex G of NSF/ANSI 61[†]. For our complete offering of wrot copper fittings, please consult the NIBCO Copper Fittings catalog at www.nibco.com or visit us at www.nibcoleadfree.com.



Look for this symbol on NIBCO lead-free packaging.


[†]NSF-61-G certification pending on some items. Consult NIBCO Customer or Technical Services for more information. EcoBrass[®] is a registered trademark of Mitsubishi Shindoh Co., LTD.

Lead-Free* Performance Bronze® Fittings

С

ELBOWS


NIBC




AHEAD OF THE FLOW®

705-D-LF Lead-Free Vent Elbow w/Cap C x C

NOM. SIZE	APPROX. NET WT. LBS.	DI C	MENSIO INCHES D	
½ Ē	0.09	1/2	¹ /2	³ /4
34 E	0.15	⁹ /16	⁹ /16	²⁹ /32
1	0.31	³ /4	³ /4	1






Lead-Free 90° Elbow C x C


707-LF

NOM. SIZE	APPROX. NET WT./LBS.	DIM. C Inches	DIM. D Inches
1¼ x ¾	0.34	⁵ /8	7/8
1½ x 1	0.55	¹¹ /16	1




707-3-LF Lead-Free 90° Elbow C x F

NOM. SIZE	APPROX. NET WT./LBS.	DIM. C Inches	DIM. E Inches
1⁄4	0.06	¹³ /32	⁹ /16
³ /8	0.09	⁷ /16	¹¹ /16
1⁄2 Ē	0.12	⁷ /16	¹³ /16
1⁄2 x 1⁄4	0.10	³ /8	²³ /32
½ x ³/8	0.09	1/2	¹³ /16
½ x ¾	0.18	¹¹ /16	¹⁵ /16
34 F	0.18	²¹ /32	³¹ /32
¾ x ½ €	0.16	⁹ /16	¹⁵ /16
3⁄4 x 1	0.36	⁷ /8	1 ¹ /8
1	0.47	²⁵ /32	1 ¹ /4
1 x ½	0.32	⁹ /16	1 ¹ /8
1 x ¾	0.40	¹¹ /16	1 ³ /16
11⁄4	0.67	1	1 ¹ / ₂
11⁄2	0.90	1 ¹ /8	15/8
2	1.46	1 ³ /8	1 ¹⁵ /16




Lead-Free 90° Drop Ear Elbow C x F

NOM. Size i	APPROX. Net WT./LBS.	DIM. A Inches	DIM. C Inches	DIM. E Inches
½ Ē	0.15	¹³ /32	⁹ /16	⁷ /8
½ x ³/8	© 0.11	³ /8	¹ /2	³ /4
34 E	0.31	¹⁷ /32	²¹ /32	¹⁵ /16
¾ x ½	0.24	¹⁷ /32	⁹ /16	¹⁵ /16
1	0.49	⁵ /8	²⁵ /32	1 ¹ / ₄




707-3-5A-LF Lead-Free 90° Hy-Set Elbow C x F

NOM. SIZE	APPROX.	DIM. X	DIM. E
	Net WT./LBS.	Inches	Inches
1/2 Ē	0.16	¹ /2	7/8



707-3-6-LF Lead-Free 90° Union Elbow C x F

NOM. SIZE	APPROX. NET WT./LBS.	DIM. A Inches	DIM. E Inches
1/2	0.31	1 ¹ /8	⁷ /8
3⁄4	0.48	1 ⁷ /16	1



707-4-6-LF Lead-Free 90° Union Elbow C x M

NOM. SIZE	APPROX. Net WT./LBS.	DIM. A Inches	DIM. E Inches
³ /8	0.20	¹⁵ /16	1 ³ /16
1/2	0.30	¹⁵ /16	1 ¹ /2
3⁄4	0.49	1 ⁷ /32	1 ¹³ /16
1	0.71	1 ¹³ /32	1 ⁵ /8

(F) Forged fitting

* Weighted average lead content \leq 0.25%