

PFXT300S

**Low Lead
Sweat Gate Valves**



Product Features


- Economy brass gate valve
- Sweat ends
- Solid wedge disc
- Non-rising stem
- Pressure rating: 200 WOG
- Not steam rated
- Temperature rating: 180°F
- Low Lead Compliant
- Not for use at or below ground level

NO	PART	MATERIAL
1	Wheel Nut	Steel
2	Name Plate	Aluminum
3	Hand Wheel	Aluminum
4	Stem	No-lead Brass
5	Packing Nut	Brass
6	Gland	Brass
7	Gland Packing	NBR
8	Bonnet	No-lead Brass
9	Locking Nut	Brass
10	Disc	No-lead Brass
11	Body	No-lead Brass



PFXT300SM

Product Specifications



MODEL	SIZE		L		H		D		d	
	in	mm	in	mm	in	mm	in	mm	in	mm
PFXT300SD	1/2	12.7	1.61	41.0	2.87	73.0	2.13	54.0	0.47	12.0
PFXT300SF	3/4	19.1	2.13	54.0	2.87	73.0	2.13	54.0	0.55	14.0
PFXT300SG	1	25.4	2.48	63.0	3.27	83.0	2.13	54.0	0.75	19.0
PFXT300SH	1-1/4	31.8	2.64	67.0	3.70	94.0	2.40	61.0	0.94	24.0
PFXT300SJ	1-1/2	38.1	2.91	74.0	4.49	114.0	3.03	77.0	1.22	31.0
PFXT300SK	2	50.8	3.46	88.0	4.84	123.0	3.03	77.0	1.46	37.0
PFXT300SL	2-1/2	63.5	4.61	117.0	7.32	186.0	4.13	105.0	2.48	63.0
PFXT300SM	3	76.2	5.20	132.0	8.74	212.0	5.20	132.0	2.95	75.0

Warranty and Codes

This PROFLO product carries a 1-year limited warranty.



Compliant with
ANSI/NSF 61-G,372

Distributed Exclusively by Ferguson and Wolseley Canada