

**NIBCO**

1516 Middlebury Street
Elkhart, IN 46516-4740

Phone: 574.295.3000 • **Fax:** 800.234.0557

E-Mail: info@nibco.com • **Web site:** www.nibco.com

Material Number NL95H04, T-585-70-66 - Two-Piece Bronze Ball Valve - Stainless Steel Trim, Threaded End Connections

The NIBCO® bronze ball valve ensures ease of operation with quarter-turn (90 degrees) open to close. The full port valve is ideal for commercial and light industrial process applications that may include HVAC, hot and cold domestic water, low pressure steam, compressed air, LP gas, natural gas and aggressive water applications. Please refer to NIBCO technical data sheet, valve selection guides and catalog for engineering and installation information. Choose NIBCO® ball valves for the most

[+ more](#)



Specifications

UPC Code	039923681010
Type	Ball Valve
Connection Type	T -- Female NPT Thread (FIPT)
Valve Size	1/4
Seal Material	RPTFE (Reinforced)
Seat Material	RPTFE (Reinforced)
Stem Material	SS - Stainless Steel
Ball Material	Stainless Steel
Body Material	Bronze
Valve Operator	CS Standard Lever Handle

Description	T5857066 1/4 THRD BALL FULL PORT SS TRM
--------------------	---

eClass Classification	Bronze Ball Valves
------------------------------	--------------------

Turns/Operation	Quarter-Turn
------------------------	--------------

Weight	0.457 lb
---------------	----------