

## 2 PC FULL PORT 1000 WOG


### Features:

- 1000 WOG
- 150 PSI WSP
- Working Temp: -4°F - 392°F (-20°C- 200°C)
- Investment Cast Body
- Blow-out Proof Stem
- Stainless Steel Handle
- Locking Lever
- RTFE Seats
- Replacement Locking Handle Kits Available
- Manufactured Silicone Free



### Standards:

- Design: With Reference to ASME B16.34, MSS SP-110
- NACE MRO103 and MRO175 Approved
- End Connections: ASME B1.20.1



### Cv, Torque & Weight

Size	Cv	Torque (in-lbs)	Wt (lbs)
1/4	21.9	62	0.5
3/8	25.4	62	0.5
1/2	36.6	62	0.7
3/4	67.7	79.7	1.0
1	110.3	132.8	1.7
1-1/4	184.7	159.3	2.5
1-1/2	266.6	221.3	3.9
2	485.3	309.8	5.9

### Figure Number Matrix

FNW 260A Size	
SIZE CODE	
1/4 = B	1 = G
3/8 = C	1-1/4 = H
1/2 = D	1-1/2 = J
3/4 = F	2 = K

### Repair Kits (Order Separately)

FNW 260ARK	Size
SIZE CODE	
1/4" = B	1" = G
3/8" = C	1-1/2" = J
1/2" = D	2" = K
3/4" = F	

### Kit Codes (Order Separately)

FNW 260A Kit	Size
KIT TYPE	SIZE CODE
Locking Handle = LHK	1/4"-1/2" = BD
Repair Kit = RK	3/4" = F
	1"-1-1/4" = GH
	1-1/2"-2" = JK