
SUBMITTAL DATA SHEET


Ductile Iron Saddle with Stainless Steel Straps - 4855A



C900 PVC x AWWA/CC

MODEL	ZIZE	A	В
4855A	4 X 3/4	3/4	4.50 - 4.80
4855A	4 X 1	1	4.50 - 4.80
4855A	4 X 1 1/4	1 1/4	4.50 - 4.80
4855A	4 X 1 1/2	1 1/2	4.50 - 4.80
4855A	4 X 2	2	4.50 - 4.80
4855A	6 X 3/4	3/4	6.63 - 6.90
4855A	6 X 1	1	6.63 - 6.90
4855A	6 X 1 1/4	1 1/4	6.63 - 6.90
4855A	6 X 1 1/2	1 1/2	6.63 - 6.90
4855A	6 X 2	2	6.63 - 6.90
4855A	8 X 3/4	3/4	8.63 - 9.05
4855A	8 X 1	1	8.63 - 9.05
4855A	8 X 1 1/4	1 1/4	8.63 - 9.05
4855A	8 X 1 1/2	1 1/2	8.63 - 9.05
4855A	8 X 2	2	8.63 - 9.05
4855A	10 X 3/4	3/4	10.75 - 11.10
4855A	10 X 1	1	10.75 - 11.10
4855A	10 X I 1/4	1 1/4	10.75 - 11.10
4855A	10 X 1 1/2	1 1/2	10.75 - 11.10
4855A	10 X 2	2	10.75 - 11.10
4855A	12 X 3/4	3/4	12.75 - 13.20
4855A	12 X 1	1	12.75 - 13.20
4855A	12 X I 1/4	1 1/4	12.75 - 13.20
4855A	12 X 1 1/2	1 1/2	12.75 - 13.20
4855A	12 X 2	2	12.75 - 13.20





SUBMITTAL INFORMATION

- Manufactured in compliance with ANSI/AWWA C800 (latest revision)
- Ductile iron conforms to ASTM A536 class 65-45-12 (latest revision)
- Certified to NSF/ANSI 61
- 304L Stainless Steel strap(s) and studs. Stainless steel nuts (PTFE coated) and washers
- EPDM o-ring
- Pipe and tap size, and thread type identified on saddle
- Outlet boss with large wrench flats
- Powder coated with blue epoxy



A.Y. McDonald Mfg. CO.

P.O. Box 508

Dubuque, IA 52004-508

Toll Free: 1-800-292-2737 **Fax:** 1-800-832-9296

Hours: 7:00 a.m. - 5:00 p.m., CST

sales@aymcdonald.com www.aymcdonald.com

A.Y. McDonald considers the information on this assembly drawing correct when published. Item and option availability, including specifications, are subject to change without notice.

Submitted by: 09-14