



## Fernco QwikSeal

| Part Number | Pipe Inlet | Host Pipe Size Application   |
|-------------|------------|------------------------------|
| QS-4        | 4" SDR     | 8" diameter and larger pipe  |
| QS-4S40     | 4" SCH-40  | 8" diameter and larger pipe  |
| QS-6        | 6" SDR-35  | 10" diameter and larger pipe |
| QS-6S40     | 6" SCH-40  | 10" diameter and larger pipe |
| QS-8        | 8" SDR-35  | 15" diameter and larger pipe |

### NOTE Corrugated Applications


- QS-4 and QS-4S40: 8" to 24" pipe diameter
- QS-6 and QS-6S40: 10" to 24" pipe diameter
- QS-8: 15" to 24" pipe diameter

## Fernco Hole Saws

| Part Number | Description                          |
|-------------|--------------------------------------|
| QS-5x4HS    | 5" OD x 4" Deep Hole Saw with Arbor  |
| QS-7x4HS    | 7" OD x 4" Deep Hole Saw with Arbor  |
| QS-9x4HS    | 9" OD x 4" Deep Hole Saw with Arbor  |
| QS-SAW5S    | 5" OD x 4" Deep Hole Saw             |
| QS-SAW7S    | 7" OD x 4" Deep Hole Saw             |
| QS-SAW9S    | 9" OD x 4" Deep Hole Saw             |
| QS-ARBOR-S  | 3/8" x 6" Drill with 1/2" Arbor      |
| QS-ADAPTER  | 1 1/4" x 3/4" Coring Machine Adapter |

## Fernco Coring Bits

| Part Number | Description                            |
|-------------|----------------------------------------|
| QS-5x14CB   | 5" OD x 14" Length Abrasive Coring Bit |
| QS-7x14CB   | 7" OD x 14" Length Abrasive Coring Bit |
| QS-9x14CB   | 9" OD x 14" Length Abrasive Coring Bit |



Corrugated



Concrete



Clay



SDR-35





## Technical Data

- Meets ASTM C 923
- When tested in concrete manholes
  - Creates water-tight, compression seal up to 10 PSI
  - Withstands up to 7° of deflection
- Easy color identification - gray Sch 40 - green SDR-26 & 35
- Independent of host pipe size, type or material
- Reduced complexity, many solutions with one QwikSeal
- Less inventory and more turns

Connect service pipe to solid wall, profile, closed profile and corrugated pipe with QwikSeal

| REVISIONS |     |             |      |          |
|-----------|-----|-------------|------|----------|
| ZONE      | REV | DESCRIPTION | DATE | APPROVED |
|           |     |             |      |          |
|           |     |             |      |          |



1. GASKET MATERIAL: GREY VIRGIN RUBBER, 50 DURO SHORE A CONFORMING TO ASTM C 923
2. CLAMP:1 PIECE 750-316HT
3. LABEL: 1 PIECE, TAGQS-6S40

|                                                                       |         |                   |           |
|-----------------------------------------------------------------------|---------|-------------------|-----------|
| UNLESS OTHERWISE SPECIFIED:<br>DIMENSIONS ARE IN INCHES<br>TOLERANCES |         |                   |           |
| DECIMALS                                                              | ANGULAR |                   |           |
| .XX ± .06                                                             | ± 0.5°  | 6" QwikSeal SCH40 |           |
| .XXX ± .03                                                            |         | SIZE              | FSCM NO.  |
| DO NOT SCALE DRAWING                                                  |         | A                 | QWIK-SEAL |
| DRAWN                                                                 | DATE    | DWG NO.           |           |
| AJD                                                                   | 08Aug07 | QS-6S40           |           |
| CHECKED                                                               |         | REV               |           |
|                                                                       |         |                   |           |
| NTS                                                                   |         |                   |           |