



Google Nest Cam IQ Outdoor

Each Google Nest Cam plays a unique role within the connected home. See what makes each camera special.



Color



Dimensions

- L: 3.7 in (9.3 cm)
- W: 3.7 in (9.3 cm)
- H: 5.0 in (12.8 cm)
- Total cable length: 25 ft (7.5 m)

Weight

- 20 oz (568 g)

Power

- AC power adapter

Languages

- English (US, UK)
- Dutch
- French (Canada, France)
- German
- Italian
- Spanish (North America, Spain)

Input

- 100–240V AC, 50/60Hz, 0.65A

DC-output

- 15V DC, 1.87A

Camera input

- 5VDC 1.0A

Security

- 128-bit AES with TLS/SSL

Wireless

- 802.11 a/b/g/n (2.4GHz/5GHz) Wi-Fi; WEP, WPA, WPA2 encryption supported
- Bluetooth® low energy
- 802.15.4 (2.4GHz)
- MIMO

Operating temperature

- -40°–113°F (-40°–45°C)

Weather resistance

- IP66 rating

Audio

- High-quality speaker, 3-microphone array

Lights

- Status light and RGB light ring

Camera

- 1/2.5-inch, 8-megapixel (4K) color sensor, 12x digital zoom and enhance, close-up tracking view

Video

- Up to 1080p (1920 x 1080)
- 30 frames/sec
- H.264 encoding
- HDR

Field of view

- 130° diagonal

Night vision

- High-power 850 nm infrared LEDs

Lights

- Status light and RGB light ring

Sensors

- Ambient light

Green

- Recyclable packaging

Warranty

- 2-year limited warranty. For support, visit nest.com/support
- The Nest support team is available seven days a week

Installation options

- Open a window, route the power cord through, then close it.
- Drill through your exterior wall and plug it into an indoor outlet.
- Plug it into an outdoor outlet with the Weatherproof Power Adapter for Nest Cam IQ outdoor. (Sold separately)

Other

- RoHS compliant
- REACH compliant