MOEN[®]

There is more than 1 version of this model. Page down to identify the version you have.

PRODUCT DESCRIPTION

- · Battery powered, sensor activated, exposed water closet flushometer retrofit
- Brass construction with chrome plated finish
- Chloramine resistant seals
- 1-½" tailpiece nut assembly
- All flush valves are intended for use with compatible flush volume fixtures as specified by the fixture manufacturer. WaterSense® labeled flush valves should be used with a WaterSense® labeled fixture that has a compatible flush volume to ensure complete system performance.

OPERATION

- Self-cleaning Accuset[™] piston flush technology
- · Mechanical override
- · Adjustable infrared sensor range
- · Four (4) Alkaline AA batteries included
- Battery life: Up to 8 years*
- · Low battery indicator light
- Optional 24 hour Sentinel Flush (Factory setting is off)
- Operating Pressure Range: 20-125psi

FLOW RATE

Closet

□**8310SR35** (3.5gpf/13.2Lpf)

□8310R16 (1.6gpf/6.0Lpf)

□8310RDF16 (1.0/1.6gpf 3.8/6.0Lpf) – 1.0gpf up to 60 seconds/1.6gpf after 60 seconds

□8310SR128 (1.28gpf/4.8Lpf) – WaterSense® certified

Urinal

□8312R10 (1.0gpf/3.8Lpf)

□8312SR05 (0.5gpf/1.9Lpf) – WaterSense® certified

□8312SR125 (0.125 gpf/0.5Lpf) – **WaterSense® certified**

STOP VALVE

Adjustable installation (left or right connection)


STANDARDS


- Third party certified to meet: ASSE1037 / ASME A112.1037 / CSA125.37, ASME A112.19.2 / CSA B45.1 and all applicable requirements referenced therein
- BAA
- ADA 📞

WARRANTY

· Warranted for 5 years against material or manufacturing defects

*Typical alkaline battery life at 130 uses per day is about 8 years





CRITICAL DIMENSIONS

(DO NOT SCALE)

Specifications



M•POWER™ Battery Powered Sensor Exposed Style Retrofit Flush Valve

Models: 8310SR35, 8310R16, 8310RDF16, 8310SR128, 8312R10, 8312SR05, 8312SR125





MOEN[®]

PRODUCT DESCRIPTION

· Brass construction w/chrome plated finish

OPERATION

- · Adjustable sensor eyes
- Battery powered (4) standard AA (included)
- Average battery life 250,000 cycles
- · Self-diagnostic electronics
- · Piston flushing mechanism
- · Self cleaning filter system
- · Low battery indicator light
- All flush valves are intended for use with compatible flush volume fixtures as specified by the fixture manufacturer. WaterSense® labeled flush valves should be used with a WaterSense® labeled fixture that has a compatible flush volume to ensure complete system performance.

FLOW

Closet

□8310R16 (1.6gpf/6.0Lpf)

 \square 8310RDF16 (1.0/1.6gpf 3.8/6.0Lpf) – 1.0gpf up to 60 seconds/1.6gpf after 60 seconds Urinal

□**8312R10** (1.0gpf/3.8Lpf)


- · Operating pressures 10 to 125 psi
- 24 hour sentinel flush
- Manual override button

STANDARDS

- Third party certified by IAPMO and CSA to meet ASME A112.19.2M and all applicable requirements referenced therein and complies with requirements of ASSE 1037
- · ADA

WARRANTY

· Warranted for 5 years against material or manufacturing defects



CRITICAL DIMENSIONS

(DO NOT SCALE)

Specifications



Battery Powered Sensor Exposed Style Retrofit Flush Valve

Models: 8310R16, 8310RDF16, 8312R10