

PROFESSIONAL TOOLS RAPTOR®

POWER TOOL ACCESSORIES • HAND TOOLS EXTENSION CORDS • GLOVES • INSTALLATION SUPPLIES

Wanna' tear through stuff with the destructive force of a wild animal? Of course you do.

BAPTUR RAW

B B B B B BAAPTOR RAW WOOD, METAL & PLASTIC

HEAVY COMPOSITION

WORK LIKE A

> Beef up your tool arsenal with our new and improved Raptor RAW Premium Cutting Hole Saw & Reciprocating Saw Blades.




RAPTORTOOL.COM

Table of Contents

RAPTOR[®] offers a wide variety of professional tools and other complementary product lines for the trade. Whether you're a professional looking for a tool tough enough for the jobsite, or a home mechanic looking for a quality tool for a project, RAPTOR[®] can handle any job.

RAPTOR[®] is sold exclusively through our counters and specialized industrial waterworks and HVAC locations exclusively through WNA operating companies; Ferguson, Ferguson HVAC, Air Cold & Wolseley Canada. Our product offering encompasses a comprehensive line of tools which carry a limited lifetime warranty.







Bi-Metal Hole Saws

- Cuts through various types of steel sheets and pipes and other materials such as steel sheets, pipes, hardwood, plywood and plastics
- · Bi-metal for long life
- GSA approved

SKU	Size
RAWHS78	7/8"
RAWHS1	1"
RAWHS1316	1 3/16
RAWHS114	1 1/4
RAWHS138	1 3/8
RAWHS112	1 1/2
RAWHS134	1 3/4
RAWHS2	2"
RAWHS214	2 1/4
RAWHS212	2 1/2
RAWHS2916	2 9/16
RAWHS258	2 5/8
RAWHS234	2 3/4
RAWHS3	3"
RAWHS312	3 1/2
RAWHS4	4"
RAWHS412	4 1/2
RAWHS5	5"
RAWHS512	5 1/2
RAWHS6	6"

Hole Saw Arbors

- Fits hole saws ⁷/8" (22mm) to 1 ³/₁₆" (30mm) diameter
- · Fits most bi-metal hole saws
- 7/16" hex shank
- GSA approved
- Optional accessories: Replacement pilot drill bit: RAWPD14

SKU RAW1L



Hole Saw Arbors

- Fits hole saws 1 ¹/₄" (32mm) to 6" (152mm) diameter
- · Fits most bi-metal hole saws
- 7/16" hex shank
- GSA approved

 Optional accessories: Replacement pilot drill bit: RAWPD14

SKU RAW2L

Power Tool Accessories

Reciprocating Saw Blades

• Long lasting, high performance, bi-metal construction

It Comment Partition

- Various blades available for different needs: 10 TPI (wood, plastic and steel); 14 TPI (metal ³/₁₆" through ¹/₄"); 18 TPI (metal ¹/₈" through ³/₁₆"); 24 TPI (metal thinner than ¹/₈")
- Package Quantity: 5

SKU	Length	TPI
RAWRB610	6"	10
RAWRB614	6"	14
RAWRB618	6"	18
RAWRB624	6"	24
RAWRB814	8"	14
RAWRB818	8"	18
RAWRB910	9"	10

Reciprocating Saw Blades

- Heavy duty
- Long lasting, high performance, bi-metal construction
- Various blades available for different needs: 6 TPI (wood with nails and general roughing in); 14 TPI (metal ³/₁₆" through ¹/₄"); 18 TPI (metal ¹/₈" through ³/₁₆")

Length	TPI	Pkg Qty
6"	6	3
6"	14	5
9"	6	3
9"	14	5
9"	18	5
	6" 6" 9" 9"	6" 6 6" 14 9" 6 9" 14



Cement Tools

- Brick trowel
- 10" L x 5" W
- Slightly rounded, diamond-shaped blade
- Designed for laying brick, block, tamping and cutting bricks

SKU RAP44026

Cement Tools

- Gauging trowel
- 7" L x 3" W
- V-shaped back, rounded tip
- Designed for gauging, or mixing in specified proportions, small amounts of quick set plaster

SKU RAP44024

Cement Tools

- Margin trowel
- 5" L x 2" W
- V-shaped back, rectangular front
- Used to mix thinset and other material and scooping/spreading material such as adhesives in tight spots

SKU RAP44022

Cement Tools

- · Pointing trowel
- Smaller version of brick trowel
- Used to separate concrete from forms, finishing brick wall joints and filling small cavities

SKU RAP44020 RAP44030 Size 5 1/2" 7" x 3"

Cement Tools

- Finish trowel
- 16" L x 4" W
- Large, flat rectangular blade
- Used to smooth a surface after concrete has begun to set

SKU RAP44036

S

Cement Tools

- Magnesium masonry float
- 16" L x 3" W
- Floating helps remove imperfections and produces a flatter surface
- Compacts the slab and the mortar at the surface in preparation for later finishing operations



Cement Tools

- Concrete groover
- 6" L x 3" W
- Shaped bit and leading edge cuts proper and sharp groove
- 1/2" depth, 1/2" width with 1/4" radius





Cement Tools

- Concrete edger
- 6" L x 3" W
- 1/2" lip with 3/8" radius

SKU RAP44034



Masonry Lines

- #18 gauge braided nylon
- Used for brick and block laying, staking out sites, concrete and landscape layout

Color/Finish

Orange

Yellow

SKU	Length
RAP44040	250'
RAP44042	750'



Cleaning Tools

- 4-in-1 tool
- Cleans inside and outside of both 1/2" and 3/4" copper tube
- · Cleans pipe and fittings

SKU RAP50185



Caulk Guns

- Drip free
- Capacity: 12 oz
- Integrated plunger
- GSA approved

SKU RAP11002



Caulk Guns

- Professional grade
- · Capacity: 12 oz
- Steel frame
- Integrated plunger
- Smooth design for accurate application
- Swing out steel rod for seal puncture
- Ladder hook
- GSA approved





Hammers

- Ball Pein
- 32 oz
- Computer designed for better balance
- Slip resistant grip
- High density fiberglass handle

SKU RAP12518

Hammers

- Brick
- 16 oz
- Head Length: 7 1/4"
- Blade Size: 2" L x ⁷/₈" W
- Wood handle

SKU RAP12530



Hammers

- Dead Blow
- 3 lbs
- Will not damage wood, tile, chrome, or soft metals like steel hammers
- Non-rebounding, non-sparking, shock-absorbant
- Rugged, uni-body heavy-duty construction

SKU RAP12507



- Engineer
- 4 lbs
- · Extra large striking face
- Slip resistant grip
- High density fiberglass handle with overstrike shield

SKU RAP12509



Hammers

- Fiberglass Claw
- 16 oz
- Computer designed for better balance
- Slip resistant grip
- High density fiberglass shock absorbtion handle with hollow core

SKU RAP12501



Hammers

- HVAC Setting
- 24 oz
- Single piece forged construction
- Balanced design
- · Square beveled face
- Textured non-slip, vinyl handle
- GSA approved



Hammers

- Steel Claw
- 24 oz
- Computer designed for better balance
- Patented shock absorbing hickory plug
- Slip resistant grip

SKU RAP12504



Hex Key Sets

- 12 Piece SAE Set
- Includes Key Sizes: ¹/₁₆", ⁵/₆₄", ⁵/₃₂", ³/₁₆", ³/₃₂", ⁷/₃₂", ⁷/₆₄", ¹/₄", ¹/₈", ⁵/₁₆", ⁹/₆₄", ³/₈"
- Snap set holder for secure storage
- Durable black finish
- GSA approved

SKU RAP13002



Hex Key Sets

- 9 Piece Metric Set
- Includes Key Sizes: 1.5mm, 2mm, 2.5mm, 3mm, 4mm, 5mm, 6mm, 8mm, 10mm
- Snap set holder for secure storage
- Durable black finish
- GSA approved

SKU RAP13004



Hex Key Sets

- 9 Piece Folding Set
- Includes Key Sizes: 3/16", 1/8", 7/32", 7/64", 1/4", 3/32", 5/32", 5/64", 9/64"
- Durable black finish
- GSA approved
 - SKU RAP13003





Flame Guards

- 12" L x 16" W
- Flame and heat resistant up to 2200°F
- Asbestos free
- Smoke and odor free
- Aluminum backer can be molded around an object and helps keep guard in place

SKU RAP64010



Magnetic Nut Drivers

- Hardened steel construction
- Permanent magnet
- 1/4" hex shaft fits most drills and won't strip
- GSA approved

SKU	Size	Length
RAP75001	1/4"	1 3/4"
RAP75003	1/4"	4"
RAP75004	1/4"	6"
RAP75007	5/16"	1 3/4"
RAP75009	5/16"	4"
RAP75010	5/16"	6"
RAP75005	3/8"	1 3/4"
RAP75006	3/8"	4"



Sillcock Keys

- · Fits many sillcocks and valves
- Fits sizes 1/4", 9/32", 5/16" and 11/32"
- · Heat treated steel
- Carded

SKU RAP50105



Nut Driver Sets

- 7 Piece Set Hollow Shaft
- Includes: 3/16", 1/4", 5/16", 11/32", 3/8", 7/16" and 1/2" nut drivers
- Comfortable, color coded rubber vinyl grips
- GSA approved



Nut Driver Sets

- 3 Piece Set Magnetic Tip
- Includes: 1/4", 5/16" and 3/8" tips
- · Comfortable, rubber vinyl grip
- GSA approved

SKU RAP14560PK



Nut Drivers

- Hollow Shaft
- Comfortable, color coded rubber vinyl grips
- Type: STD
- GSA approved

SKU	Size
RAP14503	1/4"
RAP14504	5/16"
RAP14506	3/8"
RAP14507	7/16"
RAP14508	1/2"



Nut Drivers

- Magnetic Tip
- Comfortable, color coded rubber vinyl grips are easy on the hands
- GSA approved

SKU	Size	Shaft Length
RAP14550	1/4"	Stubby
RAP14551	1/4"	Standard
RAP14552	5/16"	Stubby
RAP14553	5/16"	Standard



Deburring Tools

- Precision tempered blades
- Includes extra cutting blade
- Blade storage in handle
- Optional accessories: Replacement blade: RAP50250

SKU RAP50245



Flaring Tools

- ³/₁₆", ¹/₄", ⁵/₁₆", ³/₈", ⁷/₁₆", ¹/₂", ⁵/₈" O.D. tubing
- Self-centering yoke
- Ductile iron with hardened cone
- Individually carded





Inside Pipe Cutters

- Use for closet flanges, sink waste, overflows, shower drains and sink rims
- For hard-to-reach applications
- Use with power drill
- Heat treated steel blade
- Optional accessories: Replacement blade: RAP15512

SKU RAP15510

.....

Pipe & Tubing Cutters

- Ratchet
- Heavy duty cast aluminum
- Ratchet mechanism reduces force needed to make cut
- Single hand operation
- Cuts PVC and CPVC up to 1 1/4"
- Cuts PEX ployethylene and most types of hose up to 1 1/2"
- Easily replaceable blade
- GSA approved
- Optional accessories: Replacement blade: RAP60022

SKU RAP60002



Nipple Extractors

- 3-piece set includes 3/8", 1/2", 3/4"
- · Cam type
- Provides non-slipping grip on the inside of nipples, pipes and fittings
- · Can be turned either way

SKU RAP50190



Pipe & Tubing Cutters

- Scissor
- Heavy duty cast aluminum scissor style cutter
- Single hand operation
- Cuts PVC and CPVC up to 3/4"
- Cuts PEX ployethylene and most types of hose up to 1"
- Reversible replaceable blade
- GSA approved
- Optional accessories: Replacement blade: RAP60021



Pipe Reamers

- Reams all sizes from 3/16" to 1 1/2" O.D. capacity
- Inside and outside
- Works on steel, iron, copper, PVC and ABS pipe

SKU RAP50330



Pliers

- Tongue & Groove
- Right angle teeth grip in all directions
- Self locking jaw opening adjustment
- Long, cushioned handles for extra leverage
- GSA approved

SKU	Length	Jaw Capacity
RAP18001	10"	2"
RAP18002	12"	2 1/2"
RAP18003	16"	4"



Pliers

- Water Plier
- Length: 6"
- Jaw Capacity: 1 1/4"
- Right angle teeth grip in all directions
- · Self locking jaw opening adjustment
- Long, cushioned handles for extra leverage
- GSA approved

SKU RAP18004

all's

Locking Pliers

- Length: 10"
- Jaw Capacity: 1 3/4"
- Curved jaw for increased pressure point
- Guarded release trigger
- Durable turn screw for increased pressure
- GSA approved





Side Cut Pliers

- Length: 8"
- Ideal for cutting copper, brass, iron and steel wire
- Not for use on live wires
- Forged steel
- GSA approved

SKU RAP18024



Cable Saws

- Cuts PVC, CPVC and ABS
- Stainless steel cable with heavy duty handles
- Great in tight spaces

SKU RAP15610 RAP15615 Length 24" 36"



Hacksaws

- High-tension design
- Quick-change blade
- 90° and 45° cutting angles
- Comfort grip handles front and back

SKU RAP15507

Jab Saws

• Demolition teeth cut on both push and pull strokes

0

- Sharpened tip punches through drywall easily
- · Ideal for wood, plastic or drywall
- · Comfort slip resistant handle

SKU RAP15502



Mini Hacksaws

- · Blade Length: 10"
- · Cuts wood, plaster, steel and brass
- Ideal for tight places

SKU RAP15508



Mini Hacksaws

- Cuts wood, plaster, steel, brass and other materials
- Vinyl grip handle
- · Works well in tight places
- Optional accessories: Replacement saw blade, 10 pack: RAP50320



Saws

- For cutting PVC pipe
- Aluminum handle
- Rubberized handles allow for confident handling
- Handle converts for flush cut applications
- Optional accessories: 12" replacement saw blade: RAP15521 18" replacement saw blade: RAP15516

SKU RAP15520 RAP15515 Length 12" 18"



Screwdriver Sets

- 6-piece set
- Flat Tips Included: 3/16" x 3", 3/16" x 6", 1/4" x 4", 5/16" x 6"
- Phillips Tips Included: #1 x 3", #2 x 4"
- Vinyl grip
- Durable alloy steel, precision formed tips to ensure a more secure fit
- Chrome-plated shaft for corrosion resistance
- GSA approved

SKU RAP16014



Saws

- Plumber
- Blade Length: 22"
- Aluminum handle
- Rubberized handles allow for confident handling
- 9 TPI/10 point blade made of hardened steel

SKU RAP15525

Screwdrivers

- Flat Head
- Shaft runs length of tool
- Contoured, comfort grip handle with ribs for added grasp

-

GSA approved

SKU	Length	Tip Size
RAP16001	3"	1/8"
RAP16002	4"	3/16"
RAP16004	6"	1/4"
RAP16003	8"	5/16"





Screwdrivers

- Phillips Head
- Shaft runs length of tool
- Contoured, comfort grip handle with ribs for added grasp
- GSA approved

SKU	Length	Tip Size
RAP16009	4"	#2
RAP16007	6"	#1

Screwdrivers

- 19-in-1
- Pivoting ratchet drive
- Includes: 3 flat, 3 star, 5 Phillips, 3 hex tips and 4 nut drivers

- Screw top cap with bit storage
- · Contoured comfort grip handle
- GSA approved

SKU RAP16013



Screwdrivers

- 6-in-1
- Includes: 2 flat tips, 2 Phillips tips, 1/4" and 5/16" nut drivers
- Contoured, comfort grip handle with ribs for added grasp
- GSA approved

SKU RAP16012

Undermount Sink Screwdrivers

- Sink Socket
- Extra long screwdriver
- Designed specifically for installing sinks that require clips

Robertson Head Screwdrivers

 Durable square alloy steel, precision formed tips to ensure a more secure fit

- Chrome-plated shaft for corrosion resistance
- GSA approved

SKU	Tip Size
RAP16030	#0
RAP16031	#1
RAP16032	#2
RAP16033	#3



Robertson Head Screwdrivers

- 4-piece set
- Includes: 1 each of sizes 0, 1, 2 and 3
- Durable square alloy steel tips precision formed to ensure a more secure fit
- Chrome-plated for corrosion resistance
- GSA approved

```
SKU
RAP16034
```

Snips

- Long straight
- Professional quality
- Cuts up to 18 gauge cold rolled steel
- Also cuts aluminum and vinyl siding, screening and copper wire to 10 gauge
- Serrated cutting edges prevent materials from slipping during use
- Comfort, contoured grip
- GSA approved

SKU RAP16501



Snips

- Professional guality
- Cuts up to 16 gauge cold rolled steel or 20 gauge stainless steel
- Also cuts aluminum, vinyl siding, screening and other materials
- Serrated blade design for easy cutting
- Comfort grip handle
- Solid steel

SKU RAP16504 RAP16505 RAP16506

Type Straight Right Left





Snips

- Cuts up to 16 gauge cold rolled steel or 20 gauge stainless steel
- Ideal for straight cuts, tight curves, angles and circles
- Ergonomic bowed handles
- SKU RAP16507 RAP16508

Type Offset Left Offset Right

Socket Savers

- Removes plastic pipe from plastic fittings
- The rate of cut will depend on the rpm and power of the drill along with the amount of pressure applied to the drill while reboring
- To be used with schedule 40 applications only

SKU	Size
RAP13515	1/2", 3/4" &
RAP13511	1 1/2"
RAP13512	2"
RAP13513	3"
RAP13514	4"



1"



Snips

- One-piece drop forged high carbon steel construction
- Cuts up to 20 gauge cold rolled steel or 24 gauge stainless steel
- Designed for cutting straight and wide curves to the left or right
- Cushion handle with smooth, comfortable bows for ease in use and safety
- GSA approved

SKU RAP16512

Tape Measures

- Length: 25'
- 8' tape standout
- 1" wide blade with large numbers for easy readability
- High impact rubber palm grip
- Top-forward blade lock for quick locking and unlocking
- Triple riveted hook grabs on side or top
- Bottom stopper for controlled tape recoil
- Shock-absorbing blade return bumper
- Belt-clip for quick accessibility
- GSA approved



Tape Measures

- · Length: 25'
- 8' tape standout
- 1" wide blade with large numbers for easy readability
- Stainless steel case for durability
- Top-forward blade snap lock
- Nylon coated blade
- Triple rieted end hook
- Belt-clip for quick accessibility

SKU RAP17006



Utility Knife Blades

- 10 piece set
- · Fits most standard utility knives
- Extra sharp treated blade

SKU RAP10501



Utility Knife Blades

- 100 piece set
- · Fits most standard utility knives
- · Extra sharp treated blade

SKU RAP10502



Utility Knives

- Quick change
- Easy turn dial for quick blade change
- Rubberized textured grip
- Optional accessories: Replacement blade, 10 pack: RAP10501

Replacement blade, 100 pack: RAP10502

SKU RAP10543



Tape Measures

- 9' tape standout
- 1 ¹/₄" wide blade with large numbers for easy readability
- Rubber case
- Large top-forward blade lock for quick locking and unlocking
- Shock-absorbing blade return bumper
- Belt-clip for quick accessibility
- GSA approved

SKU	
RAP17007	
RAP17004	





Utility Knives

- Steel
- Patent pending locking/folding mechanism
- Quick change blade design
- Precision machined anodized
- Aluminum handle

SKU RAP10520

Curb Stop Keys

- T-handle
- Telescoping Length: 4' 7'
- Designed to shut off ³/₄" 1" curb stops
- 5/8" round carbon steel for center stem
- 18" long T-handle
- 1/4" plate for wrench end
- SKU RAP41035



Curb Stop Keys

- T-handle
- Designed to shut off ³/₄" 1" curb stops
- 5/8" round carbon steel for center stem
- 18" long T-handle
- 1/4" plate for wrench end

SKU	Lengt
RAP41030	3'
RAP41031	4'
RAP41032	5'
RAP41033	6'
RAP41034	8'

Gate Valve Keys

- T-handle
- Rugged painted, all steel construction
- 2 1/8" ID square socket end
- Socket designed with an opening to allow soil, rock and debris to exit tool end

SKU	Lengt
RAP41023	4'
RAP41024	5'
RAP41025	6'
RAP41026	8'



Gate Valve Keys

- T-handle
- Telescoping
- Rugged painted, all steel construction
- Square socket end
- Socket designed with an opening to allow soil, rock and debris to exit tool end

SKU RAP41027 RAP41028 Length 5' - 10' 6' - 11'



Hydrant Setters

- 1,000 lb capacity
- Carbon steel tube
- · Heavy duty chain
- Fits most hydrant designs
- Spreader bars to help with stability when maneuvering and setting fire hydrants into place

SKU RAP41039



Handle Pullers

- Standard
- T-handle
- Two jaws
- Forged Steel

SKU RAP50175



Manhole Cover Hooks

- Head designed for extra leverage to pry loose conventional manhole covers
- Rocker design and pointed chisel help with the toughest lids
- Rotated handle providing firm grip

SKU	Length
RAP42014	28"
RAP42015	36"



Meter Box Lid Lifters

- Length: 36"
- Simple tool used to hook and lift the lid of a meter box
- Stainless steel construction
- Cushioned handle with attached wrist strap
- Hooked end


SKU RAP41017



Valve Setters

- 1,000 lb capacity
- One size fits 4" 12" gate to fit most gate valves
- Holds a gate valve straight and steady during installation

SKU RAP41038





Waterworks Ratchet Wrenches

- 3 piece double socket
- Case Includes 1 of Each: 7/8" x 3/4", 1 1/8" x 15/16", 1 1/4" x 11/16"
- For use on bolts, mechanical joints, hex nuts, clamps, couplings and saddles

SKU RAP41003

Valve Keys

- Length: 5'
- T-Handle Length: 18"
- Designed to operate a 2" or smaller valve with hand wheel
- 5/8" round carbon steel for center stem

Waterworks Ratchet Wrenches

- Double socket
- For tightening nuts on long bolts or all-thread rod without bottoming out
- For use on bolts, mechanical joints, hex nuts, clamps, couplings and saddles

SKU	Size	Color/Finish
RAP41007	1 ¹ /8" x 1 ⁵ /16"	Green
RAP41008	1 1/4" x 1 1/16"	Blue



Waterworks Ratchet Wrenches

- 1 1/4" x 1 1/16"
- Open box end design allows tightening without bottoming out
- For use on 5/8" and 3/4" bolts, as well as most clamps, couplings and saddles
- Fully enclosed rugged construction keeps dirt and debris from jamming gears

SKU RAP42040



Waterworks Ratchet Wrenches

- Adjustable pivot
- 1 1/4" x 1 1/16"
- Pivot handle for difficult access to nuts and bolts
- For tightening nuts on long bolts or all-thread rod without bottoming out
- For use on bolts, mechanical joints, hex nuts, clamps, couplings and saddles

SKU RAP42009



Wire Strippers

- 6-in-1
- Cuts, crimps, strips and measures
- All steel tool with shear type edge that cuts both stranded and solid copper wire
- Wire Stripper Capacity: 10-22 AWG
- Gages solid and stranded wire sizes
 SKU

RAP18541





Adjustable Wrenches

- Unique jaw design precisely grips the flat sides of fasteners, avoiding the rounding of fastener corners
- Specially designed handle reduces overall weight by 10%
- Non-protruding moveable jaw end allows easier access to fastener in tight spaces
- 18-25% wider jaw opening increases useful range of fastener sizes and gives the advantages of economy, convenience and lighter weight
- GSA approved

SKU	Length	Jaw Capacity
RAP18008	4"	5/8"
RAP18007	6"	1"
RAP18011	10"	1 1/4"
RAP18010	12"	1 1/2"
RAP18009	15"	1 7/8"



Adjustable Wrenches

- Superwide 8" wrench opens to a full 1 1/2" jaw capacity
- Unique jaw design precisely grips the flat sides of fasteners, avoiding the rounding of fastener corners
- Specially designed handle reduces overall weight by 10%
- Laser-etched SAE and metric rule on wrench head for easy fastener size identification
- Non-protruding moveable jaw end allows easier access to fastener in tight spaces
- 18-25% wider jaw opening increases useful range of fastener sizes and gives the advantages of economy, convenience and lighter weight
 - SKU RAP18006

Basin Wrenches

- T-handle
- Telescoping and adjusts from 9"–15"
- Self tightening spring loaded jaws



Basin Wrenches

- T-handle
- Length: 11"
- Self-tightening spring-loaded jaws

SKU RAP50115





- Smart Dumbell
- Universal
- Accommodates most tub drains and closet spuds
- Use adjustable wrench or screwdriver to turn the tool
- Double ended

SKU RAP50205



Disposal Wrenches

- Disposalift[®]
- Simplifies installation of most under sink disposals
- Three tabs hold disposer firmly in place
- Snap into position between disposal and locking mechanism
- Widely-spaced handles to easily lift and rotate disposal unit







Hydrant Wrenches

- Adjustable
- Fits most hydrant operating nuts
- · Forged steel handle
- Textured end to provide surface for gripping
- Nut is cast component, deburred for smooth seating
- For use on pentagon nuts and pumper or steamer caps

Nut Wrenches

- Adjustable thumb screw wrench
- Locking wing nut
- Wide mouth jaw opening, 7/8" to 3"
- Malleable iron, bright finish

SKU RAP50125





Handle Pullers

- Two large jaws fit under handle
- Deluxe model that removes even the most stubborn handles
- Extra wide opening

SKU RAP50210

RAPTORTOOL.COM



)ing Wronobac

Pipe Wrenches

- Forged and heat-treated, high-grade cast iron
- Guaranteed to withstand jobsite
 abuse
- Scale marked on hook
- Adjusting nut spins easily

SKU
RAP11214
RAP11218
RAP11224

Length 14" 18" 24"

Pipe Wrenches

- Length: 14"
- Aluminum
- Scale marked on hook
- Adjusting nut spins easily

SKU RAP11514



Pipe Wrenches

- Aluminum
- Guaranteed to withstand jobsite abuse
- Scale marked on hook
- · Adjusting nut spins easily

SKU	Length
RAP11414	14"
RAP11418	18"
RAP11424	24"





Plug Wrenches

- Necessary for tub/drain installation with pop-up drain plugs
- Ensures proper tightness without ruining the finish of the strainer

SKU RAP50220

Seat Wrenches

- Straight and tapered
- Universal fit
- Hardened Steel

SKU **RAP50505**

Seat Wrenches

- Angled and tapered
- Universal fit
- Hardened Steel

SKU RAP50150

Spud Wrenches

- · Length: 9"
- 4-in-1 design works on many closet spuds, urinal spuds, kitchen basket strainers, urinal flush valves and more
- Compact design



Strainer Wrenches

- Double ended design fits most tub drains
- Install and remove bath tub drains with or without cross bars
- Use adjustable wrench or screwdriver to turn the tool

SKU RAP50215



Torque Wrenches

- · For standard duty no-hub couplings
- Measures torque on no-hub couplings to 60 in-lbs
- Ratchets when correct torque is achieved

SKU RAP50145





Strap Wrenches

- Length: 12"
- Provides gripping power without scratching or deforming plastic and polished metal pipe
- Use on plastic pipe, filters, or any slick or smooth surface
- Woven nylon, polyurethane-coated strap
- Material: Aluminum

SKU RAP11312

Torque Wrenches

- No-hub
- T-handle style tools color coded to match the correct no-hub coupling
- Torque setting designed to slip when coupling nut has reached proper setting
- Locking collar lets user tighten nut to specified torque setting in one direction or use as non-torqueing tool in both directions
- GSA approved

		Maximum	
SKU	Size	Torque	Color/Finish
RAP18550	5/16"	60 in-lbs	Black
RAP18551	5/16"	80 in-lbs	Yellow
RAP18552	3/8"	80 in-lbs	Green





- Heavy duty
- All weather
- 12/3 gauge
- Yellow
- Water resistant and flame retardant jacket will not absorb water that can corrode copper conductors or cause dangerous electrical shocks
- Superior flexibility and resists cracking in temperatures down to -40°F and up to 140°F (-40°C up to 60°C)
- Power indicator light allows user to see when the power is on
- Meets OSHA requirements for extension cords and adapters for use on jobsites
- UL/cUL tested to both U.S. and Canadian standards

SKU	Cord Length
RAP31203	25'
RAP31202	50'
RAP31201	100'



Extension Cords

- Extreme weather
- 12/3 gauge
- Blue/Orange
- SJEOW Heavy duty outdoor extension cord
- Oil resistant, water resistant, and flame retardant
- Superior flexibility and resists cracking to -58°F (-50°C)
- Meets OSHA requirements for extension cords and adapters for use on jobsites
- UL/cUL tested to both U.S. and Canadian standards

SKU	Cord Length
RAP31206	50'
RAP31207	100'



Extension Cords

- Medium duty
- All weather
- 14/3 gauge
- Blue/Yellow
- Water resistant and flame retardant jacket will not absorb water that can corrode copper conductors or cause dangerous electrical shocks
- Superior flexibility and resists cracking in temperatures down to -40°F and up to 140°F (-40°C up to 60°C)
- Power indicator light allows user to see when the power is on
- Meets OSHA requirements for extension cords and adapters for use on jobsites
- UL/cUL tested to both U.S. and Canadian standards

SKU	Cord Length
RAP31402	50'
RAP31401	100'



Extension Cords

- Medium duty
- All weather
- 16/3 gauge
- Orange
- Water resistant and flame retardant will not absorb water that can corrode copper conductors or cause dangerous electrical shocks
- Superior flexibility and resists cracking in temperatures down to -40°F and up to 140°F (-40°C up to 60°C)
- Power indicator light allows user to see when the power is on
- Meets OSHA requirements for extension cords and adapters for use on jobsites
- UL/cUL tested to both U.S. and Canadian standards

SKU	Cord Lengt
RAP31602	25'
RAP31601	50'





- Twist-Lock
- Cord Length: 100'
- 12/3 gauge
- Oil resistant, water resistant and flame retardant
- Superior flexibility and resists cracking in temperatures down to -40°F (-40°C)
- Meets OSHA requirements for extension cords and adapters for use on jobsites
- UL/cUL tested to both U.S. and Canadian standards

SKU RAP41201



Power Block Adapters

- Triple Tap
- · Cord Length: 2'
- 12/3 gauge
- Triple tap U-ground power block
- Water resistant, oil resistant, and flame retardant
- Superior flexibility at sub-freezing temperatures
- Meets OSHA requirements for extension cords and adapters for use on jobsites
- UL/cUL tested to both U.S. and Canadian standards

SKU RAP31204



Power Supply Cords

- 16/3-wire grounded cord
- Tinned and stripped ends for easier connection
- For RAP33003 and RAP33002, accessories include 3 wire nuts and Romex connector
- UL/cUL tested to both U.S. and Canadian standards

SKU	Cord Length	Plug
RAP33003	3'	Angle
RAP33001	6'	Angle
RAP33002	6'	Straight



Ground Fault Current Interrupters

- Cord Length: 3' in-line
- 12/3 gauge
- Water resistant and flame retardant jacket on cord
- Working temperature range is -31°F to +140°F
- Converts one outlet into additional GFCI protected outlets
- Power indicator light allows user to see when the power is on
- Meets OSHA requirements for ground fault circuit interrupters for use on jobsites
- UL/cUL tested to both U.S. and Canadian standards

SKU RAP32001



Utility Worklights

- 16/3 gauge
- Working temperature range is -31°F to +140°F
- Utilizes standard 75W bulbs
- Anodized aluminum reflector
- Metal hook for hands-free applications
- · Ergonomic handle is easy to hold
- On/Off switch and convenience outlet in handle
- UL/cUL tested to both U.S. and Canadian standards

SKU	Cord Length
RAP30501	25'
RAP30502	50'









Cut Resistant Gloves

- Seamless knit Kevlar® shell protects against abrasion and cuts
- Cut resistant rubber palm
- EN Cut Level 4, ANSI Cut Level 2 Protection

SKU	
PSG12152	
PSG12153	
PSG12154	



Driver Gloves

- Driver made in Gunn pattern with straight thumb
- C Grade cow grain leather with shirred elastic back

SKU	Size
PSG20152	М
PSG20153	L
PSG20154	XL



Cut Resistant Gloves

- · High performance synthetic
- Technical synthetic performance fabric protects against abrasions and cuts
- High performance polyethylene
- EN Cut Level 3, ANSI Cut Level 2 Protection

SKU	Size
PSG12251	S
PSG12252	М
PSG12253	L
PSG12254	XL





Jersey Gloves

• 100% cotton

Size: LargeColor/Finish: Brown

PSG16323

PSG16383PK

SKU



Pkg Qty

1 Pair

12 Pack

¥

Nitrile Coated Gloves

• 100% nitrile foam coating

SKU	Size
PSG14451	S
PSG14452	М
PSG14453	L
PSG14454	XL



Knit Gloves

- Industrial grade
- Seamless
- Textured latex palm for superior grip and chemical resistance
- Cotton/poly blend

SKU	Size
PSG17552	М
PSG17553	L
PSG17554	XL







PVC Gloves

- · Gauntlet style
- Extra Long Length: 14"
- Provides basic protection from oils, greases, acids and petrochemicals
- One size fits all
- PVC

SKU PSG18156



Work Gloves

- 2 1/2" rubberized cuff
- Cow leather palms, fingertips and knuckle with cotton back
- Cotton/poly blend lining

SKU	Size
PSG20452	М
PSG20453	L
PSG20454	XL







Mechanics Gloves

- · General duty
- One-piece palm of flexible synthetic suede
- Durable synthetic suede base layer does not shrink, stretch or harden
- Slip fit cuff with pull tab
- ID tag for jobsite recognition
- Internal knuckle padding

SKU	Siz
RAP90101	M
RAP90102	L
RAP90103	XL



Mechanics Gloves

- Utility Plus
- All-purpose and abrasion-resistant
- Form-fit, washable and durable
- Neoprene cuff with gusset and Velcro closure adds wrist support, locks out cold, dirt and debris
- Neoprene knuckle padding
- Reinforced synthetic suede fingertips
- Terry cloth thumb to wipe away sweat and debris
- Non-slip palm and finger reinforcement provides extra grip

SKU	Size
RAP90201	М
RAP90202	L
RAP90203	XL







100% Silicone Caulk

- Excellent adhesion with lasting flexibility
- Interior/exterior
- · Cured sealant is mildew resistant
- VOC CARB non-chem curing (n.a) < 3.0%
- Size: 10.1 oz

SKU PFC500ALU PFC500CLR PFC500WHT Color/Finish Aluminum Clear White

Latex Tub & Tile Caulk

- Fast curing, durable, mildew resistant
- Can also be used for kitchen and bath applications
- VOC CARB non-chem curing (n.a) < 1.5%
- Color/Finish: White

SKU PFC301WHT PFC300WHT Size 5.5 oz 10.1 oz



Acrylic Latex Caulk

- · For interior/exterior use
- 15-year life expectancy
- Paintable with latex or oil based paints
- · Soap and water clean up
- Cured sealant is mildew resistant
- Do not use for structural repairs
- Do not use below grade or underwater
- VOC CARB non-chem curing (n.a) < 1.5%
- Size: 10.1 oz
- Color/Finish: White

SKU PFC100WHT

RTV High Temperature Silicone Caulk

- Single component room temperature cure
- Continuous Operating Temperature Range: 75°F to 500°F (-60°C to 260°C)
- Excellent electrical insulation properties
- Excellent resistance to weather, ozone, UV and chemicals
- VOC CARB non-chem curing (n.a) < 3.0%
- Size: 10.1 oz
- Color/Finish: Red

SKU PFC700RED





Siliconized Acrylic Caulk

- Non-flammable
- Neutral odor
- UV stabilized to guard against premature yellowing
- Can be painted over if desired
- Soap and water clean up
- Goes on white, dries to translucent clear in approximately 10 to 14 days
- VOC CARB non-chem curing (n.a) < 1.5%
- Size: 10.1 oz

SKU PFC600CLR

Siliconized Acrylic Latex Caulk

- · For interior/exterior use
- 35-year life expectancy
- Paintable with latex or oil based paints
- Soap and water clean up
- VOC CARB non-chem curing (n.a) < 1.5%
- Size: 10.1 oz
- Color/Finish: White

SKU PFC200WHT



Siliconized Acrylic Caulk

- · For kitchen/bath use
- · Dries bright white
- · Cured caulk is mildew resistant
- Soap and water clean up
- VOC CARB non-chem curing (n.a) < 1.5%
- Size: 5.5 oz

SKU PFC401ALM PFC401BIS PFC401CLR PFC401WHT Color/Finish Almond Biscuit Clear White







Hydraulic Cements

- For repair in masonry surfaces including ruptured concrete water pipes
- Compounded to withstand continual exposure to water even under pressure
- Sets rapidly for emergency repairs with minimal downtime
- · For industrial, commercial and residential applications above or below grade

 Repairs leaks in sewer pipes, basements & manholes

SKU
PSHYD1GALREG
PSHYD5GALFAS
PSHYD5GALREG

Container	
Size	٦
1 gal	F
5 gal	F
5 gal	F

vpe Regular Set ast Set Regular Set



Pipe Joint Lubricants

- All purpose, biodegradable pipe lubricant
- Can be used to assemble pipes made of cast iron, concrete, plastic and clay pipe
- Can be applied in temperatures from -10°F to 150°F
- Contains no petroleum, phosphate or silicone and will not support bacteria growth
- Water dispersible and can be washed or rinsed from surfaces easily
- Less odor
- Minimal to no separation
- Clings well to almost any surface
- SKU PSLUBXL1Q PSLUBXL1G PSLUBXL5G

Container Size 1 gt or 2 lbs 1 gal or 8 lbs 5 gal or 40 lbs



Patching Cements

- Ready to use in approximately 60 mins, fast initial setting (9-11 mins)
- Each bag covers approximately 10 square feet at 1/2" depth
- Size: 50 lbs

SKU PSPC50LB



Fender Washers

- Low carbon steel
- Sold in packs only
- Color/Finish: Zinc Plated

SKU	Size	Pkg Qty
PS000824	1/4" x 1"	50
PS000825	1/4" x 1 1/4"	50
PS000826	3/8" x 1 1/4"	50
PS000827	3/8" x 1 1/2"	50
PS000828	³ /8" x 2"	25
PS000829	1/2" x 1 1/2"	25
PS000830	1/2" x 2"	25



Anchor Kits

 Use to anchor concrete, block, stucco, wood, stone, drywall and more

SKU	Size
PSAK10H	#10 x 1 1/4"
PSAK14J	#14 x 1 1/2"

Flat Washers

- Low carbon steel
- · Sold in packs only
- Color/Finish: Zinc Plated

SKU	Size	Pkg Qty
PS000854	1/4"	100
PS000855	5/16"	100
PS000856	3/8"	100
PS000857	1/2"	25
PS000858	5/8"	25
PS000859	3/4"	12
PS000860	7/8"	12
PS000861	1"	12





Heavy Hex Nuts

- Grade 2
- Low carbon steel
- Sold in packs only
- Color/Finish: Zinc Plated

SKU	Size	Pkg Qty
PS000335	1/4"- 20	100
PS000336	5/16"- 18	100
PS000337	3/8"- 16	50
PS000338	1/2"- 13	25
PS000326	5/8"- 11	12
PS000339	5/8"- 11	12
PS000340	3/4"-10	4
PS000328	7/8"- 9	4
PS000341	7/8"- 9	4
PS000342	1"- 8	4
PS000343	1 1/8"- 7	2
PS000344	1 1/4"- 7	2
PS000345	1 1/2"- 6	2



Heavy Hex Nuts

- Grade 2
- Low carbon steel
- Sold in packs only
- Color/Finish: Plain

SKU	Size	Pkg Qty
PS000324	3/8"-16	50
PS000325	1/2"-13	25
PS000327	3/4"-10	4
PS000329	1"- 8	4
PS000326	5/8"- 11	12
PS000328	7/8"- 9	4



Hex Head Cap Screws

- Grade 2
- Color/Finish: Zinc Plated

00101/1111		
SKU	Size	Pkg Qt
PS000412	¹ /4"- 20 x 1"	50
PS000414	1/4"- 20 x 1 1/2"	50
PS000427	⁵ /16"- 18 x 1"	100
PS000431	⁵ / ₁₆ "- 18 x 2"	100
PS000439	3/8"- 16 x 3/4"	25
PS000440	³ /8"- 16 x 1"	25
PS000441	3/8"- 16 x 1 1/4"	25
PS000442	3/8"- 16 x 1 1/2"	25
PS000443	³ /8"- 16 x 1 ³ /4"	25
PS000446	3/8"- 16 x 2 1/2"	25
PS000448	³ /8"- 16 x 3"	25
PS000453	1/2"- 13 x 3/4"	10
PS000454	¹ /2"- 13 x 1"	10
PS000456	1/2"- 13 x 1 1/2"	10
PS000461	¹ /2"- 13 x 2 ³ /4"	10
PS000462	1/2"- 13 x 3"	10
PS000470	5/8"- 11 x 1 1/4"	8
PS000471	5/8"- 11 x 1 1/2"	8
PS000472	⁵ /8"- 11 x 1 ³ /4"	8
PS000473	⁵ /8"- 11 x 2"	8
PS000474	5/8"- 11 x 2 1/4"	8
PS000475	5/8"- 11 x 2 1/2"	4
PS000476	5/8"- 11 x 2 3/4"	8
PS000477	⁵ /8"- 11 x 3"	4
PS000478	5/8"- 11 x 3 1/2"	4
PS000479	⁵ /8"- 11 x 4"	4
PS000484	3/4"- 10 x 1 3/4"	4
PS000485	³ /4"- 10 x 2"	4
PS000486	3/4"- 10 x 2 1/4"	4
PS000487	3/4"- 10 x 2 1/2"	4
PS000488	3/4"- 10 x 2 3/4"	4
PS000489	³ /4"- 10 x 3"	4
PS000490	3/4"- 10 x 3 1/2"	2
PS000491	3/4"- 10 x 4"	2
PS000492	3/4"- 10 x 4 1/2"	2
PS000494	⁷ /8"- 9 x 2 1/2"	2
PS000496	⁷ /8"- 9 x 3 ¹ /2"	2
PS000497	⁷ /8"- 9 x 4"	2
PS000498	⁷ /8"- 9 x 4 ¹ /2"	2
PS000503	1"- 8 x 3"	2
PS000504	1"- 8 x 3 1/2"	2
PS000505	1"- 8 x 4"	2
PS000506	1"- 8 x 4 1/2"	2





Hex Nuts

- Grade 2
- Low carbon steel
- Sold in packs only
- Color/Finish: Zinc Plated

SKU	Size	Pkg Qt
PS000312	1/4"- 20	100
PS000313	⁵ /16"- 18	100
PS000314	³ /8"- 16	100
PS000315	1/2"- 13	25
PS000316	5/8"- 11	10
PS000317	3/4"- 10	10
PS000318	7/8"- 9	4
PS000319	1"- 8	4



Toggle Bolts

• Package Quantity: 10

Size
1/4"- 20 x 3"
1/4"- 20 x 4"
1/4"- 20 x 6"
³ /8"- 16 x 3"
³ /8"- 16 x 4"
³ /8"- 16 x 6"



- Zinc plated
- Carbon steel
- Countersunk head
- Use with Phillips #3
- Package Quantity: 50

SKU	Size
PS000909	12 -11 x 1 1/2"
PS000910	12 -11 x 2"
PS000911	12 -11 x 2 1/2"
PS000913	14 -10 x 1 1/2"
PS000915	14 -10 x 2"
PS000916	14 -10 x 2 1/2"
PS000918	14 -10 x 3"

0

Flat Washers

- Size: 3/4"
- Low carbon steel
- Sold in packs only
- Color/Finish: Plain
- Package Quantity: 12

SKU PS000814

Rod Couplings

Color/Finish: Zinc Plated

SKU	Size	Pkg Qty
PS000202	1/4"	12
PS000203	3/8"	12
PS000204	1/2"	12
PS000205	5/8"	4
PS000206	3/4"	4



Stove Bolts

Package Quantity: 25

Size
1/4"- 20 x 3/4"
1/4"- 20 x 1"
1/4"- 20 x 1 1/4"





Acid Brushes

- 3/8"
- For use on flux, pastes and other chemicals
- Hollow tin handle
- 100% horse hair bristle

SKU PS10001



Fitting Brushes

- T-Handle
- Tempered high carbon kinked steel bristles
- · Galvanized 2-ply wire stem

SKU	Size
PS0654	3"
PS0655	4"



Fitting Brushes

- 2-ply wire loop handle
- Tempered high carbon kinked steel bristles
- Galvanized 2-ply wire stem

SKU	Size	Pkg Qty
PS546	1/2"	1
PS546BP	1/2"	100
PS548	3/4"	1
PS548BP	3/4"	100
PS549	1"	1
PS550	1 1/4"	1
PS551	1 1/2"	1
PS552	2"	1

Chip Brushes

- Wood handle chip brush
- Natural bristle

SKU	Size
PS67191	1/2"
PS67192	1"
PS67193	1 1/2"
PS67194	2"
PS67195	2 1/2"
PS67196	3"
PS67198	4"





Fitting Brushes

- Hex shaft
- Tempered high carbon kinked steel bristles

Size 1/2" 3/4"

Galvanized 2-ply wire stem

SKU	
PS9546	
PS9548	

Fitting Brushes
Concave surface plastic handle
Tempered high carbon kinked steel

- bristles
- Galvanized 2-ply wire stem

SKU	Size
PS0644	1/4"
PS0645	3/8"
PS0646	1/2"
PS0648	3/4"
PS0649	1"
PS0650	1 1/4"
PS0651	1 1/2"
PS0652	2"
PS0653	2 1/2"



Fitting Brushes

- Heavy duty
- Flat surface plastic handle is easy to hold
- Tempered high carbon straight steel bristles
- Galvanized 4-ply wire stem

SKU	Size
PSHDFBD	1/2"
PSHDFBF	3/4"
PSHDFBG	1"
PSHDFBH	1 1/4
PSHDFBJ	1 1/2
PSHDFBK	2"

Round Cotton Swabs

- 1" x 6"
- · Heavy duty wire handle

in the local

100% cotton

SKU PSCPLS



Pipe Dope Brushes

- 3/4"
- For use on flux or other pastes
- Round tapered wooden handle
- 100% horse hair bristle

SKU PS10007







DWV Hangers

- Vinyl coated
- Galvanized steel construction

SKU	
PF220J	
PF220K	
PF220M	
PF220P	

Si	ze
1	1/2'
2	
3	
4	



Hanger Straps

Galvanized steel construction

SKU	Length	Gauge
PF100G20F10	10'	20
PFPT22010	10'	22
PF100G24F10	10'	24
PFPT26010	10'	26
PF101G28F10	10'	28
PF100G24F50	50'	24
PF101G28F50	50'	28
PF100G24F100	100'	24
PF101G28F100	100'	28



Hanger Straps

- Length: 50'
- 22 gauge
- Copper clad construction

SKU PF100C22F50



Hanger Straps

- 24 gauge
- Steel construction

Length
10'
50'
100'





J-Hooks

 12 gauge 		
SKU PF12CCJNPL	Size 3/8" IPS/ 1/2" CTS	Material Plastic Coated Copper
PF12CCJN	1/2"	Copper Plated
PF12GAJN	1/2"	Galvanized
PF34CCJNPL	1/2" IPS/ 3/4" CTS	Plastic Coated Copper
PF540	^{1/2} " & ^{3/4} " CTS	Copper
PF1CCJNPL	^{3/4"} IPS/ 1" CTS	Plastic Coated Copper



J-Hooks

- For use on SCH 40 pipe
- Nail holes on all four sides for attachment at various angles and pipe runs
- Maximum Safe Load: 50 lbs
- Maximum Temperature Rating: 240°F
- Nails included
- ABS construction
- Color/Finish: White

SKU	Size
PF33845	1 1/2"
PF33846	2"
PF33847	3"
PF33848	4"







Insulated Pipe Clamps

- Provides fast and easy installation and support for all types of copper tube size piping
- Impact resistant to 0°F
- Maximum Temperature: 180°F
- Eliminates contact between the pipe and framing surface
- Insulates against sound
- Can be used with hydronic heating systems

Size 1/2" 3/4" **1**"

Flexible low density polyethylene

SKU	
PF34256	
PF34257	
PF34258	



Pipe Clamps

- · Half clamp including barb nail
- Provides fast and easy installation and support for all types of copper tube size piping
- Eliminates contact between the pipe and framing surface
- Insulates against sound
- Can be used with hydronic heating systems
- High impact polypropylene

SKU	Size
PF34240	1/2"
PF34241	3/4"
PF34242	1"



Pipe Clamps

- · Full clamp including barb nail
- Provides fast and easy installation and support for all types of copper tube size piping
- Eliminates contact between the pipe and framing surface
- Insulates against sound
- Can be used with hydronic heating systems
- High impact polypropylene

SKU	Size
PF34243	1/2"
PF34244	3/4"
PF34245	1"





Pipe Clamps

- Suspension style
- Provides fast and easy installation and support for all types of copper tube size piping
- Can be used as an insulator when running water distribution lines through wooden framing
- · Can be used with hydronic heating systems

ize

Polypropylene construction

SKU	S
PF34250	1
PF34251	3
PF34252	1
PF34260	1
PF34261	1
PF34262	2



- **Pipe Clamps**
- Standard
- · Provides fast and easy installation and support for all types of piping
- · Permits quick pipe cooling and reduces water noise
- Design allows piping to be flush mounted to the wall and joists
- · Can be used with hydronic heating systems

- Copper tube size
- Polypropylene construction

SKU	Size
PF34253	1/2" CTS
PF34254	3/4" CTS
PF34255	1" CTS
PF34263	1 1/4" CTS
PF34264	1 1/2" CTS
PF34265	2" CTS



Pipe Clamps

- · Quick, one hand installation
- Snaps shut
- Pre-loaded nail
- Ribbed for low noise
- Copper safe copolymer

SKU	Size
PF513D	1/2
PF513F	3/4







Pipe Straps

- Two hole design
- Copper clad steel construction

SKU	Size
PFCTSA	1/8" CTS
PFCTSB	1/4" CTS
PF500B	1/4" IPS
PFCTSC	3/8" CTS
PF500C	3/8" IPS
PFCTSD	1/2" CTS
PF500D	1/2" IPS
PFCTSF	3/4" CTS
PF500F	3/4" IPS
PFCTSG	1" CTS
PF500G	1" IPS
PFCTSH	1 1/4" CTS
PF500H	1 1/4" IPS
PFCTSJ	1 1/2" CTS
PF500J	1 1/2" IPS
PFCTSK	2" CTS
PF500K	2" IPS



Pipe Straps

- One hole design
- Iron pipe size
- Galvanized steel construction

SKU	Size
PF610C	3/8" IPS
PF610D	1/2" IPS
PF610F	3/4" IPS
PF610G	1" IPS
PF610H	1 1/4" IPS
PF610J	1 1/2" IPS
PF610K	2" IPS



Plate Straps

Steel construction

		Holes	
SKU	Size	(Ea. End)	Gauge
PFPS0916	1 ¹ /2" x 9"	4	16
PFPS09126	1 ¹ / ₂ " x 9"	6	12
PFPS169	1 ¹ /2" x 9"	6	16
PFPS12164	1 ¹ /2" x 12"	4	16
PFPS12126	1 1/2" x 12"	6	12
PFPS12166	1 1/2" x 12"	6	16
PFPS18126	1 ¹ /2" x 18"	6	12
PFPS18166	1 1/2" x 18"	6	16
PFPS2416	1 ¹ /2" x 24"	4	16
PFPS24126	1 1/2" x 24"	6	12
PFPS24166	1 1/2" x 24"	6	16

Pipe Straps

- Two hole design
- Iron pipe size
- Galvanized steel construction

SKU	Size
PF600C	3/8" IPS
PF600D	1/2" IPS
PF600F	3/4" IPS
PF600G	1" IPS
PF600H	1 1/4" IPS
PF600J	1 1/2" IPS
PF600K	2" IPS
PF600L	2 1/2" IPS
PF600M	3" IPS
PF600N	3 1/2" IPS
PF600P	4" IPS
PF600U	6" IPS





Safety Plates

· Steel self-nailing safety plates

SKU	Size	Gauge
PFSP316100	1 1/2" x 3"	16
PF530JM	1 1/2" x 3"	18
PFSP416100	1 1/2" x 4"	16
PF530JS	1 1/2" x 5"	18
PF531JS	1 1/2" x 5"	20
PF530JU	1 1/2" x 6"	18
PF531JU	1 1/2" x 6"	20
PF532JU	1 1/2" x 6"	22
PF531JX	1 1/2" x 8"	20
PFSP5161002	2" x 5"	16
PFSP5161003	3" x 5"	16



Wire Pipe Hooks

Iron pipe size

SKU	Size	Gauge	Material
PF200SDU10	¹ / ₂ " x 6" IPS	10	Steel
PF200PSDU12	1/2" x 6" IPS	12	PVC
			Coated Steel
PF200PSFP10	3/4" x 4" IPS	10	PVC
			Coated Steel
PF200SFP10	3/4" x 4" IPS	10	Steel
PF200PSFU10	3/4" x 6" IPS	10	PVC
			Coated Steel
PF200SFU10	3/4" x 6" IPS	10	Steel
PF200PSFU12	3/4" x 6" IPS	12	PVC
			Coated
			Steel
PF200SGU10	1" x 6" IPS	10	Steel
PF200PSGU10	1" x 6" IPS	10	Steel
PF200SGX10	1" x 8" IPS	10	Steel



Stud Shoes

٠	Not	for	load	bearing	wall
---	-----	-----	------	---------	------

SKU	
PF5331	
PF5332	
PF5333	

Type Single Double Triple



Wire Pipe Hooks

- 10 gauge
- Copper tube size
- Copper Plated

 SKU
 Size

 PF200CDP10
 1/2" x 4" CTS

 PF200CDU10
 1/2" x 6" CTS

 PF200CFP10
 3/4" x 4" CTS

 PF200CFU10
 3/4" x 6" CTS

 PF200CGU10
 1" x 6" CTS







Cable Ties

- High tensile strength
- Manufactured from type 6/6 nylon
- UL 181 B-C approved on 36" and 48" ties for HVAC industry

Size	Pkg Qty	Color/Finish
7 1/2"	100	Black
7 1/2"	1,000	Black
11"	100	Black
14 1/2"	100	Black
24"	50	Black
36"	50	Black
36"	50	Natural
48"	50	Black
401	50	Natural
	7 1/2" 7 1/2" 11" 14 1/2" 24" 36" 36"	$\begin{array}{cccc} 7 & 1/2" & 100 \\ 7 & 1/2" & 1,000 \\ 11" & 100 \\ 14 & 1/2" & 100 \\ 24" & 50 \\ 36" & 50 \\ 36" & 50 \\ 48" & 50 \end{array}$



Duct Tapes

- 2" x 60 yds
- · Tears evenly and shreds minimally
- Adheres well to irregular surfaces
- Won't twist or curl during application
- Made from high quality polyester (PET) cloth, polyethylene (PE) film, and a natural rubber, pressure sensitive adhesive
- Tested in accordance with UL-723, HUD and BOCA rated

SKU
PSDTC260B
PSDTC260S
PSDTU260S

Grade Premium Premium Utility Color/Finish Black Silver Silver



Pipe Wraps

- Non-corrosive, pressure-sensitive adhesive tape
- For use above or below ground as a rust preventer and UV inhibitor
- Approved for use on all types of pipe including gas and oil pipe
- Moisture resistant
- UPC Certified

SKU	Size	Thickness	Color/Finish
PSPWT110	1" x 100'	10 mil	Black
PSPWT210	2" x 100'	10 mil	Black
PSPWT210Y	2" x 100'	10 mil	Yellow
PSPWT220	2" x 100'	20 mil	Black
PSPWT410	4" x 100'	10 mil	Black
PSPWT410Y	4" x 100'	10 mil	Yellow





PTFE Pipe Thread Tapes

- High density
- 1.2 g/cm³ density
- Can be used on all types of threaded fittings for passage of potable and non-potable water, most chemicals, oxygen, liquid and natural gas, hydraulic lines, and high-pressure lines not exceeding 1 1/2" in diameter
- 100% PTFE
- Color/Finish: White

Size
260" L x 1/2" W
520" L x 1/2" W
520" L x 3/4" W



PTFE Pipe Thread Tapes

- Yellow gas
- 1.2 g/cm³ density
- Intended for application to male threads of metal pipe not exceeding 1 ¹/₂"
- Used primarily in assemblies handling gasoline, naphtha, benzene, kerosene and petroleum oils to make joints tight against leakage
- Adaptable in some cases for application on pipe used with devices handling propane, butane or natural gas at a pressure not over 300 psi (2070kPa)
- 100% PTFE
- Color/Finish: Yellow

SKU	Size
PSGTTD260	260" L x 1/2" W
PSGTTD520	520" L x 1/2" W



PTFE Pipe Thread Tapes


- Standard density
- 0.35 g/cm³ density
- May be used on all types of threaded fittings for passage of water potable and non-potable, most chemicals, oxygen, gas, hydraulic and high-pressure lines to 1 ¹/₂" in diameter
- Not for use on liquid fuels such as gasoline or diesel
- 100% PTFE
- Teflon
- Meets MIL-spec T-27730A

SKU	Size
PSTTD260	260" L x 1/2" W
PSTTF260	260" L x 3/4" W
PSTTD520	520" L x 1/2" W
PSTTF520	520" L x 3/4" W
PSTTG520	520" L x 1" W





RAP10501 17	RAP16007 14	RAP41007 21	RAP60001 10
RAP10502 17	RAP16009 14	RAP41008 21	RAP60002 10
RAP10520 18	RAP16012 14	RAP41017 20	RAP64010 8
RAP10543 17	RAP16013 14	RAP41023 18	RAP75001 8
RAP110025	RAP16014 13	RAP41024 18	RAP75003 8
RAP110035	RAP16030 15	RAP41025 18	RAP75004 8
RAP11214 25	RAP16031 15	RAP41026 18	RAP75005 8
RAP11218 25	RAP16032 15	RAP41027 19	RAP75006 8
RAP11224 25	RAP16033 15	RAP41028 19	RAP75007 8
RAP11312 27	RAP16034 15	RAP41030 18	RAP75009 8
RAP11414 25	RAP16501 15	RAP41031 18	RAP75010 8
RAP11418 25	RAP16504 15	RAP41032 18	RAP90101 35
RAP11424 25	RAP16505 15	RAP41033 18	RAP90102 35
RAP11502 11	RAP16506 15	RAP41034 18	RAP90103 35
RAP11514 25	RAP16507 16	RAP41035 18	RAP90201 35
RAP12501 6	RAP16508 16	RAP41037 20	RAP90202 35
RAP125047	RAP16512 16	RAP41038 20	RAP90203 35
RAP12507 6	RAP17002 16	RAP41039 19	RAP147708 23
RAP12509 6	RAP17004 17	RAP41201 30	RAW1L2
RAP12518 6	RAP17006 17	RAP42009 21	RAW2L2
RAP12525 6	RAP17007 17	RAP42014 19	RAWHS12
RAP12530 6	RAP18001 11	RAP42015 19	RAWHS22
RAP130027	RAP18002 11	RAP42040 21	RAWHS32
RAP130037	RAP18003 11	RAP44020 4	RAWHS42
RAP130047	RAP18004 11	RAP44022 4	RAWHS52
RAP13511 16	RAP18006 22	RAP44024 4	RAWHS62
RAP13512 16	RAP18007 22	RAP44026 4	RAWHS782
RAP13513 16	RAP18008 22	RAP44028 4	RAWHS1122
RAP13514 16	RAP18009 22	RAP44030 4	RAWHS1142
RAP13515 16	RAP18010 22	RAP44032 5	RAWHS1342
RAP145039	RAP18011 22	RAP440345	RAWHS1382
RAP145049	RAP18024 12	RAP44036 4	RAWHS2122
RAP14506 9	RAP18541 21	RAP44040 5	RAWHS2142
RAP14507 9	RAP18550 27	RAP44042 5	RAWHS2342
RAP145089	RAP18551 27	RAP50105 8	RAWHS2582
RAP14509 8	RAP18552 27	RAP50115 23	RAWHS3122
RAP145509	RAP30501 31	RAP50125 24	RAWHS4122
RAP14551 9	RAP30502 31	RAP50130 26	RAWHS5122
RAP14552 9	RAP31201 28	RAP50145 27	RAWHS13162
RAP145539	RAP31202 28	RAP50150 26	RAWHS29162
RAP14560PK9	RAP31203 28	RAP50175 19	RAWRB606HD 3
RAP15502 12	RAP31204 30	RAP501855	RAWRB6103
RAP15507 12	RAP31206 28	RAP50190 10	RAWRB6143
RAP15508 12	RAP31207 28	RAP50200 12	RAWRB614HD 3
RAP15510 10	RAP31401 29	RAP50205 23	RAWRB6183
RAP15515 13	RAP31402 29	RAP50210 24	RAWRB6243
RAP15520 13	RAP31601 29	RAP50215 27	RAWRB8143
RAP15525 13	RAP31602 29	RAP50220 26	RAWRB8183
RAP15610 12	RAP32001 31	RAP50230 22	RAWRB906HD 3
RAP15615 12	RAP33001 30	RAP50245 9	RAWRB9103
RAP16001 13	RAP33002 30	RAP50315 9	RAWRB914HD 3
RAP16002 13	RAP33003 30	RAP50325 14	RAWRB918HD 3
RAP16003 13	RAP41002 24	RAP50330 11	
RAP16004 13	RAP41003 20	RAP50505 26	



YOUR SUPPLIES ARE JUST A FEW CLICKS AWAY.

VISIT FERGUSON.COM TO VIEW OUR FULL SELECTION OF PRODUCTS AND SERVICES.



RAPTOR®

RAPTORTOOL.COM

©2016 Ferguson Enterprises, Inc.

PL-RAP-100 0416 153507