

BAND SAW BLADES

EXTREME METAL BAND SAW BLADES

OVERVIEW

Our new Extreme Metal Band Saw Blades deliver exactly what you need for daily job site use – More Cuts and Less Blade Changes. An aggressive variable pitched tooth design gives you the versatility to cut more metal thickness with one band saw blade. The portable band saw blade's versatility pairs with 3X longer life in stainless steel. Each blade gives you more cuts resulting in fewer blade changes. The band saw blade also gives fast, clean cuts in common materials, delivering you the performance you are looking for in a single blade. These blades are available in Deep Cut (44-7/8"), Compact (35-3/8"), and Sub-Compact (27") sizes.



FEATURES

- More Cuts. Less Blade Changes.
- Fastest cutting blade in thin, hard metals
- Aggressive tooth design for 2X Faster cuts in thick metals

EXTREME METAL BAND SAW BLADES

TPI	44-7/8"			35-3/8"			27"		
	3 Pack	25 Pack	100 Pack	3 Pack	25 Pack	100 Pack	3 Pack	25 Pack	100 Pack
8/10	48-39-0601	48-39-0605	48-39-0603	48-39-0609	48-39-0606	48-39-0653	-	-	-
12/14	48-39-0611	48-39-0615	48-39-0613	48-39-0619	48-39-0616	48-39-0663	48-39-0711	-	-

STANDARD BAND SAW BLADES

OVERVIEW

Maximize your band saw performance and make straight, accurate cuts in a variety of materials with MILWAUKEE® Band Saw Blades. MILWAUKEE's Band Saw Blades deliver long tooth life in a variety of metal, including strut, conduit, angle iron, copper tube, threaded rod, and pipe. The blade's tooth form, pitch, and set ensure straight, accurate cuts time and time again. These blades are available in Deep Cut (44-7/8"), Compact (35-3/8"), and Sub-Compact (27") sizes.

STANDARD BAND SAW BLADES

TPI	44-7/8"			35-3/8"		32-7/8"	27"
	1 Pack	2 Pack	3 Pack	1 Pack	3 Pack	3 Pack	3 Pack
10	48-39-0500	-	48-39-0501	48-39-0508	48-39-0509	-	-
10/14	48-39-0550	48-39-0554	48-39-0551	-	-	-	-
14	48-39-0510	48-39-0514	48-39-0511	48-39-0518	48-39-0519	-	-
14/18	48-39-0560	-	48-39-0561	-	-	-	-
18	48-39-0520	48-39-0524	48-39-0521	48-39-0528	48-39-0529	48-39-0579	48-39-0572
24	48-39-0530	48-39-0534	48-39-0531	48-39-0538	48-39-0539	-	-

CARBIDE HOLE CUTTERS

STEEL PLATE CARBIDE HOLE CUTTERS

OVERVIEW

Specifically designed for hand-held operations in materials up to 3/8" thick, these carbide-tipped Steel Plate Hole Cutters stay sharper longer than High Speed Steel or Bi-Metal Hole Saws. They produce Drill Press quality holes even in hand-held operations. For cutting materials over 3/8" up to a depth of 1/2", a drill press is recommended. When cutting depth is over 1/4", use HAWG WASH™ cutting fluid to keep cutting surface cool and lubricated. HAWG WASH™ fluid is available in 16 ounce bottles (49-32-0081). One bottle makes one gallon of lubricating solution.



FEATURES

- Clean Holes: Drills burr-free holes
- Long Life: Carbide tips stay sharper longer than high-speed steel or bi-metal cutters
- Versatile: 1/2" cutting depth

STEEL PLATE CARBIDE HOLE CUTTERS

Diameter	Cutting Depth	Material	Part No.
11/16"	1/2"		49-57-8201
3/4"	1/2"		49-57-8203
13/16"	1/2"		49-57-8205
7/8"	1/2"		49-57-8207
15/16"	1/2"		49-57-8209
1"	1/2"		49-57-8211
1-1/16"	1/2"		49-57-8213

Diameter	Cutting Depth	Material	Part No.
1-1/8"	1/2"		49-57-8215
1-3/16"	1/2"		49-57-8217
1-1/4"	1/2"		49-57-8219
1-5/16"	1/2"		49-57-8221
1-3/8"	1/2"		49-57-8223
1-7/16"	1/2"		49-57-8225
1-1/2"	1/2"		49-57-8227

STEEL PLATE CARBIDE HOLE CUTTER KITS

STEEL PLATE CARBIDE HOLE CUTTER KITS

Description	Includes	Material	Part No.
5 Pc Contractor's Steel Plate Carbide Hole Cutter Kit	(1) 11/16" Carbide Cutter (1) 13/16" Carbide Cutter (1) 15/16" Carbide Cutter (1) Pilot Bit (1) Quick Change Arbor with Pilot Bit		49-22-8200
7 Pc Contractor's Steel Plate Carbide Hole Cutter Kit	(1) 11/16" Carbide Cutter (1) 13/16" Carbide Cutter (1) 15/16" Carbide Cutter (1) 1-1/8" Carbide Cutter (1) 1-3/8" Carbide Cutter (1) Pilot Bit (1) Quick Change Arbor with Pilot Bit		49-22-8210

BAND SAW BLADES

CARBIDE HOLE CUTTERS