

M18 FUEL 10" Dual Bevel Sliding

Compound Miter Saw Kit 2734-21HD (2734-20 Tool-Only)

Specifications:

-	
Blade Size	10"
No Load RPM	4,000
Max Bevel Angle	48° / 48°
Max Miter Angle	50° / 60°
Max Vertical Capacity	5-3/4"
Max Horizontal Capacity	2x12
Weight	47.0 lbs



Includes: (1) M18[™] REDLITHIUM[™] HIGH OUTPUT[™] XC8.0 Battery Pack, Blade Wrench, Carbide Tipped Blade, Clamp, Dust Bag, Rapid Charger

M18 FUEL

7-1/4" Dual Bevel Sliding **Compound Miter Saw Kit** 2733-21 (2733-20 Tool-Only)

Specifications:

-p	
Blade Size	7-1/4"
No Load RPM	5,000
Max Bevel Angle	48° / 48°
Max Miter Angle	48° / 48°
Max Vertical Capacity	3-1/2"
Max Horizontal Capacity	2x8
Weight	28.0 lbs

Includes: (1) M18[™] REDLITHIUM[™] XC5.0 Battery Pack, Blade Wrench, Blade, Clamp, Multi-Voltage Charger





DLITHIUM

Blade Size 8-1/4" 5/8" Arbor Size Max Bevel Cut Depth 2-1/2" at 90°; 1-3/4" at 45° 24" Left of Blade; 12" Right of Blade Rip Capacity Weight 45.0 lbs

6,300

Includes: (1) M18™ REDLITHIUM™ HIGH OUTPUT™ HD12.0 Battery Pack, Blade, Wrench, Anti-Kickback Pawls, Guard, Riving Knife, Fence, Push Stick, Miter Gauge, Rapid Charger

M18 FUEL

M18 FUEL

Specifications:

RPM

8-1/4" Table Saw

2736-21HD (2736-20 Tool-Only)

w/ ONE-KEY™ Kit

12" Dual Bevel Sliding Compound Miter Saw w/ ONE-KEY™ Kit

2739-21HD (2739-20 Tool-Only)

Specifications:

specifications.		
Blade Size	12"	
No Load RPM	3,500	
Max Bevel Angle	48° / 48°	
Max Miter Angle	50° / 60°	
Max Vertical Capacity	6-3/4"	
Max Horizontal Capacity	2x14	
Weight	47.6 lbs	



Includes: (1) M18™ REDLITHIUM™ HIGH OUTPUT™ HD12.0 Battery Pack, Blade, Clamp, Handles, Rapid Charger











Specifications:

•	· · · · · · · · · · · · · · · · · · ·	u
Collation Angle	21° Round Head Nail	I
Nail Size	2" - 3-1/2"	
Nail Collation	20° – 22°	
Magazine Size	45 Nails	
Max Fire Rate	3 Nails per Second	
Firing Modes	Sequential or Contact Actuation	

Includes: (1) M18™ REDLITHIUM™ XC5.0 Battery Pack, Rafter Hook, Hex Key, Multi-Voltage Charger, Contractor Bag

Related Accessory: 48-08-2744 21° Framing Nailer Extended Capacity Magazine





M18 FUEL **18 Gauge Brad Nailer Kit**

2746-21CT (2746-20 Tool-Only)

Specifications:

opcomoditions:		
	Nail Diameter	18 Gauge
	Nail Size	5/8" - 2-1/8"
	Magazine Size	110 Nails
	Max Fire Rate	3 Nails per Second
	Magazine Loading	Side Load
	Firing Modes	Sequential or Contact Actuation

Includes: (1) M18™ REDLITHIUM™ CP2.0 Battery Pack, Reversible Belt Hook, Multi-Voltage Charger, Contractor Bag



M18 FUEL **30° Framing Nailer Kit**

2745-21 (2745-20 Tool-Only)

Specifications:

Collation Angle	30° Clipped or Full Head Nail
Nail Size	2" - 3-1/2"
Nail Collation	30° – 34°
Magazine Size	57 Nails
Max Fire Rate	3 Nails per Second
Firing Modes	Sequential or Contact Actuation

Includes: (1) M18[™] REDLITHIUM[™] XC5.0 Battery Pack, Rafter Hook, Hex Key, Multi-Voltage Charger, Contractor Bag

Related Accessory:

48-08-2745 30° Framing Nailer Extended Capacity Magazine





M18 FUEL 18 Gauge 1/4" Narrow Crown Stapler Kit

2749-21CT (2749-20 Tool-Only) Specifications:

Staple Diameter	16 Gauge
Staple Crown Size	1/4"
Staple Length	3/8" - 1-1/2"
Magazine Size	108 Staples
Max Fire Rate	4 Staples per Second
Magazine Loading	Front Load

Includes: (1) M18™ REDLITHIUM™ CP2.0 Battery Pack, Reversible Belt Hook, Multi-Voltage Charger, Contractor Bag



M18 FUEL 16 Gauge Straight Finish Nailer Kit

2741-21CT (2741-20 Tool-Only)

Specifications:

Nail Diameter	16 Gauge
Nail Size	3/4" - 2-1/2"
Nail Collation Angle	0°
Magazine Size	110 Nails
Max Fire Rate	3 Nails per Second
Magazine Loading	Bottom Load
Length / Weight	11.9" / 7.2 lbs

Includes: (1) M18™ REDLITHIUM™ CP2.0 Battery Pack, Multi-Voltage Charger, Contractor Bag





