

M18 FUEL

1/4" Hex Impact Driver w/ ONE-KEY™ Kit

2857-22, 2857-22CT (2857-20 Tool-Only)

Specifications:

|                           |                       |
|---------------------------|-----------------------|
| Max Torque                | 2,000 in-lbs          |
| IPM                       | 0 – 4,300             |
| RPM                       | 0 – 3,600             |
| DRIVE CONTROL™            | 4-Mode (Customizable) |
| Chuck Type                | 1/4" Hex              |
| Single Hand Bit Insertion | Yes                   |
| Length / Weight           | 4.6" / 3.8 lbs        |

**Includes:** 2857-22 (2) M18™ REDLITHIUM™ XC5.0 Battery Packs; 2857-22CT (2) M18™ REDLITHIUM™ CP2.0 Battery Packs; **All Kits Include:** Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case



M18 FUEL

1/4" Hex Impact Driver Kit

2853-22, 2853-22CT (2853-20 Tool-Only)

Specifications:

|                             |                |
|-----------------------------|----------------|
| Max Torque                  | 2,000 in-lbs   |
| IPM                         | 0 – 4,300      |
| RPM                         | 0 – 3,600      |
| DRIVE CONTROL™              | 4-Mode         |
| Chuck Type                  | 1/4" Hex       |
| Single-Handed Bit Insertion | Yes            |
| Length / Weight             | 4.6" / 3.8 lbs |

**Includes:** 2853-22 (2) M18™ REDLITHIUM™ XC5.0 Battery Packs; 2853-22CT (2) M18™ REDLITHIUM™ CP2.0 Battery Packs; **All Kits Include:** Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case



M18 FUEL

SURGE™ 1/4" Hex Hydraulic Driver Kit

2760-22, 2760-22CT (2760-20 Tool-Only)

Specifications:

|                      |                |
|----------------------|----------------|
| Sustained Max Torque | 450 in-lbs     |
| IPM                  | 0 – 4,000      |
| RPM                  | 0 – 3,000      |
| DRIVE CONTROL™       | 4-Mode         |
| Length / Weight      | 5.0" / 3.9 lbs |

**Includes:** 2760-22 (2) M18™ REDLITHIUM™ XC5.0 Battery Packs; 2760-22CT (2) M18™ REDLITHIUM™ CP2.0 Battery Packs; **All Kits Include:** Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case



M18™

Brushless 1/4" Hex 3-Speed Impact Driver

2851-20 Tool-Only

Specifications:

|                 |                |
|-----------------|----------------|
| Max Torque      | 1,600 in-lbs   |
| IPM             | 0 – 4,200      |
| RPM             | 0 – 3,400      |
| Chuck Type      | 1/4" Hex       |
| DRIVE CONTROL™  | 3-Mode         |
| Length / Weight | 5.1" / 2.0 lbs |

Battery and Charger Sold Separately

**Includes:** Belt Clip



M18™

Right Angle Impact Driver Kit

2667-22, 2667-21CT (2667-20 Tool-Only)

Specifications:

|                     |                       |
|---------------------|-----------------------|
| Max Torque (2-Mode) | 350 / 675 in-lbs      |
| IPM                 | 0 – 2,400 / 0 – 3,400 |
| RPM                 | 0 – 1,500 / 0 – 2,250 |
| Anvil Type          | 1/4" Hex              |
| Length / Weight     | 14.1" / 3.9 lbs       |

**Includes:** 2667-22 (2) M18™ REDLITHIUM™ XC3.0 Battery Packs; 2667-21CT (1) M18™ REDLITHIUM™ CP1.5 Battery Pack; **All Kits Include:** Belt Clip, Multi-Voltage Charger, Carrying Case



M18 FUEL

1/2" Compact Impact Wrench w/ Pin Detent w/ ONE-KEY™ Kit

2759-22, 2759B-22 (2759-20, 2759B-20 Tool-Only)

Specifications:

|                    |                       |
|--------------------|-----------------------|
| Fastening Torque   | 220 ft-lbs            |
| Nut-Busting Torque | 220 ft-lbs            |
| IPM                | 0 – 3,200             |
| RPM                | 0 – 2,500             |
| DRIVE CONTROL™     | 4-Mode (Customizable) |
| Anvil Type         | 1/2" Pin Detent       |
| Length / Weight    | 6.1" / 4.2 lbs        |

**Includes:** 2759-22 1/2" Compact Impact Wrench w/ Pin Detent w/ ONE-KEY™; 2759B-22 1/2" Compact Impact Wrench w/ Friction Ring w/ ONE-KEY™; **All Kits Include:** (2) M18™ REDLITHIUM™ XC5.0 Battery Packs, Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case



M18 FUEL

Drywall Screw Gun Kit

2866-22, 2866-22CT (2866-20 Tool-Only)

Specifications:

|                 |                |
|-----------------|----------------|
| RPM             | 0 – 4,500      |
| Belt Clip       | Yes            |
| Auto Start Mode | Yes            |
| Length / Weight | 9.0" / 4.1 lbs |

**Includes:** 2866-22 (2) M18™ REDLITHIUM™ XC5.0 Battery Packs; 2866-22CT (2) M18™ REDLITHIUM™ CP2.0 Battery Packs; **All Kits Include:** Belt Clip, PR2 Bit, Multi-Voltage Charger, Contractor Bag



**Related Accessory:**  
49-20-0001 MILWAUKEE® Collated Magazine  
Screw Capacity: Up to 2"  
Compatible with all major screw brands

**Related Tool:**  
2627-22 M18™ Cut Out Tool Kit Pg. 48



M18™

Right Angle Impact Wrench Kit

2668-22, 2668-21CT (2668-20 Tool-Only)

Specifications:

|                           |                       |
|---------------------------|-----------------------|
| Fastening Torque (2-Mode) | 30 / 60 ft-lbs        |
| Nut-Busting Torque        | 60 ft-lbs             |
| IPM                       | 0 – 2,400 / 0 – 3,400 |
| RPM                       | 0 – 1,500 / 0 – 2,250 |
| Anvil Type                | 3/8"                  |
| Length / Weight           | 14.3" / 3.9 lbs       |

**Includes:** 2668-22 (2) M18™ REDLITHIUM™ XC3.0 Battery Packs; 2668-21CT (1) M18™ REDLITHIUM™ CP1.5 Battery Pack; **All Kits Include:** Belt Clip, Multi-Voltage Charger, Carrying Case



M18™

1/2" Compact Impact Wrench Kit

2659-22 (2659-20 Tool-Only)

Specifications:

|                    |                 |
|--------------------|-----------------|
| Fastening Torque   | 183 ft-lbs      |
| Nut-Busting Torque | 183 ft-lbs      |
| IPM                | 0 – 3,350       |
| RPM                | 0 – 2,450       |
| Anvil Type         | 1/2" Pin Detent |
| Length / Weight    | 6.0" / 4.1 lbs  |

**Includes:** (2) M18™ REDLITHIUM™ XC3.0 Battery Packs, Belt Clip, Multi-Voltage Charger, Carrying Case



M18 FUEL

1/2" Compact Impact Wrench w/ Pin Detent Kit

2755-22, 2755B-22 (2755-20, 2755B-20 Tool-Only)

Specifications:

|                    |                 |
|--------------------|-----------------|
| Fastening Torque   | 220 ft-lbs      |
| Nut-Busting Torque | 220 ft-lbs      |
| IPM                | 0 – 3,200       |
| RPM                | 0 – 2,500       |
| DRIVE CONTROL™     | 4-Mode          |
| Anvil Type         | 1/2" Pin Detent |
| Length / Weight    | 6.1" / 4.2 lbs  |

**Includes:** 2755-22 1/2" Compact Impact Wrench w/ Pin Detent; 2755B-22 1/2" Compact Impact Wrench w/ Friction Ring; **All Kits Include:** (2) M18™ REDLITHIUM™ XC5.0 Battery Packs, Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case

