

M18 FUEL **Sewer Sectional Machine** Kit w/ CABLE DRIVE 2871A-22, 2871-22

Specifications: Max Drain Line 2" - 8" up to 200' Capacity Cable Capacity 7/8" and 1/1-4" Powered Cable Feed & Yes, CABLE DRIVE Retract 700 RPM Cable Spin Speed


23" / 35" Height / Length Weight 74 lbs

Includes: 2871A-22 (7) 1-1/4" x 15' All Purpose Open Wind Cables, (2) Cable Containers, Straight Auger, Funnel Auger, Small Opening Tool, Medium Opening Tool, 3" Grease Cutter, 3" Root Cutter, 4" Root Cutter, Pin Key, Head Attachment Case: All Kits Include: (2) M18[™] REDLITHIUM[™] HIGH OUTPUT[™]

HD12.0 Battery Packs, Rear Guide Hose, Rapid Charger

Related Accessories:

47-53-2871 Cable Container; 47-53-2872 Rear Guide Hose; 48-53-2851 1-1/4" x 15' All Purpose Open Wind Sectional Cable; 48-53-2854 1-1/4" x 15' Heavy Duty Open Wind Sectional Cable; 48-53-2852 7/8" x 15' Open Wind Cable; 48-53-3830 Straight Auger for 7/8" Sectional Cable; 48-53-3831 Funnel Auger for 7/8" Sectional Cable; 48-53-3832 3" Root Cutter for 7/8" Sectional Cable; 48-53-3833 4" Root Cutter for 7/8" Sectional Cable; 48-53-3834 6" Root Cutter for 7/8" Sectional Cable; 48-53-3835 Small Opening Tool for 7/8" Sectional Cable; 48-53-3836 Medium Opening Tool for 7/8" Sectional Cable; 48-53-3837 3" Grease Cutter for 7/8" Sectional Cable; 48-53-3838 4" Grease Cutter for 7/8" Sectional Cable 48-53-3840 Head Attachment Kit for 7/8" Sectional Cable; 48-53-4830 Straight Auger for 1-1/4" Sectional Cable; 48-53-4831 Funnel Auger for 1-1/4" Sectional Cable; 48-53-4832 3" Root Cutter for 1-1/4" Sectional Cable; 48-53-4833 4" Root Cutter for 1-1/4" Sectional Cable: 48-53-4834 6" Root Cutter for 1-1/4" Sectional Cable; 48-53-4835 Small Opening Tool for 1-1/4" Sectional Cable; 48-53-4836 Medium Opening Tool for 1-1/4" Sectional Cable; 48-53-4837 3" Grease Cutter for 1-1/4"" Sectional Cable; 48-53-4838 4" Grease Cutter for 1-1/4" Sectional Cable; 48-53-4840 Head Attachment Kit for 1-1/4" Sectional Cable: 44-60-0005 Pin Key for Drain Cleaning; 48-53-2839 Head Attachment Case





DLITHIUI

Capacity

SWITCH PACK[™] Sectional **Drum System Kit**

2775-211, 2775A-211, 2775B-211, 2775C-222, 2775E-211 **Specifications:**



1-1/4" – 4" up to 100' Maximum Drain Line (not for roots) Drum Capacity Inner Core Cables: 5/16" x 75', Best for 1-1/4" - 2-1/2" drain lines; 3/8" x 50', Best for 2" - 3" drain lines; 1/2" x 50', Best for 3" - 4" drain lines Open Wind Cables: 5/8" x 50', Best for 1-1/4" – 3" drain lines (soft blockages) Backpack Straps Yes Removable Drum Yes, Tool-Free

| Cable Spin Speed | 250 RPM |
|-----------------------|---------|
| Electronic Foot Pedal | Yes |
| Integrated Drum Brake | Yes |
| Length | 15.8" |

Includes: 2775A-211: 5/16" x 75' Inner Core Drop Head Cable w/ RUST GUARD[™] Plating:

2775B-211: 3/8" x 50' Inner Core Coupling Cable w/ RUST GUARD™ Plating, (4) Cable Head Attachments w/ RUST GUARD[™] Plating (1-1/2" Spade Bit, 1-1/2" C-Cutter, Medium Funnel, Medium Drop Head), Pin Key; 2775C-222: Additional M18[™] REDLITHIUM[™] XC5.0 Battery Pack, Additional SWITCH PACK[™] Drum w/ Anchor Cable, (2) 1/2" x 50' Inner Core Coupling

Cables w/ RUST GUARD™ Plating, (4) Cable Head Attachments w/ RUST GUARD™ Plating (1-1/2" Spade Bit, 1-1/2" C-Cutter, Medium Funnel, Medium Drop Head), Pin Key;

2775E-211: 5/8" x 50' Open Wind Coupling Cable w/ RUST GUARD™ Plating, (4) Cable Head Attachments w/ RUST GUARD™ Plating (1" Spade Bit, C-Cutter, Small Bulb Head, Small Drop Head), Pin Key;

All Kits Include: 2775-211: SWITCH PACK™ Powered Base, SWITCH PACK[™] Drum w/ Anchor Cable, (1) M18[™] REDLITHIUM[™] XC5.0 Battery Pack, Multi-Voltage Charger

Related Accessory:

47-53-2775 SWITCH PACK[™] Drum w/ Anchor Cable



M18 FUEL Drain Snake w/ CABLE DRIVE™ **Locking Feed System Kit**

2772A-21 (2772A-20 Tool-Only), 2772B-21XC **Specifications:**

Maximum Drain Line 1-1/4" – 3" up to 50'

| Capacity | |
|---------------------------------|---|
| Drum Capacity | 1/4" x 50', Best for 1-1/4" – 2" drain lines; 5/16" x 50', Best for 1-1/4" – 2-1/2" drain lines; 3/8" x 35', Best for 2" – 3" drain lines |
| Powered Cable Feed & Retract | Yes, CABLE DRIVE™ |
| Variable Feed Speed | 0 – 8" Per Second |
| Variable Spin Speed | 0 – 600 RPM |
| Feed Lock | Yes, Twist Lock |
| Cable Lock | Yes, Twist Lock |
| LED Light | Yes |
| Length / Weight | 19.5" / 8.2 lbs |

Includes: 2772A-21 (1) M18[™] REDLITHIUM[™] CP2.0 Battery Pack, 5/16" x 35' Inner Core Bulb Head Cable w/ RUST GUARD™ Plating; 2772B-21XC (1) M18[™] REDLITHIUM[™] XC5.0 Battery Pack, 1/4" x 35' Inner Core Bulb Head Cable w/ RUST GUARD™ Plating, 3/8" x 35' Inner Core Coupling Cable w/ RUST GUARD™ Plating, (4) Cable Attachments (1" Spade Bit, 1" C-Cutter, Small Bulb Head, Small Drop Head), Pin Kev: 2772A-20 Only Includes 5/16" x 35' Inner Core Bulb Head Cable w/ RUST GUARD™ Plating, Battery and Charger Sold Separately; All Kits Include: Multi-Voltage Charger, Storage Bucket

65

SYSTEM WIDE M18



Drain Cleaning Accessories

Compatible with MILWAUKEE® and other professional brand drain cleaning machines

RUST GUARD[™] Plated Cables 48-53-2563 1/4" x 25' Inner Core Bulb Head Cable; 48-53-2564 1/4" x 25' Inner Core Drop Head Cable; 48-53-2671 1/4" x 35' Inner Core Bulb Head Cable; 48-53-2672 1/4" x 50' Inner Core Bulb Head Cable; 48-53-2561 5/16" x 25' Inner Core Bulb Head Cable; 48-53-2562 5/16" x 25' Inner Core Drop Head Cable; 48-53-2673 5/16" x 35' Inner Core Bulb Head Cable; 48-53-2674 5/16" x 50' Inner Core Bulb Head Cable; 48-53-2772 5/16" x 75' Inner Core Drop Head Cable; 48-53-2676 3/8" x 25' Inner Core Coupling Cable; 48-53-2675 3/8" x 35' Inner Core Coupling Cable: 48-53-2773 3/8" x 50' Inner Core Coupling Cable; 48-53-2774 1/2" x 50' Inner Core Coupling Cable; 48-53-2775 5/8" x 50' Open Wind Coupling Cable

RUST GUARD[™] Plated Cable Attachments Compatible with MILWAUKEE® Coupling Cables

48-53-2681 Small Bulb Head; 48-53-2682 Small Drop Head; 48-53-2683 1" Spade Bit: 48-53-2684 1" C-Cutter: 48-53-2685 5 Pc Small Cable Head Attachment Kit; 48-53-2786 Funnel Head; 48-53-2787 Medium Drop Head; 48-53-2788 1-1/2" Spade Bit; 48-53-2789 1-1/2" C-Cutter; 48-53-2790 5 Pc Medium Cable Head Attachment Kit

M18[™] Transfer Pump Kit 2771-21 (2771-20 Tool-Only)



Includes: (1) M18[™] REDLITHIUM[™] XC3.0 Battery Pack, (2) 3/4" Brass Fittings, Multi-Voltage Charger



