

SILTSOXX PREFILLED COMPOST FILTER SOCK



SiltSoxx

SiltSoxx by Filtrexx is the quickest, easiest and most cost effective solution for sediment control. Easily installed for a variety of construction applications, SiltSoxx reduces the labor cost required for installation and maintenance, while delivering optimal performance. SiltSoxx is prefilled with certified FilterMedia™, ready to ship and easy to install. Available in a variety of sizes, configurations, and mesh materials for any project requirements. All SiltSoxx mesh is knitted in the USA, and all FilterMedia is locally sourced. SiltSoxx is in compliance with most state & federal agency specifications and regulations. Common applications include perimeter control, inlet protection, check dams, and slope interruption.

SiltSoxx ORIGINAL (pg 3)

Our SiltSoxx ORIGINAL strength mesh is the most widely recognized and used product in the industry. Available in green/black stripe or tan.

SiltSoxx EXTREME (pg 4)







Our most durable mesh material, SiltSoxx EXTREME is specially designed to withstand the harsh surface conditions of asphalt and concrete. With an extra tough, wear & tear resistant mesh, this product is perfect for urban construction and/or when dealing with rugged conditions. Available in green/black stripe or solid orange for safety visibility.

SiltSoxx NATURAL (pg 4)

This line of mesh is 100% natural and biodegradable, eliminating the need for field removal. Leave in place for ongoing, natural protection.

SiltSoxx NATURAL ORIGINAL: Cotton fiber; functional field longevity up to 12 months.







SiltSoxx NATURAL PLUS: Wood fiber; functional field longevity up to 18 months.

Product Name	SiltSoxx ORIGINAL (pg 3)	SiltSoxx EXTREME (pg 4)	SiltSoxx NATURAL ORIGINAL (pg 4)	SiltSoxx NATURAL PLUS (pg 4)
Mesh Material Type	Multi-Filament Polypropylene (MFPP)	Multi-Filament Polypropylene (MFPP)	All Natural Biodegradable Cotton Fiber	All Natural Biodegradable Wood Fiber
Uses	standard applications	hard surfaces; rugged sites; high traffic	leave on site; short-term	leave on site; long-term
Mesh Opening Size	1/8"	1/16"	1/8"	1/8"
Diameters	5", 8", 12", 18", 24"	8", 12"	5", 8", 12"	5", 8", 12"
Functional Longevity/ Project Duration*	up to 5 yr	up to 5 yr	up to 12 mo	up to 18 mo
Fill Material	Locally sourced FilterMedia	Locally sourced FilterMedia	Locally sourced FilterMedia	Locally sourced FilterMedia
Mesh Color	 green/thin black stripe  tan (5" & 8" only)	 green/black thick stripe  orange	 beige	 off-white

*Functional longevity ranges are estimates only. Site specific environmental conditions may result in significantly shorter or longer time periods.

SILTSOXX PREFILLED COMPOST FILTER SOCK

SiltSoxx ORIGINAL

SiltSoxx Diameter	Mesh Type / Color	Item Number	Total Length	Unit Length	Units/Pallet	Stakes/Pallet	Pallet Pkg
5 inch	 ORIGINAL Mesh green/thin black stripe	P05-400S16	400 ft	25 ft	16	64	wrapped
		P05-400S40	400 ft	10 ft	40	80	wrapped
		P05-400S2	400 ft	200 ft	2	42	wrapped
	 ORIGINAL Mesh tan	P05T-400S16	400 ft	25 ft	16	64	wrapped
		P05T-400S40	400 ft	10 ft	40	80	wrapped
		P05T-400S2	400 ft	200 ft	2	42	wrapped
8 inch	 ORIGINAL Mesh green/thin black stripe	P08-180S18	180 ft	10 ft	18	36	wrapped
		PB08-180S18	180 ft	10 ft	18	36	bagged
		P08-200	200 ft	200 ft	1	21	wrapped
		PB08-200	200 ft	200 ft	1	21	bagged
	 ORIGINAL Mesh tan	P08T-180S18	180 ft	10 ft	18	36	wrapped
		P08T-200	200 ft	200 ft	1	21	wrapped
12 inch	 ORIGINAL Mesh green/thin black stripe	P12-100S10	100 ft	10 ft	10	20	wrapped
		PB12-100S10	100 ft	10 ft	10	20	bagged
		P12-110	110 ft	110 ft	1	12	wrapped
		PB12-110	110 ft	110 ft	1	12	bagged
18 inch	 ORIGINAL Mesh green/thin black stripe	P18-50S5	50 ft	10 ft	5	10	wrapped
		PB18-50S5	50 ft	10 ft	5	10	bagged
		P18-55	55 ft	55 ft	1	7	wrapped
		PB18-55	55 ft	55 ft	1	7	bagged
24 inch	 ORIGINAL Mesh green/thin black stripe	P24-30S3	30 ft	10 ft	3	6	wrapped
		P24-30	30 ft	30 ft	1	4	wrapped
		PB24-30	30 ft	30 ft	1	4	bagged

Diameter	Stake Size
5 inch	1" x 1" x 12"
8 inch	2" x 2" x 24"
12 inch	2" x 2" x 24"
18 inch	2" x 2" x 36"
24 inch	2" x 2" x 36"

Notes:

Approximate Pallet Weight Range: 1600-1900 lbs
 Approximate Pallet Dimension Range: 48"L x 40"W x 55"-70"H
 Pallet Packaging, Wrapped: black plastic wrapped w/high UV pallet cap
 Pallet Packaging, Bagged: white heavy duty super sack with forklift straps, available in select locations
 Some pallet items are available without stakes – call for availability