Specifications:

Door Prep	Cross Bore 2-1/8". Edge Bore 1".
Backset	Adjustable 2-3/8" or 2-3/4".
Door Thickness	1-3/8" to 1-3/4" standard, 2 1/4" doors optional on 200 and 400 functions only
Cylinder	SmartKey or Traditional 5-pin Pin & Tumbler
Faceplates	1" x 2-1/4" Specify round corner or square corner. Also available as drive-in latch.
Strikes	2-1/4" full lip. Specify round corner or square corner. Other options available.
Bolt	1/2" throw.
Door Handing	Reversible for right or left hand doors.
ANSI/BHMA	A156.2 Grade 3 (all functions except 488)

Functions:



*See price book for complete listing



SMARTKEY. featuring BumpGuard™:

EASILY RE-KEY IN THREE EASY STEPS



Insert functioning key and turn 1/4 turn clockwise.




Insert and remove the SmartKey learn tool. Remove functioning key.



Insert new key and turn 1/2 turn counterclockwise. Your lock is now re-keyed!

Dimensions:



Finishes:



Polished Brass (3)



Antique Brass (5)



NEW Satin Nickel (15)



Polished Chrome (26)



Chrome (26D)