



# Coil Gun®

Coil Gun is a "hose-end" sprayer that features five different mix ratio settings designed for coil cleaners. Utilizes a 2 quart capacity bottle and includes a foam wand as well as "quick disconnect" capability. The Coil Gun Probe accessory has a 90° direction of spray that allows cleaning from inside the coil. It also provides easy access in tough-to-reach locations.

Coil Gun	4774-0
Coil Gun Probe	4774-1

4770-2



# **Coil Mate™ Coil Cleaning Hose**

Durable 5/8 inch diameter reinforced hose with Flex-Guard protection. The 50-foot hose is equipped with solid brass wrench fittings. The Coil Mate is a necessity when using the popular Coil Gun® or rinsing an air-cooled coil with water after using a Nu-Calgon coil cleaner.

Coil Mate Hose	61231
Hot Water Hose	61238
Plastic Pistol Grip Nozzle	61241





# **Turbo Tank Rinsing Sprayer**

The Turbo Tank is a battery-operated, portable sprayer designed for use with water to rinse cleaning solutions off of HVAC coils. The sprayer is ideally suited for rinsing wall mini-splits, ceiling cassette units and coils in remote areas. Designed for use only with clean water, the sprayer includes a heavy-duty rechargeable battery, battery charger, spray gun, shoulder strap, two spray nozzles and an eight-inch, 90-degree spray wand.

Turbo Tank Sprayer	4778-0
Optional 39-inch Spray Wand	4778-11
Optional AC/DC Power Converter	4778-12
Optional Coil Gun Connector	4778-26

POLY SPRAYERS				
Model	Construction	Capacity	Features	Part #
No. 50P	High-density translucent polyethylene	3 pints	Plastic adjustable nozzle	4770-0
No. 100P	High-density translucent polyethylene	1 gallon	Brass wand & adjustable nozzle	4770-2
No. 200P	High-density translucent polyethylene	2 gallons	Brass wand & adjustable nozzle	4771-2
No. 220CP	High-density translucent polyethylene	2 gallons	Plastic wand & adjustable nozzle	4771-3
No. 300P	High-density translucent polyethylene	3 gallons	Brass wand & adjustable nozzle	4772-0
Multi-purpose Sprayer	Plastic bottle with trigger sprayer	24 ounces	Bottle marked for dilutions	4768-W3

Visit us at www.nucalgon.com or call 1-800-554-5499





# Breathe cleaner, fresher air!

With the technology installed in over 100,000 applications worldwide, iWave is a complete line of bi-polar, high-output ion generators designed specifically for treating air in air conditioning systems. As the air flows past the iWave, positive and negative ions actively purify the supply



air, killing mold, bacteria, and viruses in the coil and living space. The ionization process also reduces allergens, smoke, and static electricity, as well as controls odors (cooking, pet, VOCs) and other particles (no more sunbeams) in the air without creating ozone or any harmful byproducts. Easily installs between air filter and cooling coil to treat the indoor coil; as an alternative, the iWave can be installed in supply air. UL and cUL approved. Includes three-year limited warranty. \* Visit iwaveair.com to learn more.

### iWave®-R Residential Air Cleaner

- Patent-pending self-cleaning design, no maintenance needed
- For duct systems up to 6 tons (2400 CFM)
- Universal voltage 24VAC to 240VAC
- Universal mounting
- Programmable cleaning cycle with integral alarm contact
- No replacement parts needed

#### iWave®-C Commercial Air Cleaner

- Patent-pending self-cleaning design, no maintenance needed
- Duct-mount install for systems up to 12 tons (4800 CFM)
- Waterproof housing for installation inside or outside
- Universal voltage 24VAC to 240VAC
- Programmable cleaning cycle with integral alarm contact



#### 1 each 4900-10

# iWave®-M Mini-Flexible Air Purifier for Ductless Systems

- Versatile ion needles mounted in a flexible bar circuit
- For HVAC cooling coils up to 36" wide
- For ductless systems (mini-split, PTAC) and ice machines
- Chemical and temperature resistant, durable for long service life
- Voltage input 110VAC to 240VAC

1 each	4900-35



# **iWave®-F Flexible Air Cleaner**

- Versatile ion needles mounted in a flexible bar circuit
- For HVAC cooling coils up to 48" wide
- For ductless systems (mini-split, PTAC), duct systems and ice machines
- Durable bar is chemical and temperature resistant
- Voltage input 110VAC to 240VAC

	1 each	4900-30
--	--------	---------


4900-40

# iWave®-V Residential Air Cleaner

- Low maintenance air purifier

1 each

- For systems up to 6 tons (2400 CFM)
- Universal mounting with integrated magnets
- Small compact design with no replacement parts
- Voltage input 24VAC



<sup>\*</sup> For a valid warranty claim within three years, proof of purchase and proof of installation by a licensed HVAC or electrical contractor must be provided. See full warranty for complete details.



SPRAYERS

4770-0