EZ ROLL™ & HONOR ROLL™ GRASS PAVERS



EZ Roll™ Grass Pavers feature hexagonal cells that protect the root zone and prevent soil compaction, allowing healthy grass to thrive in areas that would traditionally have impervious hardscaping installed.

EZ RollTM Grass Pavers are honeycombed rolled grass pavers that are comprised of 24" x 24" x 1" panels. The product is made of up to 100% recycled HDPE material with UV inhibitors. Panels are available in pre-assembled rolls, and multiple panels and rolls easily connect together with a series of locking joints. EZ Roll Grass Pavers have an ultimate compression load rating of 57,888 psf "empty."

Ideal Applications

- Golf cart paths
- Residential driveways
- Parking lots

- Roadway shoulders
- Emergency vehicle or service access roads Also an effective solution for erosion control on slopes and in swales



Honor Roll™ Pavers are ideal for long, linear applications next to curbs, medians.

Specifications

EZ Roll™ Grass Paver

3.96 ft. x 24 ft. rolls -97 square feet total

3.96 ft. x 152 ft. rolls -601.6 square feet total

(150 ft. +/- 2 ft. on the length and 3.96 ft. +/- 1/2 in. for width using 76 panel pairs total)




Honor Roll™

13 in. x 150 ft. rolls - 158.3 square feet total 18 in. x 150 ft. rolls - 226.5 square feet total Empty cells have a compressive strength of

57,888 psf

Product ships in large rolls for easy rollout

Easy to connect locking tabs on sides and ends



Part No.	Description	Color	Pallet Qty.	Wt. Ea. Lbs.	Product Class
EZ4X24	EZ Roll™ Grass Pavers, 3.96 ft. x 24 ft. roll, 97 sf total	Black	6	55.44	55GP
EZ4X150	EZ Roll™ Grass Pavers, 3.96 ft. x 152 ft. roll, 601.6 sf total	Black	1	360.00	55GP
EZ13X150	Honor Roll™ Pavers, 13 in. wide roll	Black	1	172.49	55GP
EZ1.5X150	Honor Roll™ Pavers, 18 in. wide roll	Black	1	172.49	55GP