High-Efficiency Toilet



Product Features

- 1.28 GPF HET, High Efficiency Toilet
- · Gravity fed, jetted box rim
- 2" fully glazed trapway
- High performance 3" flush valve
- 9" x 7" water surface
- Close coupled tank with cover
- Quick connect, 2 bolt tank to bowl installation

- Standard chrome trip lever
- Available in round front, chair height round front, elongated and ADA elongated
- Seat and supply not included
- Anti-siphon fill valve
- Sanitary Bar on all bowls
- Uses 20% less water than standard low consumption toilets



PF1503WH/PF6112WH

Codes and Standards

- ADA (PF1503WH)
- IAPMO/cUPC
- ASME A112.19.2 / CSA B45.1-13
- EPA WaterSense Certified
- MaP tested 1000g
- LEED Compliant

Model Numbers

PF1500WH Round Front HET Bowl, White

PF1500CHWH Round Front HET Chair Height Bowl, White

PF1501WH Elongated HET Bowl, White PF1503WH ADA Height HET Bowl, White

 PF6112WH
 1.28 HET Tank w/ 12" RI for PF1500 series

 PF6110WH
 1.28 HET Tank w/ 10" RI for PF1500 series

 PF6114WH
 1.28 HET Tank w/ 14" RI for PF1500 series

 PF6112RWH
 1.28 RH Tank w/ 12" RI for PF1500 series







High-Efficiency Toilet



Product Specification


The combination toilet shall be made of vitreous china. Toilet shall be 1.28 gpf (4.8 lpf). Toilet shall have 2" (5.1cm) fully glazed trapway. Toilet shall include chrome trip lever. Toilet shall be less seat and supply. Toilet shall be ADA compliant (PF1503) with 17" high bowl.


	RF	RF CH	EL	ADA
	PF1500/PF6112	PF1500CH/PF6112	PF1501/PF6112	PF1503/PF6112
Α	30"	31-1/2"	30"	31-1/2"
В	16-1/2"	16-1/2"	18-1/2"	18-1/2"
С	15-1/2"	17"	15-1/2"	17"
D	27"	27"	29"	29-1/4"
Е	10"	10"	9-7/8"	10"
F	20-5/8"	21"	21-3/8"	21"
G	8"	8"	8"	8"
Н	12"	12"	12"	12"

	PF1500/PF6110	PF1500CH/PF6110	PF1501/PF6110	PF1503/PF6110
D	26-1/4"	26"	27-7/8"	28-1/8"
G	6-3/4"	6-3/4"	6-3/4"	6-3/4"
Н	10"	10"	10"	10"

	PF1500/PF6114	PF1500CH/PF6114	PF1503/PF6114	PF1503/PF6114
D	29-7/8"	29-1/3"	31-3/8"	31-3/8"
G	10-1/4"	10-1/4"	10-1/4"	10-1/4"
Н	14"	14"	14"	14"

Note: All dimensions and specifications are nominal and may vary: Dimensions of 8" and greater have a tolerances of +3%. Dimensions less than 8" have a tolerances of +5%.





Warranty and Codes

This product comes complete with installation, operating, care and maintenance instructions. All PROFLO fixtures carry a 1-year limited warranty. This product meets or exceeds ASME/ANSI A112.19.2M. In an effort to continually improve our products, we will make design changes from time to time. We reserve the right to ship newly designed product to fill any order unless we agree in writing to do otherwise.





