PFXPG SERIES Dual Scale Pressure Gauge



Product Features

- · Accuracy: ± 2.5% of span (grade B ANSI B40.1)
- · 1/4" NPT brass connection (lower mount)
- · Black corrosion-resistant paint steel case with flat glass window
- · Dual scale: 0-100psi/0-700kpa
- · Bourdon tube style
- · Operating temperature: Ambient: -4 °F to 140 °F (-20 °C to 60 °C) Media: Max. 158 °F (70 °C)
- · Low lead compliant
- Liquid filled additional features (PFXPGLF100K):
 300 Series stainless steel, with removable nipple for venting, pressure relief and liquid-fill access standard liquid Glycerin

For use with air, gas or water applications and medium that will not clog the connection port or corrode the copper alloy (examples: hydraulic and pneumatic systems, pumps, compressors, water systems and regulator).




PFXPG100K


Model Numbers:

PFXPG100K 2" Pressure gauge 0-100psi/0-700kpa **PFXPGLF100K** 2" Liquid filled gauge 0-100psi/0-700kpa

Product Specifications







Liquid Filled PFXPGLF100K

Warranty and Codes

This product comes complete with installation, operating, care and maintenance instructions. This PROFLO product carries a 1-year limited warranty.

