PF92952 Pre-Assembled Primary / Backup Sump Pump Kit



- · Rugged cast iron pump body for durability
- SJE Rhombus vertical float switch
- 1-1/2" NPT Discharge
- Handles up to 1/2" solids
- · Clog resistant impeller
- · Carrying handle attached
- 10' power supply cord

Backup Pump Features

- 12 Volt DC pump
- SJE Rhombus vertical float switch
- Maximum flow rate 23 gpm.
- 1-1/2" NPT discharge size.

Kit Features

- · Electric control panel with indicator liahts
- Thermoplastic battery box
- 87 decibel alarm with mute
- Reverse polarity protection
- Low battery alarm

- · Built-in thermal overload protection
- for safety · Permanent split capacitor
- continuous duty motor
- 5.9 amps. 708 Watts
- 3450 RPM
- Handles 1/8" solids.
- Clog resistant impeller
- AC charger
- Pre-assembled with PVC pipe and fittinas



1/3HP 120 Volt AC (5.9 amps)

Performance Chart									
Lift	0'	5'	10'	15'	20'	25'			
GPM GPH	60 3600	56	50	35	15	6			
GPH	3600	3360	3000	2100	900	360			

Backup Motor Performance

• 12 Volt DC

Performance Chart									
Lift	0'	5'	10'	15'	20'				
GPM	23	22	18	13	8				
GPH	1380	1320	1080	780	480				


Warranty and Codes

This product comes complete with installation, operating, care and maintenance instructions. This PROFLO sump pump carries a 3 year warranty when installed in residential applications. See owners manual for warranty details.

This PROFLO sump pump carries a 3 year limited warranty. In an effort to continually improve our products, we will make design changes from time to time. We reserve the right to ship newly designed product to fill any order unless it is agreed in writing to do otherwise.

PF92952





* All measurements are nominal. Please verify before actual installation.



- Two full flow check valves