

Twistlock Extension Cord

RAP41201



Model Numbers

RAP41201 100FT 12/3 SJTW YELLOW TWIST-TO-LOCK
EXTENSION CORD - 20AMPS

Product Features

- **Water Resistant** – Jacket will not absorb water that can corrode copper conductors or cause dangerous electrical shocks
- **Flame Retardant** – Jacket compound is designed to not allow burning to spread. The compound is formulated to cause the flame to burn out before spreading further on the cord.
- **Superior Flexibility at Sub-Freezing Temperatures** – This cord is designed to maintain flexibility and resist cracking in temperatures down to -40°F (-40°C) and resists heat up to 140°F (60°C).
- **OSHA Approved** – Meets OSHA requirements for extension cords and adapters for use on jobsites. Meets requirements for California and other applications (generators and temporary power boxes) where twist-to-lock plugs are specified.
- **cULus** – Tested to both U.S. and Canadian standards
- **NEMA Plug Configuration** – L5-20 to L5-20R
- **Electrical Ratings** – 15A/125V/1875W

Warranty

Subject to the limitations expressed herein, Seller warrants to the original Buyer that hand tools manufactured and sold by Seller ("Tool") shall be free from defects in design, material and workmanship under Normal Use for the life of tool. This warranty is void for any damage caused by misuse, abuse, neglect, or acts of God. For the purpose of this section, "Normal Use" means in strict accordance with any documentation describing safe practices used by a professional tradesman in the industry.