



WhisperWarm™ Lite - Quiet, Fan/Heater/Light Solution, 110 CFM

FV-11VHL2

• MORE DETAILS

- Static Pressure (in inches w.g.) 0.1
0.25
- Air Volume (CFM) 110 @ 0.1" static pressure
89 @ 0.25" static pressure
- Noise (sones) 0.7 at 0.1" static pressure
- Power Consumption (Watts) 30.6 at 0.1" static pressure
30.5 at 0.25" static pressure
- Energy Efficiency (CFM's/Watt) 3.6 at 0.1" static pressure
2.9 at 0.25" static pressure
- Speed (RPM) 812 at 0.1" static pressure
956 at 0.25" static pressure
- Current (Amps) 0.25 at 0.1" static pressure
0.25 at 0.25" static pressure
- Combined Amps 12.5
- Power Rating (V/Hz) 120/60
- Motor Type Condenser
- Type of Motor Bearing Ball
- Thermal Fuse Protection Yes
- Blower Wheel Type Sirocco
- Duct Diameter (inches) 4"
- Mounting Opening (inches sq.) 17 3/8" x 12 5/8"
- Grille Size (inches sq.) 18 1/8"L x 13 5/16"W
- Light Yes
- Lamp Watts 2 x 18 watts
- Lamp Color Rendering Index 84

- **Lamp Color Temp. (Kelvin) 3500**
- **Lamp Rated Average Life (hrs) 10,000**
- **Lamp Model # FDS18E35/4**
- **Night Light Yes**
- **Night Light Lamp Watts 4**
- **Heater Yes**
- **Heater Stainless Steel Sheathed Element Yes**
- **Heater Directional Louver No**
- **Heating Element Watts 1400**
- **Heater Blower Fan (CFM) 90**
- **Heater Blower Fan (Watts) 25**
- **UL Listed for Tub/ Shower Enclosure No**
- **Washington State VIAQ Code Yes**
- **California Title 24 Compliant Yes**
- **Mfg in ISO 9001 Certified Facility Yes**
- **Gross Weight (lbs.) 22.7**

-
- ◦ **UPC037988870660**
-