

Features

- 36-inch minimum base cabinet width.
- Large/medium bowls.
- 9 3/4-inch left depth and 7 3/4-inch right depth.
- Three oversized faucet holes with one oversized accessory hole to the right.
- Oversized holes allow for easy installation of faucets and accessories.
- Offset faucet ledge.

Material

• KOHLER[®] enameled cast iron.

Installation

Undermount.

Recommended Products/Accessories

K-6001 Left-Bowl Sink Rack K-6539 Drainboard with Sink Rack K-8801 Sink Strainer K-8799 Sink Strainer K-23726 Drain treatment K-23725 Cast iron cleaner 1411886 Undermount sink kit 23"

Optional Products/Accessories

K-6521 Sink Basket K-6515 Cutting Board K-11352 Disposal Flange with Stopper K-9000 P-Trap



Codes/Standards

ASME A112.19.1/CSA B45.2

KOHLER[®] Enameled Cast Iron Kitchen Sink Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White
	FF	Sea Salt™
	96	Biscuit
	47	Almond
	NY	Dune
	95	lce™ Grey
	K4	Cashmere
	FT	Basalt
	58	Thunder™ Grey
	FP	Caviar
	7	Black Black™



Executive Chef[™]

Under-Mount Kitchen Sink K-5931-4U


Notes **Technical Information** All product dimensions are nominal. Bowl configuration: Off-set Large/small Installation: Undermount Min. base cabinet 36" (914 mm) width: Bowl area (Left): Length: 16" (406 mm)

Width: 19" (483 mm) Bowl depth: 9-3/4" (248 mm) Length: 12" (305 mm) Bowl area (Right): Width: 17" (432 mm) Bowl depth: 7-3/4" (197 mm) Number of deck holes: 4 Faucet hole spacing: 4" (102 mm) Faucet hole(s): 2-3/8" (60 mm) Drain hole: 3-5/8" (92 mm) Template: 116808-7, required, included

Install this product according to the installation instructions.

Under-Mount Kitchen Sink

K-5931-4U





16"



Executive Chef[™]