

### Features

- 27-inch minimum base cabinet width.
- Single bowl.
- 9" (229 mm) depth provides generous workspace.
- Rear drain increases workspace in the sink and allows for more storage space underneath the sink.
- SilentShield<sup>®</sup> sound-absorption technology offers quieter performance.
- Includes a combination dishcloth bar/utility shelf and a bottom sink rack.
- Includes installation hardware.
- Rounded 10mm corners are easy to clean.

#### Material

- Handcrafted from 16-gauge stainless steel.
- Premium 16-gauge stainless steel.

### Installation

- No faucet holes.
- Undermount.

## **Recommended Products/Accessories**

K-6645 Sink Rack K-8801 Sink Strainer K-8799 Sink Strainer K-23726 Drain treatment K-23729 Stainless steel cleaner

## **Optional Products/Accessories**

K-11352 Disposal Flange with Stopper

### **Included Components**

Additional Components: Cut-out template Hardware kit



# Codes/Standards


ASME A112.19.3/CSA B45.4

Lifetime Limited Warranty for KOHLER<sup>®</sup> Stainless Steel Sinks See website for detailed warranty information.





# Strive® Under-Mount Kitchen Sink K-5286



## **Technical Information**

All product dimensions are nominal.	
Bowl configuration:	Single
Installation:	Under-mount
Min. base cabinet width:	27" (686 mm)
Bowl area:	Length: 22-1/4" (565 mm) Width: 16-1/2" (419 mm) Bowl depth: 9-5/16" (237 mm) Water depth: 9" (229 mm)
Template:	1207218-7, required, included

#### Notes

Install this product according to the installation instructions.

