CLEANOUTS

How to Order

FLOOR CLEANOUTS — Unless optional materials are specified, standard material shown in Specification will be provided.

Example: Series No. 55000			Туре	No. 55	004
	55004	-Z 	- 1	-VP	-22
Outlet Size —					
Outlet Type, No Hub Outlet —					
Optional Material, Satin Finish Nikaloy Top —					
Option, Secured Cover, Vandal-Proof Screws —					
Option, Taper Thread Bronze Plug					

WALL OR FLOOR ACCESS COVERS — When outlet size does not apply, refer to dimension table for Type No. to be ordered.

Example: Series No. 58630		T	ype No. 5	8631
	58631	-CO3	-20	-VF
Type No. for 8" x 8" Cover—				
No-Hub Cleanout, 3" —				
Raised Head Bronze Plug —				
Secured Cover, Vandal-Proof Screws —				

CLEANOUTS • Pictorial Selection Guide







55000 SERIES

LEVELEZE® KLEENATRON® II SPECIAL-DUTY

APPLICATION

For use in finished or unfinished floors subject to heavy wheel traffic such as warehouses, loading docks and warehouse stores. Top design allows for unimpaired adjustment even as the floor is being poured.

SPECIFICATION

JOSAM 55000 Series coated cast iron LEVELEZE® KLEENATRON® II Floor Cleanout, internal ABS cleanout plug, adjustable cast iron housing with special-duty scoriated secured round cast iron cover.


Available Options

- ▼ -1 Satin Finish Nikaloy Top
 ▼ -1-SD Special-Duty Satin Finish Nikaloy Top
- ▼ -1-SQ Square Top, Satin Finish Nikaloy
- ▼ -1-12 Cover Recessed for Tile, Satin Finish Nikaloy
- ▼ -1-13 Terrazzo Tile Cover, Satin Finish Nikaloy
 - -2 Satin Finish Bronze Top
 - -2-SD Special-Duty Satin Finish Bronze Top
 - -2-SQ Square Top, Satin Finish Bronze
 - -2-12 Cover Recessed for Tile, Satin Finish Bronze
 - -2-13 Terrazzo Tile Cover, Satin Finish Bronze
 - -SS Stainless Steel Top

- -SS-SQ Square Top, Stainless Steel
- ▼ -5 Ductile Iron Top
 - -14 Carpet Cleanout Marker
 - -VP Secured Cover, Vandal-Proof Screws
 - -22 Taper Thread Bronze Plug
 - -31 Galvanized Cast Iron Parts
 - -41 Clamp Ring and Flange
 - -F Flange Only
 - -WF Wide Flange (not available on CI)
 - -CFC Carpet Cleanout Flange Cover

OUTLETS:

- -X Inside Caulk Outlet
- -Y Hub Outlet w/Gasket, 2"-4"
- -Z No-Hub Outlet



FLANGE STANDARD ON 4" -X AND 6" SIZES.

FOR OUTLET TYPE SPECIFY -X, -Y or -Z								
TYPE NO.	PIPE SIZE	Α	В	C*	D	Х	Υ	LBS.
55002	2	6	3-3/4	7-1/2	5-9/16	2-3/4	4-1/4	15
55003	3	6	3-3/4	7-1/2	5-9/16	2-3/4	4-1/4	15
55004	4	6	3-3/4	7-1/2	5-9/16	2-3/4	4-1/4	16
55004-X	4	7-1/2	4-1/4	9-3/16	7	2-5/8	4-5/16	18
55005-Z	5	6	3-3/4	7-1/2	5-9/16	2-3/4	4-1/4	16
55006-Z	6	7-1/2	4-1/4	9-3/16	7	2-5/8	4-5/16	18

55000-1 SERIES


APPLICATION

For use in finished floors subject to pedestrian and light wheel traffic such as schools, hospitals and shopping malls. Top design allows for unimpaired adjustment even as the floor is being poured.

SPECIFICATION

JOSAM 55000-1 Series coated cast iron LEVELEZE® KLEENATRON® II Floor Cleanout, internal ABS cleanout plug, adjustable cast iron housing with medium-duty scoriated secured round satin Nikaloy cover.

with -1 Nikaloy Top



* FLANGE STANDARD ON 4" -X AND 6" SIZES.

FOR OUTLET TYPE SPECIFY -X, -Y or -Z								
TYPE NO.	PIPE SIZE	Α	В	C*	D	Х	Υ	LBS.
55002-1	2	5-1/8	3-3/4	7-1/2	5-9/16	2-1/8	3-5/8	12
55003-1	3	5-1/8	3-3/4	7-1/2	5-9/16	2-1/8	3-5/8	12
55004-1	4	5-1/8	3-3/4	7-1/2	5-9/16	2-1/8	3-5/8	13
55004-1-X	4	6-5/8	4-1/4	9-3/16	7	2	3-11/16	14
55005-1-Z	5	5-1/8	3-3/4	7-1/2	5-9/16	2-1/8	3-5/8	12
55006-1-Z	6	6-5/8	4-1/4	9-3/16	7	2	3-11/16	14