

20V MAX* DRILL/DRIVERS

Compact Drill/Driver

200 USA

DCD780B



SPECIFICATIONS	
Voltage	20V MAX*
Max Power	350 UW0
# of Speed Settings	2
No Load Speed	0-600/0-2000 rpm
Chuck Size	1/2"
Chuck Type	Metal, Ratcheting
Tool Weight (Tool only)	3.4 lbs
Includes	Belt Hook

AVAILABLE	
DCD780B	Batteries and Charger Sold Separately
DCD780C2	Also Includes: (2) 20V MAX* Lithium Ion Batteries (1.5 Ah), Charger, and Kit Bag



DCD780C2

Brushless Compact Drill/Driver Kit



DCD777C2	
	DOWALK MANAGEMENT
To be	

SPECIFICATIONS	
Voltage	20V MAX*
Max Power	340 UW0
# of Speed Settings	2
No Load Speed	0-500/0-1750 rpm
Chuck Size	1/2"
Chuck Type	Plastic, Ratcheting
Tool Weight (Tool only)	3.5 lbs
Includes	(2) 20V MAX* Lithium lon Batteries (1.5 Ah), Charger, and Kit Bag

Compact Drill/Driver Kit DCD771C2



SPECIFICATIONS	
Voltage	20V MAX*
Max Power	300 UW0
# of Speed Settings	2
No Load Speed	0-450/0-1500 rpm
Chuck Size	1/2"
Chuck Type	Plastic, Ratcheting
Tool Weight (Tool only)	3.6 lbs
Includes	(2) 20V MAX* Lithium lon Batteries (1.5 Ah), Charger, and Kit Bag

3/8" Right Angle Drill/Driver DCD740B

20v



SPECIFICATIONS	
Voltage	20V MAX*
Max Power	340 UW0
# of Speed Settings	2
No Load Speed	0-650/0-2000 rpm
Chuck Size	3/8"
Chuck Type	Keyless / Ratcheting
Tool Weight (Tool only)	3.0 lbs
Includes	Belt Hook and 2" Phillips Bit Tip

AVAILABLE DCD740B Batteries and Charger Sold Separately Also Includes: (1) 20V MAX* Lithium Ion Battery (1.5 Ah), Charger, and Kit Box DCD740C1



DCD740C1

XR® Brushless Tool Connect™ 1/4" Impact Driver



20v







SPECIFICATIONS Voltage 20V MAX* 1/4" **Drive Size** Drive Type Quick Release Hex No Load Speed 0-1000/0-2800/0-3250 rpm Impacts / Minute 0-3600 ipm Max Torque 0-240/0-1500/0-1825 in-lbs Max Torque 0-20/0-125/0-152 ft-lbs LEDs Yes, 3 Tool Length 5.3" Tool Weight (Tool only) 2.0 lbs

AVAILABLE	
DCF888B	Batteries and Charger Sold Separately
DCF888D2	Also Includes: (2) 20V MAX* Lithium Ion Batteries (2.0 Ah), Charger, and Kit Box
DCF888P2BT	Also Includes: (2) 20V MAX* XR® Tool Connect™ Lithium Ion Batteries (5.0 Åh), Charger, and Kit Box





DCF888D2

DCF888P2BT

XR® Brushless 1/4" 3-Speed Impact Driver DCF887B



20v X

Driver

ľ	IISA=	
	WITH GLOBAL MATERIALS	

SPECIFICATIONS	
Voltage	20V MAX*
Drive Size	1/4"
Drive Type	Quick Release Hex
No Load Speed	0-1000/0-2800/0-3250 rpm
Impacts / Minute	0-3600 ipm
Max Torque	0-240/0-1500/0-1825 in-lbs
Max Torque	0-20/0-125/0-152 ft-lbs
LEDs	Yes, 3
Tool Length	5.3"
Tool Weight (Tool only)	2.0 lbs
Includes	Belt Hook

Belt Hook

AVAILABLE	
DCF887B	Batteries and Charger Sold Separately
DCF887D2	Also Includes: (2) 20V MAX* Lithium Ion Batteries (2.0 Ah), Charger, and Kit Box
DCF887M2	Also Includes: (2) 20V MAX* XR® Lithium Ion Batteries (4.0 Ah), Charger, and Kit Box





DCF887D2

DCF887M2