# PRODUCTS

## Manufactured by Vanderlans & Sons, Inc.

MULTI-SIZE FLOW-THRUSTM

#### THE MULTI-SIZE FLOW-THRUS™

are built with the same patented designs as our Domehead™ plugs (see page 3 for design characteristics). The Flow-Thru™ plug goes one step further by offering a large by-pass within the pipe plug. The by-passes are ideal for doing a water test or sewer by-pass. Lansas Flow-Thru™ plugs are available with standard by-passes up to 8" NPT. 12" threaded connections and larger flanged connections can be special ordered. As with any Lansas plug, the Multi-Size Flow-Thru's™ can be manufactured with nitrile or neoprene rubber and with stainless steel components for use in chemical and petroleum applications. Convert your Flow-Thru™ Plug for air testing applications with a simple conversion cap (see page 37). A PVC cap is supplied with each plug with up to a 6" NPT by-pass.



**Custom Designs** Are Always™Available



Part No. 094-1218 Part No. 098-1218 Two 12" X 18" Multi-Size Flow-Thru™ Plugs are shown; one with a 4" by-pass, the other with an 8" by-pass.



## 5-Line™ MULTI-SIZE INTERCHANGE™ PLUGS





LANSAS New 5-Line™ Multi-Size INTER-CHANGE™ Plugs are equipped with our new RP2 Rupture Protection pressure relief valve. These plugs have a new and improved design made with a newly reformulated rubber blend and with more plug sizes and cover sizes available.

The LANSAS 5-Line™ Multi-Size INTER-CHANGE™ Plug has interchangeable covers. The plugs can be equipped with standard or custom covers, we will build the exact by-pass cover needed to fit your application. LANSAS 5-Line™ Multi-Size INTER-CHANGE™ Plug sizes start at our 15"-21" Multi-Size unit up to as large as 96" in diameter. The bolt-on covers can be equipped with threaded by-pass connections up to 12" (M) NPT, flanged connections or an open tube end for use as a SUPER-FLOW™

## SINGLE & MULTI-SIZE SUPER FLOWTM PLUGS

#### THE LANSAS SUPER-FLOW™ PIPE PLUGS

are designed with the largest by-passes available. These pipe plugs are excellent for use in flow diversion and manhole rehabilitation projects. Field replaceable bladders now avaliable.



A "TEE" configuration with three plugs, three hoses and a "TEE" fitting.



## THE NEW LANSAS SMART-BOX™ Super-Flow™ By-Pass Kit

Each complete kit contains the following:

- (2) Multi-Size SUPER-FLOW™ Plugs
- (2) 30 ft. Standard Inflation Kits with Gauge (Part No. 321-30)
- (1) 5 ft. By-Pass Hose
- (1) High Pressure Hand Pump (Part No. 310-00)
- Black Plastic Storage Container

Part No. 186-610 ............. (2) 185-610 Multi-Size Super-Flow™ Plug Part No. 186-812 ...... (2) 185-812 Multi-Size Super-Flow™ Plug Part No. 186-1016 ....... (2) 185-1016 Multi-Size Super-Flow™ Plug

(Please note that other plug sizes and by-pass hose lengths are available upon request, but may not fit into the supplied storage container)



Shown with two 24" Super -Flow™ Plugs and optional 20" by-pass hose



### **ITEM 6 & 7 IN PRICE LIST**

MULTI-SIZE FLOW-THRU™ PLUG									
	RANGE OF USE				BYPASS		PRODUCT DIMENSIONS		
PART NUMBER	MINIMUM PIPE DIAMETER	MAXIMUM PIPE DIAMETER	REQUIRED INFLATION PRESSURE	MAXIMUM BACK/TEST PRESSURE	SIZE (S-Soft or H-Hard)	LENGTH	DEFLATED DIAMETER	WEIGHT	
092-48	3.8"	8.25"	30 psi	15 psi	2" - H	16.0"	3.5"	6.5 lbs.	
093-610	5.3"	10.25"	30 psi	15 psi	3" - H	20.0"	5.0"	15 lbs.	
092-812	7.3"	12.25"	25 psi	15 psi	2" - H	20.0"	7.0"	15 lbs.	
094-812	7.3"	12.25"	25 psi	15 psi	4" - H	20.0"	7.0"	20 lbs.	
096-812	7.3"	12.25"	25 psi	15 psi	6" - H	22.0"	7.0"	27 lbs.	
094-1016	9.5"	16.25"	25 psi	15 psi	4" - H	28.0"	9.3"	36 lbs.	
096-1016	9.5"	16.25"	25 psi	15 psi	6" - H	28.0"	9.3"	40 lbs.	
094-1218	11.0"	18.25"	25 psi	15 psi	4" - H	28.0"	10.5"	46 lbs.	
096-1218	11.0"	18.25"	25 psi	15 psi	6" - H	28.0"	10.5"	48 lbs.	
098-1218	11.0"	18.25"	25 psi	15 psi	8" - H	28.0"	10.5"	50 lbs.	
094-1224	11.0"	24.25"	25 psi	15 psi	4" - H	41.0"	10.5"	71 lbs.	
096-1224	11.0"	24.25"	25 psi	15 psi	6" - H	41.0"	10.5"	76 lbs.	
098-1224	11.0"	24.25"	25 psi	15 psi	8" - H	41.0"	10.5"	79 lbs.	
094-1530	14.0"	30.25"	20 psi	8 psi	4" - S	52.0"	13.5"	69 lbs.	
094-1530H	14.0"	30.25"	20 psi	8 psi	4" - H	52.0"	13.5"	130 lbs.	
096-1530	14.0"	30.25"	20 psi	8 psi	6" - H	52.0"	13.5"	130 lbs.	
098-1530	14.0"	30.25"	20 psi	8 psi	8" - H	52.0"	13.5"	135 lbs.	
094-2036	19.0"	36.25"	20 psi	8 psi	4" - S	64.0"	18.5"	117 lbs.	
094-2036H	19.0"	36.25"	20 psi	8 psi	4" - H	52.0"	18.5"	155 lbs.	
096-2036	19.0"	36.25"	20 psi	8 psi	6" - H	52.0"	18.5"	160 lbs	
098-2036	19.0"	36.25"	20 psi	8 psi	8" - H	52.0"	18.5"	165 lbs.	
094-2448	22.0"	48.25"	15 psi	8 psi	4" - S	84.0"	21.5"	133 lbs.	
096-2448	22.0"	48.25"	15 psi	8 psi	6" - S	84.0"	21.5"	195 lbs.	
098-2448	22.0"	48.25"	15 psi	8 psi	8" - S	84.0"	21.5"	227 lbs.	
094-3660	34.5"	60.25"	10 psi	6 psi	4" - S	84.0"	29.5"	208 lbs.	
096-3660	34.5"	60.25"	10 psi	6 psi	6" - S	84.0"	29.5"	237 lbs.	
098-3660	34.5"	60.25"	10 psi	6 psi	8" - S	84.0"	29.5"	274 lbs.	
094-4278	37.0"	78.25"	10 psi	6 psi	4" - S	101.0"	37.0"	335 lbs.	
096-4278	37.0"	78.25"	10 psi	6 psi	6" - S	101.0"	37.0"	367 lbs.	
098-4278	37.0"	78.25"	10 psi	6 psi	8" - S	101.0"	37.0"	408 lbs.	
094-4872	46.0"	72.25"	10 psi	6 psi	4" - S	84.0"	43.5"	340 lbs.	
096-4872	46.0"	72.25"	10 psi	6 psi	6" - S	84.0"	43.5"	380 lbs.	
098-4872	46.0"	72.25"	10 psi	6 psi	8" - S	84.0"	43.5"	410 lbs.	
094-6096	58.0"	96.25"	10 psi	6 psi	4" - S	110.0"	56.0"	537 lbs.	
096-6096	58.0"	96.25"	10 psi	6 psi	6" - S	110.0"	56.0"	570 lbs.	
098-6096	58.0"	96.25"	10 psi	6 psi	8" - S	110.0"	56.0"	598 lbs.	

#### **ITEM 15 IN PRICE LIST**

SINGLE-SIZE & MULTI-SIZE SUPER-FLOW™ PLUGS								
RANGE OF USE					PRODUCT DIMENSIONS			
PART NUMBER	MINIMUM PIPE DIAMETER	MAXIMUM PIPE DIAMETER	REQUIRED INFLATION PRESSURE	MAXIMUM BACK/TEST PRESSURE	BYPASS SIZE	LENGTH	DEFLATED DIAMETER	WEIGHT
SINGLE-SIZED MODELS								
180-04	3.8"	4.25"	25 psi	10 psi	3"	12.0"	3.5"	6 lbs
180-06	5.0"	6.25"	25 psi	10 psi	4"	14.0"	4.5"	9 lbs.
180-08	7.0"	8.25"	25 psi	10 psi	6"	16.0"	6.5"	15 lbs.
180-10	9.0"	10.25"	25 psi	10 psi	8"	20.0"	8.5"	24 lbs.
180-12	11.0"	12.25"	25 psi	10 psi	10"	20.0"	10.5"	33 lbs.
180-15	13.0"	16.25"	25 psi	10 psi	12"	20.0"	12.8"	40 lbs.
180-18	17.0"	18.25"	25 psi	10 psi	16"	20.0"	16.8"	50 lbs.
180-20	19.0"	21.25"	25 psi	10 psi	18"	20.0"	18.8"	63 lbs.
180-24	22.0"	24.25"	25 psi	10 psi	20"	20.0"	20.8"	70 lbs.
			MULTI-	SIZE MODELS				
185-48	3.8"	8.25"	25 psi	10 psi	3"	18.0"	3.5"	7 lbs.
185-610	5.0"	10.25"	25 psi	10 psi	4"	22.0"	4.5"	13 lbs.
185-812	7.0"	12.25"	25 psi	10 psi	6"	22.0"	6.5"	19 lbs.
185-1016	9.0"	16.25"	25 psi	10 psi	8"	26.0"	8.8"	29 lbs.
185-1218	11.0"	18.25"	25 psi	10 psi	10"	26.0"	10.8"	38 lbs.
185-1421	13.0"	21.25"	25 psi	10 psi	12"	30.0"	12.8"	67 lbs.
185-1824	17.0"	24.25"	25 psi	10 psi	16"	30.0"	16.8"	79 lbs.
185-2030	19.0"	30.25"	25 psi	10 psi	18"	36.0"	18.8"	92 lbs.
185-2436	22.0"	36.25"	25 psi	10 psi	20"	55.0"	22.0"	176 lbs.

**ITEM 9 IN PRICE LIST** 

		MULTI-SIZE INTERCHANGE PLUGS							
	0.	RANGE OF USE				PRODUCT DIMENSIONS			
PART NUMBE	R	MINIMUM PIPE DIAMETER	MAXIMUM PIPE DIAMETER	REQUIRED INFLATION PRESSURE	MAXIMUM BACK/TEST PRESSURE	LENGTH	DEFLATED DIAMETER	WEIGHT	
595-152	21	14.25"	21.25"	20 psi	10 psi	24.0"	14.0"	44 lbs.	
595-153	30	14.25"	30.25"	20 psi	10 psi	42.0"	14.0"	88 lbs.	
595-182	24	16.25"	24.25"	20 psi	10 psi	24.0"	16.0"	57 lbs.	
595-243	36	23.25"	36.25"	20 psi	10 psi	30.0"	22.0"	110 lbs.	
595-364	18	34.25"	48.25"	20 psi	10 psi	30.0"	34.0"	160 lbs.	
595-486	50	46.25"	60.25"	20 psi	10 psi	30.0"	46.0"	216 lbs.	
595-607	72	58.25"	72.25"	20 psi	10 psi	30.0"	58.0"	272 lbs.	
595-728	34	70.25"	84.25"	20 psi	10 psi	30.0"	70.0"	329 lbs.	

All plugs are sold without a cover. Choose a cover for the appropriate size plug below. All covers are fabricted steel. Adapter Plate sold seperatly

COVERS FOR 15"X 21"					
AND 15"X 30" PLUGS					
PART NUMBER	BY-PASS SIZE				
599-15-04T	4" (M) NPT				
599-15-06T	6" (M) NPT				
599-15-06T	8" (M) NPT				
599-15-06T	10" (M) NPT				
599-15-06T	12" (M) NPT				
599-15-06T	8" TUBE				
599-15-06T	10" TUBE				
599-15-06T	12" TUBE				
599-15-06T	8" FLANGE				
599-15-06T	10" FLANGE				
599-15-06T	12" FLANGE				

COVERS FOR 18	3"X24" PLUGS
PART NUMBER	BY-PASS SIZE
599-18-04T	4" (M) NPT
599-18-06T	6" (M) NPT
599-18-08T	8" (M) NPT
599-18-10T	10" (M) NPT
599-18-12T	12" (M) NPT
599-18-08SF	8" TUBE
599-18-10SF	10" TUBE
599-18-12SF	12" TUBE
599-18-14SF	14" TUBE
599-18-08FG	8" FLANGE
599-18-10FG	10" FLANGE
599-18-12FG	12" FLANGE
599-18-14FG	14" FLANGE

COVERS FOR 24	PLUGS
PART NUMBER	BY-PASS SIZE
599-24-04T	4" (M) NPT
599-24-06T	6" (M) NPT
599-24-08T	8" (M) NPT
599-24-10T	10" (M) NPT
599-24-12T	12" (M) NPT
599-24-08SF	8" TUBE
599-24-10SF	10" TUBE
599-24-12SF	12" TUBE
599-24-14SF	14" TUBE
599-24-16SF	16" TUBE

COVERS FOR 24	I"X36" PLUGS
PART NUMBER	BY-PASS SIZE
599-24-18SF	18" TUBE
599-24-20SF	20" TUBE
599-24-08FG	8" FLANGE
599-24-10FG	10" FLANGE
599-24-12FG	12" FLANGE
599-24-14FG	14" FLANGE
599-24-16FG	16" FLANGE
599-24-18FG	18" FLANGE
599-24-20FG	20" FLANGE