

### M12<sup>™</sup> Spot Polisher Kit

2438-22X, 2438-22 (2438-20 Tool-Only) **Specifications:** 

Polishing RPM	0 - 2,800
Sanding RPM	0 - 8,300
Length / Weight	5.1" / 2.4 lbs

RPM

Arbor

Weight

**Includes: 2438-22X** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> XC3.0 Battery Pack, (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Pack; 2438-22 (2) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Packs; All Kits Include: 5 Pc Accessory Pack, Side Handle, Charger, Soft Carrying Case



**Includes:** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> XC4.0 Battery Pack, Circular Saw Blade, Wrench, Charger, Contractor Bag

6.2 lbs



### M12 FUEL HACKZALL® One-Handed **Recip Saw Kit**

	520-21XC (2520-2 pecificatio		Milwanker
	SPM	0 – 3,000	
5	Stroke Length	5/8"	
	Keyless Blade Clamp	QUIK-LOK <sup>™</sup> (Accepts all SAWZALL <sup>®</sup> Blad	es)
L	_ength / Weight	13.3" / 4.1 lbs	

Includes: (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> XC4.0 Battery Pack, HACKZALL® Blade, Charger, Contractor Bag

### M12<sup>™</sup> HACKZALL<sup>®</sup> One-Handed **Recip Saw Kit** 0400 01 (0400 00 T

2420-22, 2420-21 (2420-20 Tool-Only)		and the second second
<b>Specificatio</b>	ns:	
SPM	0-3,000	
Stroke Length	1/2"	
Keyless Blade Clamp	QUIK-LOK <sup>™</sup> (Accepts all SAWZALL <sup>®</sup> Blac	des)
Length / Weight	11.0" / 2.6 lbs	

Includes: 2420-22 (2) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Packs; **2420-21** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Pack; All Kits Include: (2) HACKZALL® Blades, Charger, Contractor Bag



45° (Positive Locks QUIK-LOK<sup>™</sup> T-Shank Blade Clamp Length / Weight 8.8" / 4.2 lbs

Includes: (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Pack, 10 TPI Wood Cutting T-Shank Jig Saw Blade, Anti-Splintering Insert, Non-Marring Shoe, Charger, Contractor Bag

### M12<sup>™</sup> Multi-Tool Kit

2426-22, 2426-21 (2426-20 Tool-Only)

Specifications:	
Speed Settings	12
OPM	5,000 - 20,000
Universal Accessory Adapter	Yes
Length / Weight	10.9" / 2.1 lbs

Includes: 2426-22 (2) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Packs; **2426-21** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Pack; All Kits Include: Accessory Adapter, Wood Cutting Blade, Sanding Pad, (5) Assorted Sanding Sheets, Charger, Contractor Bag

M12 <sup>™</sup> Sub- Band Saw 2429-21XC (2429-2 Specification	<b>Kit</b> 0 Tool-Only)	
SFPM	280	
Blade Size	27"	SOLUTION
Cut Capacity	1-5/8" x 1-5/8"	Meets OSHA Guarding
Length / Weight	11.0" / 6.7 lbs	Requirements. Suitable for One-Handed Use.

Includes: (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> XC3.0 Battery Pack, 18 TPI Sub-Compact Portable Band Saw Blade, Charger, Carrying Case Related Accessories:

48-39-0572 18 TPI Sub-Compact Portable Band Saw Blades (3-Pack); 48-39-0711 12/14 TPI Extreme Metal Sub-Compact Portable Band Saw Blades (3-Pack)





# 

ł	3" Compac	t Cut-Off To	ool Kit 🛛 🚄
1	2522-21XC (2522-20 1	fool-Only)	
;	<b>Specifications</b>		
	Blade Size	3"	Milwautee
	RPM	20,000	
	Arbor Size	3/8"	
	Cut Depth	0.64"	
	Blade Rotation	Reversible	
	Length / Weight	8.9" / 2.4 lbs	

Includes: (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> XC4.0 Battery Pack, Dust Accessory Shoe, (3) Accessory Blades (Metal Cut-Off, Carbide Abrasive, Diamond Tile), Blade Wrench, Charger, Contractor Bag



### M12<sup>™</sup> Rotary Tool Kit

2460-21 (2460-20 Tool-Only) **Specifications:** 

Speed Settings	6
RPM	5,000 - 32,000
Collet	1/8", Universal
Length / Weight	9.5" / 1.3 lbs

Includes: (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Pack, (5) Cutting Wheels, Mandrel, Wrench, Charger, Soft Carrying Case

### **Related Accessory:**

49-94-1500 5 Pc Reinforced Cut-Off Wheels

### M12<sup>™</sup> 10 oz Caulk & **Adhesive Gun Kit**

2441-21 (2441-20 Tool-Only)

Weight

Specifications:		
Force	400 lbs	
Inches Per Minute	0 – 29	
Speed Settings	6	
Auto-Reverse Anti-Drin	Ves	



Includes: (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Pack, 10 oz Carriage, M12™ 10 oz Plunger Rod and Piston Assembly, Charger

4.1 lbs

### M12<sup>™</sup> 20 oz Aluminum Barrel Sausage **Style Caulk & Adhesive Gun Kit**

400 lbs	
0 – 29	
6	
Yes	
4.9 lbs	
	0 – 29 6 Yes

Includes: (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Pack, 20 oz Aluminum Sausage Style Barrel, M12<sup>™</sup> 20 oz Plunger Rod and Piston Assembly, Nozzle, Charger



## SYSTEM WIDE M12



### M12<sup>™</sup> Quart Caulk & Adhesive Gun Kit 2444-21

### Specifications:

Force	400 lbs
Inches Per Minute	0 – 29
Speed Settings	6
Auto-Reverse Anti-Drip	Yes
Weight	5.5 lbs



Includes: (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Pack, Quart Carriage, M12<sup>™</sup> Quart Plunger Rod and Piston Assembly, Charger



### **Caulk Gun Accessories**

Compatible with 2441-21, 2442-21, 2444-21 31-12-0700 Caulk Gun Nozzle - Black; 48-08-0900 M12<sup>™</sup> 10 oz Caulk and Adhesive Gun Conversion Kit; 48-08-0905 M12<sup>™</sup> 20 oz Aluminum Barrel Sausage Style Caulk and Adhesive Gun Conversion Kit; 48-08-0910 M12<sup>™</sup> Quart Caulk and Adhesive Gun Conversion Kit; 48-08-1091 20 oz Aluminum Barrel Kit; 48-08-1096 20 oz Clear Barrel Kit

### M12<sup>™</sup> Grease Gun Kit 2446-21XC (2446-20 Tool-Only)

### Specifications:

specificatio	15:	
Output Pressure	Over 8,000 PSI	
Run-Time	Up to 7 Grease Cartridges Per Charge	
Grease Capacity	14 oz Cartridge, 16 oz Bulk, 16 oz Suction	
Air Bleeder Valve	Yes	
Weight	7.2 lbs	

Includes: (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> XC3.0 Battery Pack, 36" Flex Hose with Spring Guard, Grease Coupler, Charger, Carrying Case



### M12<sup>™</sup> Soldering Iron Kit 2488-21 (2488-20 Tool-Only) **Specifications:**

750°F
90 Watts
18 Seconds
Yes
Chisel and Point
11.6" / 0.9 lbs



**Includes:** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Pack, Chisel Tip, Pointed Tip, Charger, Carrying Case

