

E-TRACK AND VAN INTERIOR ASSEMBLIES

To order non-standard interior van restraint assemblies specify:

- Overall length.
- Fixed Length.
- Cam Buckle or Ratchet Buckle.
- Spring-loaded E-Track, 3-piece E-Track, or any of the end fittings listed in Series 5,000 *Load Huggers* may be attached.
- E-Track only works with E-Track fittings.
- **Ultimate Assembly Strength**
Cam Buckle: 2,500-lbs.
Ratchet Buckle: 3,000-lbs.
- **Working Load Limit**
Cam Buckle: 800-lbs.
Ratchet Buckle: 1,000-lbs.

Standard E-Track Straps	Standard Part No.	Tuff-Edge* Part No.	Wt. (lbs.)
2" X 12' Cam Buckle/Spring E-Track Fittings - Yellow	60805	TE60805	1.6
2" X 16' Cam Buckle/Spring E-Track Fittings - Gray	60806	TE60806	1.7
2" X 20' Cam Buckle/Spring E-Track Fittings - Blue	60807	TE60807	1.8
2" X 12' Ratchet/Spring E-Track Fittings - Yellow	60808	TE60808	2.0
2" X 16' Ratchet/Spring E-Track Fittings - Gray	60809	TE60809	2.1
2" X 20' Ratchet/Spring E-Track Fittings - Blue	60810	TE60810	2.2

* Tuff-Edge web is yellow for all lengths.

NOTE:

Van interior restraint assemblies are only as strong as the anchor or track to which they are attached.



Tie-Off Strap #TOS



Spring Loaded E-Track Fitting (standard)



Horizontal E-Track #60801
12-Ga. Steel Galvanized
10-ft. Sections (17-lbs.)




Vertical E-Track #60802
12-Ga. Steel Galvanized
10-ft. Sections (13-lbs.)

Note: E-Track can be cut into lengths suitable for UPS shipments.

TIEDOWN CHAIN AND LOAD BINDERS

Tiedown Chain Grab Hook Each End	Domestic Part No.	Import Part No.	Wt. (lbs.)
5/16" X 20' G-70 Yellow Dichromate – Welded Hooks	16001	—	21.0
3/8" X 20' G-43 Self-Colored – Welded Hooks	16002	—	32.0
5/16" X 20' G-70 Yellow Dichromate – Clevis Hooks	16005	—	21.0
3/8" X 20' G-43 Self-Colored – Clevis Hooks	16006	—	32.0
Load Binders	Domestic Part No.	Import Part No.	Wt. (lbs.)
5/16" - 3/8" Lever Style	16004	16004I	8.0
5/16" - 3/8" Ratchet Style	16003	16003I	12.0



Tiedown Chain



Load Binders

Lever Style

Ratchet Style