## **20V MAX\* GRINDERS**

**DEWALT** 

XR® Brushless 4-1/2" Angle Grinder DCG413B

SPECIFICATIONS

SPECIFIC/

SPECIFICATIONS

Tool Weight (Tool only)

Voltage

Includes

No Load Speed

Spindle Thread

Spindle Lock

Voltage



XR® Brushless 4-1/2"/ 5" Flathead **Angle Grinder** DCG413FB



4-1/2"/ 5" Angle Grinder DCG412B



XR® Brushless Variable Speed **Die Grinder** DCG426B



SPECIFICATIONS	
Voltage	20V MAX*
No Load Speed	0-25,000 rpm
Spindle Lock	No
Spindle Thread	1/4" Collet
Tool Weight (Tool only)	3.9 lbs
Includes	(2) Wrenches and 1/4" Collet
Tool Weight (Tool only)	3.9 lbs

20V MAX\*

8000 rpm

5/8" - 11

4.1 lbs

Yes

# **AVAILABLE**

DCG413B Batteries and Charger Sold Separately DCG413R2

Also Includes: (2) 20V MAX\* XR® Lithium Ion Batteries (6.0 Ah), Charger, and Kit Bag



DCG413R2

ATIONS		AV
	20V MAX*	DC
ed	9000 rpm	DC
	Yes	
ad	5/8" - 11	
stem	Yes	
ike™	Yes	
Tool only)	3.9 lbs	
	5" Type 27 Guard,2-Position Side Handle, Inner and Outer Flanges, and Hex Wrench	

5" Type 27 Guard, Hex Wrench, and 2-Position Side Handle

4-1/2" Type 27 Guard, 2-Position Side Handle, Inner and Outer Flanges, and

20V MAX\*

9000 rpm

5/8" - 11

Yes

Yes

Yes

3.7 lbs

Hex Wrench

# VAILABLE

G413FB Batteries and Charger Sold Separately Also Includes: (2) 20V MAX\*  $\rm XR^{\otimes}$  Lithium Ion Batteries (6.0 Ah), Charger, and Kit Bag G413FR2



DCG413FR2

#### **AVAILABLE**

DCG412B Batteries and Charger Sold Separately Also Includes: (2) 20V MAX\* XR® Lithium Ion Batteries (5.0 Ah), DCG412P2 Charger, and Kit Bag



DCG412P2

#### **AVAILABLE**

DCG426B Batteries and Charger Sold Separately Also Includes: (2) 20V MAX\*  $\text{XR}^{\otimes}$  Lithium Ion Batteries (4.0 Ah), Charger, and Kit Bag DCG426M2



### DUST EXTRACTION FOR GRIND

5"/ 6" Cutting/Tuckpointing Shroud DWE46100



SPECIFICATIONS	
Max Wheel Diameter	5" / 6"
Hose Port Inner Diameter	35 mm
Hose Port Outer Diameter	42 mm
Tool-Free Shroud Change	No
AirLock™ Compatible	Yes

#### **5" Surface Grinding Dust Shroud** DWE46152



SPECIFICATIONS	
Max Wheel Diameter	5"
Hose Port Inner Diameter	35 mm
Hose Port Outer Diameter	42 mm
Tool-Free Shroud Change	No
AirLock™ Compatible	Yes