

**Honesty®** single-handle bathroom sink faucet

K-99760-4

#### Features

- Single lever handle allows for both volume and temperature control.
- KOHLER ceramic disc valves exceed industry longevity standards for a lifetime of durable performance.
- Temperature memory allows faucet to be turned on and off at the temperature set during prior usage.
- 1.2 gpm (4.5 lmin) maximum flow rate.
- Includes metal pop-up drain with 1-1/4" tailpiece.
- 4-3/16" (107 mm) spout reach.
- Red/blue indexing on handle.
- Coordinates with Honesty faucets and showering components to complete your bathroom.

#### Material

- Brass construction.
- KOHLER finishes resist corrosion and tarnishing.

#### Installation

- For single-hole installation.
- Pre-attached flexible supply lines simplify installation.

#### **Recommended Products/Accessories**

K-23726 Drain treatment K-23723 Faucet cleaner

#### **Included Components**

Additional Components:

Flexible supply hoses





#### Codes/Standards

ASME A112.18.1/CSA B125.1 NSF/ANSI 61 NSF/ANSI 372 All applicable US Federal and State material regulations DOE - Energy Policy Act 1992 EPA WaterSense® California Energy Commission (CEC) ADA ICC/ANSI A117.1 CSA B651 OBC

## KOHLER<sup>®</sup> Faucet Lifetime Limited Warranty

See website for detailed warranty information.

#### **Available Colors/Finishes**

Color tiles intended for reference only.

#### Color Code Description

CP
BN

BL Matte Black

**Polished Chrome** 


Vibrant® Brushed Nickel



### Honesty®

# KOHLER, Faucets

single-handle bathroom sink faucet K-99760-4



#### **Technical Information**

All product dimensions are nominal.

#### Faucet:

Flow rate:	1.2 gal/min (4.5 l/min)
Pressure:	60 psi (4.1 bar)
Valve body:	Plastic
Drain included:	Yes
Drain with overflow:	Yes
Spout:	
Spout reach:	4-3/16" (106 mm)

#### Notes

Install this product according to the installation guide.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

