

Drake® Transitional Close Coupled Toilet, 1.28 and 0.8 GPF

FEATURES

- DYNAMAX TORNADO FLUSH® utilizes 360° cleaning power to reach every part of the bowl
- High-efficiency dual flush 1.28 & 0.8 GPF (4.8 & 3.0 LPF)
- CEFIONTECT® ceramic glaze prevents debris and mold from sticking to ceramic surfaces
- Design of the bowl reduces water flow resistance resulting in a quieter flushing sound
- Elongated front bowl, less seat
- Chrome plated trip lever
- 12" Rough-in
- Semi-concealed trapway

MODELS

- CST748CEMG (#01, #03, #11, #12)
With CEFIONTECT ceramic glaze
- CST748CEM (#51)
Without CEFIONTECT ceramic glaze

COMPONENTS

- CT746CU(G)
Elongated bowl with CEFIONTECT
- ST748EMA
Tank and cover only

COLORS/FINISHES

- | | |
|--------------------|----------------------|
| • #01 Cotton | Made to Order |
| • #12 Sedona Beige | • #03 Bone |
| | • #11 Colonial White |
| | • #51 Ebony |



 **DYNAMAX
TORNADO FLUSH**

 **CEFIONTECT**

 **WATER SAVING**

PRODUCT SPECIFICATION

The two-piece high-efficiency DYNAMAX TORNADO FLUSH toilet shall be dual flush 1.28 GPF/0.8 GPF. Toilet shall be 12" rough-in. Toilet shall have optional CEFIONTECT ceramic glaze. Toilet shall have elongated front bowl and chrome plated trip lever. Toilet shall be TOTO Model CST748CEMG.

CODES/STANDARDS

- Meets and exceeds ASME A112.19.2/CSA B45.1, ASME A112.19.14
- Certifications: IAPMO(cUPC®), EPA WaterSense, State of Massachusetts, and others
- Code Compliance: UPC, IPC, NSPC, NPC Canada, and others
- Complies with CA AB715, CA Green Building Code, Los Angeles Water Efficiency Ordinance and others
- Complies with CA Prop 65 warning requirements



CST748CEMG

Drake® Transitional Close Coupled Toilet, 1.28 and 0.8 GPF


SPECIFICATIONS

Water Use	1.28 & 0.8 GPF (4.8 & 3.0 LPF)
Flush System	DYNAMAX TORNADO FLUSH®
Min. Water Pressure	8 psi (Static)
Water Surface	5-5/8" x 4-1/8"
Trap Diameter	2-1/2"
Rough-in	12"
Trap Seal	2-1/8"
Warranty	One Year Limited Warranty
Material	Vitreous China
Shipping Weight	CT746CU(G) 66 lbs. ST748EMA 33.1 lbs.
Shipping Dimensions	CT746CU(G) 28" L x 15-1/4" W x 16-7/8" H ST748EMA 19-7/8" L x 9-3/8" W x 15-5/8" H

INSTALLATION NOTES


Back-to-Back Toilet Installations:

TOTO recommends the use of a nationally listed, double sanitary tee-wye only, in vertical waste stacks, in accordance with the stipulations noted in the majority of nationally recognized plumbing codes.



To maintain adequate wall gap between the back of the tank and wall, mount the floor flange at a nominal 12" rough-in distance.

DIMENSIONS



Fixture Dimensions shown are nominal. These dimensions and specifications are subject to change without notice.