

Select Pro

PREPROGRAMMED WITH THE OPTION TO MATCH THE OEM PROFILE

ECM REPLACEMENT FOR FURNACES AND **AIR HANDLERS**



















Industry-leading moisture protection



Integrated **Bluetooth**[®] Technology



Integrated Bluetooth® Technology

Preprogrammed. To unlock advanced features, download the RESCUE Select Pro programming app: **Ready to install!**

No additional programming tool required!

- OEM direct programming
 Customized airflow in operation
- Real-time diagnostics

FREE from Google Play or the App store



App Store


Programmable and Tunable in Operation



SPECIFICATIONS

HORSEPOWER: 1/3, 1/2, 3/4 and 1 HP VOLTAGE: 1Ø, 115, 208-230 Vac SPEEDS: Programmable (1075/Var) ROTATION: Programmable (CCW or CW) INPUTS: 24Vac, Tap Inputs HERTZ: 50/60 Hz

OPERATION MODE: Constant Torque FRAME: NEMA®† 48 ENCLOSURE: Open Air Over (OAO) EFFICIENCY: Up to 82% MOUNTING: Belly-band



CATALOG NUMBER	НР	VOLTS	AMPS	RPM	DIM. A	DIM. B
6633	1/2 -1/3	115/208-230	6.3/4.0-3.8	1075/Var	3.662	11.225
6643	3/4	115/208-230	9.3/5.8-5.4	1075/Var	4.037	11.6
6653	1	115/208-230	12.4/7.8-7.2	1075/Var	4.412	11.975



8050 W. Florissant Avenue | St. Louis, MO 63136 Phone: 855-487-6686 | Fax: 800-899-2887

† All marks shown within this document are properties of their respective owners.

Nidec, 2020; All Rights Reserved. U.S. MOTORS® is a registered trademark of Nidec Motor Corporation. Nidec Motor Corporation trademarks followed by the ® symbol are registered with U.S Patent and Trademark Office

