Location: SYMMONS® Dia[®] the smart choice™

3501-CYL-B-TRM, 3501CYLBTRMTC Shower Trim **Specification Submittal**

Feature Highlights

- Dia Shower Trim
 Requires Temptrol[®] Pressure Balancing Shower Valve
- Metal lever handle
- 1 mode showerhead
- 2.5 gpm (9.5 L/min) flow restrictor
- Tub spout not included
- Components shall be metal and nonmetallic construction, plated in standard Polished Chrome finish
- Available with TA-10 flow control spindle and T-12A cap assembly for Temptrol valve bodies installed with Test Cap (order p/n 3501CYLBTRMTC)

Model Numbers

- 3501-CYL-B-TRM Shower Trim, Temptrol Pressure Balancing Shower Valve ordered separately
- 3501CYLBTRMTC
 Shower Trim with TA-10 flow control spindle and
 T-12A cap assembly, must order Temptrol valve with Test Cap

Compliance

• ASME A112.18.1/CSA B125.1



Warranty

Limited Lifetime - to the original end purchaser in consumer/residential installations.

5 Years - for industrial/commercial installations.

Refer to www.symmons.com/warranty for complete warranty information. Go to www.symmons.com/register to register your Symmons product.


Options/Modifications

-	
-1.5 CG	1.5 gpm (5.7 L/min) flow restrictor
-2.0	2.0 gpm (7.6 L/min) flow restrictor
Delete Suffix B	Chrome plastic escutcheon on valve with color graphic/indicators in place of standard brass escutcheon
-EX	Exposed column/slide bar, hand shower bracket and hand shower wand (35EX)
-L1	Less showerhead
-REB	Rebuild trim kit, includes TA-10 and TA-4
-SH2	Alternative 352SH-3, 3 mode showerhead
-SH3	Alternative 362SH Duro showerhead
-SH4	Alternative 361SH Duro square showerhead
-VP	Vandal resistant escutcheon screws in place of standard screws
-BBZ	Brushed Bronze finish
-MB	Matte Black finish
-STN	Satin Nickel finish


Note: Append appropriate -suffix to model number.



Dimensions



Measurements			
Α	Ø 2-1/2", 64 mm		
В	6-3/4", 171 mm		
С	Ref. 77", 1956 mm		
D	3-1/2", 89 mm		
E	Ø 7-1/2", 191 mm		
F	3", 76 mm		
G	2-7/8", 73 mm		
Н	Ref. 42", mm		
I	Rough-in 2-3/8" ± 1/2", 60 mm ± 13 mm		
J	6-3/4", 171 mm		
K	6", 152 mm		
L	5-5/8", 143 mm		



Notes:

- 1) Valve body and piping not included and shown as reference only.
- 2) Plaster shield (p/n T-176) for dry wall, plaster or other type walls 1/2" or greater.
- 3) All dimensions measured from nominal rough-in (see I as reference).
- 4) Dimensions subject to change without notice.